

Specification Sheet

P/N: MLV-YT12NR47M-C4-RU

Products: Certifications:

Molded Power Chokes ISO9001

Multilayer Chip Inductors IATF16949

<u>Lan Transformer</u> ISO14001

RF Passive / Antennas QC080000

Automotive

US Office Contact Us

5406 Bolsa Ave., Huntington Beach, CA 92649 (714) 898-8377 www.maglayersusa.com info@maglayersusa.com

Application

Laptop, desktop and server applications

High current power supplies

Battery powered devices

PMIC

Features

RoHS compliant & halogen free

Low resistance and high current rating

Magnetic core made by high performance magnetic metal powder

Product Identification

MLV - YT12 N R47
$$\square$$
 - C4 -RU

- 1 Product Code
- ② Dimensions
- 3 Inductance: R47 = $0.47 \mu H$
- 4 Inductance Tolerance: M = ±20%, N = ±30%
- Series Type: C4 Type

Note: Please refer to the "Product Dimension" for detail dimensions.



Electrical Performance

	Inductance	Rdc(mΩ)		Heat rating	Saturation
Part number	@0A	Ruc	(11152)	current (ldc) ¹	current (Isat) ²
	(µH)	Тур.	Max.	DC amps (A)	DC amps (A)
MLV-YT12NR47□-C4-RU	0.47	18	23	5.5	6

Note

Test frequency: 1MHz, 0.25V.

Test instruments: Inductance/saturation current: Keysight 4285A or equivalent.

Rdc: ADEX AX1152D or equivalent.

Notes:

1. The heat rating current (Idc) will cause temperature rise approximate 40℃.

2. The saturation current (Isat) will cause initial inductance drop approximate 30%.


3. All test data is referenced at 25℃ ambient.

4. Operating temperature range -40℃ to +125℃.

5. Withstand voltage: 25V DC.




Electrical Characteristics





Product Dimension




Dimension Part number	А	В	С	D
MLV-YT12NR47□-C4-RU	2.5 ± 0.2	2.0 ± 0.2	1.2 Max	0.6 ± 0.2

Unit: mm



Recommended PCB Layout



Туре	YT12
А	2.0
В	1.2
C	2.8

Unit: mm

Safety precaution

- 1. Do not make any through holes and copper pattern in the dotted line area. Except a copper pattern to the electrode.
- 2. Don't design/mount any components in contact with this product.

This power choke do not have any protective function in abnormal condition such as overload, short circuit, open conditions and etc, it shall be confirmed as the end product that there is no risk of smoking, fire, dielectric withstand voltage, insulation resistance etc. in abnormal conditions to provide protective devices and/or protection circuit in the end product.It is recommended the temperature rise of choke during operation is less than 50%.


Packaging

Peel-off force




The peel off force of cover tape is 10 to 70 grams in the arrow direction.

Dimensions



Туре	А	В	С	D	Е	F
8mm	178±1	60+0.5/-0	19.3±0.1	13±0.2	9±0.5	12±0.5


Unit: mm



TYPE	SIZE	А	В	W	Р	Т
MLV	YT12	2.27	2.74	8.0	4.0	1.4


Unit: mm





Taping quantity

raping quantity				
Series	YT12			
PCS/Reel	3000			



Tape packing case

Number of case	W	L	Н
2	18±0.5	18±0.5	2.4±0.2
3	18±0.5	18±0.5	3.6±0.2
4	18±0.5	18±0.5	4.8±0.2
5	18±0.5	18±0.5	6.0±0.2