

OCXO Model: OS400-1005-017

Issue 2; 11th May 2022

Features

- Temperature stability to ± 10 ppb
- Low phase noise
- Frequency 10MHz
- Industry standard package
- The flexible nature of the design means that variations to suit almost any application can be developed to meet individual customer requirements



Option B

- Temperature stability: ± 10 ppb over $(-20$ to $+70)^{\circ}\text{C}$
- Output: Sinewave +7dBm nominal
- Harmonics: -20dBc
- Voltage: 12.0V
- Warm up current: 220mA
- Quiescent current: 120mA

Phase Noise (typical)

- $F_{0}+10\text{Hz}$ -125 dBc/Hz
- $F_{0}+100\text{Hz}$ -145 dBc/Hz
- $F_{0}+1\text{KHz}$ -155 dBc/Hz
- $F_{0}+10\text{KHz}$ -165 dBc/Hz
- $F_{0}+100\text{KHz}$ -168 dBc/Hz

Values based on a 10MHz unit

Voltage / Load change

- $\pm 5\%$ supply voltage change: ± 2 ppb
- $\pm 10\%$ load change: ± 10 ppb

Ageing

Bases on 10MHz unit after 30 days continuous operation:

- Per day: ± 0.7 ppb max.
- Per year: ± 200 ppb max.
- Warm up time: 5 minutes to within 1 ppm

Voltage Trim

- ± 0.5 ppm minimum
- Trim impedance 50K Ω


Reference Options

- 4.5V


Environmental

- Electrostatic-Sensitive Device (ESD)
- Storage Temperature Range: $(-40$ to $+125)^{\circ}\text{C}$

Dimensions (mm)



Phase Noise Plot



- Mechanical shock: MIL standard 202F, method 213, condition J
- Thermal shock: MIL standard 202F, method 107, condition A
- Vibration: MIL standard 202F, method 204, condition B
- Solderability: 5 seconds maximum at 230°C
- 3 seconds maximum at 350°C

Compliance

- RoHS Status (2011/65/EU) - Compliant
- REACH Status - Compliant

Packaging

- Pack Style: Bulk

Ordering Information

- Unique customer part number and custom specification issued with each application
- OCXO Model: OS400-1005-017
- Frequency: 10MHz
- Stability/Output/Voltage: Option B
- Supply voltage code: V3 = +12.0Vd.c. supply
- Add suffix (R) for Vref output on pin #5

Test Circuit - Sinewave

