


Feb. 1. 2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	
△					△					
△					△					
APPLICATION STANDARD										
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C			STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C				
	VOLTAGE	AC 50 V			OPERATING HUMIDITY RANGE	RELATIVE HUMIDITY : 95 % MAX (NO DEW CONDENSATION IS PERMITTED)				
	CURRENT	0.3 A								
SPECIFICATIONS										
ITEM	TEST METHOD				REQUIREMENT				QT	AT
CONSTRUCTION										
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING				X	X
MARKING		CONFIRMED VISUALLY.							X	X
ELECTRICAL CHARACTERISTICS										
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).			60 mΩ MAX.				X	X
INSULATION RESISTANCE		100 V DC.			100 MΩ MIN.				X	-
VOLTAGE PROOF		150 V AC FOR 1 min.			NO FLASHOVER OR BREAKDOWN.				X	X
MECHANICAL CHARACTERISTICS										
INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR.			INSERTION FORCE: 84 N MAX WITHDRAWAL FORCE: 3.5 N MIN.				X	-
MECHANICAL OPERATION		50 TIMES INSERTION AND EXTRACTIONS.			1) CONTACT RESISTANCE 70 mΩ MAX. 2) NO DAMAGE, CRACK AND LOOSENESS OF PART.				X	-
VIBRATION		FREQUENCY: 10 TO 55 Hz, SINGLE AMPLITUDE: 0.75 mm, — m/s ² AT 10 CYCLES FOR 3 DIRECTIONS.			1) NO ELECTRICAL DISCONTINUITY OF 1 μs MIN. 2) NO DAMAGE, CRACK AND LOOSENESS OF PART.				X	-
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.							X	-
ENVIRONMENTAL CHARACTERISTICS										
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90~95 %, 96 h.			1) CONTACT RESISTANCE: 70 mΩ MAX. 2) INSULATION RESISTANCE: 100 MΩ MIN.				X	-
RAPID CHAGE OF TEMPERTURE		TEMPERATURE -55→15~35→ 85→15~35°C TIME 30→ 2~ 3→ 30→ 2~ 3 min. UNDER 5 CYCLES.			3) NO DAMAGE, CRACK AND LOOSENESS OF PART.				X	-
DRY HEAT		EXPOSED AT 85 °C, 96 h.			1) CONTACT RESISTANCE: 70 mΩ MAX.				X	-
COLD		EXPOSED AT -55 °C, 96 h.			2) NO DAMAGE, CRACK AND LOOSENESS OF PART.					
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.			NO HEAVY CORROSION.				X	-
SULPHUR DIOXIDE		EXPOSED IN 10 PPM FOR 96 h. (TEST STANDARD: JIS C 0090)			1) CONTACT RESISTANCE: 70 mΩ MAX. 2) NO HEAVY CORROSION				X	-
RESISTANCE TO SOLDERING HEAT		REFLOW RECOMMENDED TEMPERATURE PROFILE  25°C (60 S) 150°C 160°C (30 S) 240°C 5 S MAX 200°C 60~90 S (20~30 S)			NO MELTING OF RESIN WHICH AFFECTS THE PERFORMANCE OF COMPONENT.				X	-
SOLDRABILITY		SOLDERED AT SOLDER TEMPERATURE, 235 °C FOR IMMERSION DURATION, 2 s.			NO PINHOLE OR DEWETTING ON SOLDERED SURFACE.				X	-
REMARKS					DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED	
					<i>J. Nishikawa</i>	<i>J. Nishikawa</i>	<i>M. Ashida</i>	<i>T. Yoshimura</i>		
UNLESS OTERWISE SPECIFIED, REFER TO JIS C 5402.					99.10.25	99.10.25	99.10.26	99.10.16		
NOTE QT: QUALIFICATION TEST AT: ASSURANCE TEST X: APPLICABLE TEST										
HS HIROSE ELECTRIC CO., LTD.				SPECIFICATION SHEET				PART NO.		
				FX11LB - 140P - SV (21)						
CODE NO. (OLD)			DRAWING NO.			CODE NO.			1	
CL			ELC4 - 152107 - 01			CL 573 - 0055 - 3 - 21			1	

TO
PCK