



HDC

TE Internal #: T2050002010-000

Socket Contact, Silver, 8 – 8 AWG Wire Size, 8.34 mm<sup>2</sup> Wire Size, Crimp, Copper Alloy, Power

[View on TE.com >](#)

Connectors > Contacts > Connector Contacts



Contact Type: **Socket**

Contact Mating Area Plating Material: **Silver**

Wire Contact Termination Area Plating Material: **Silver**

Wire Size: **8.34 mm<sup>2</sup>**

**Features**

**Product Type Features**

Discrete Wire Type	Solid or Stranded
Sealable	No

**Contact Features**

Contact Mating Area Plating Material Finish	Bright
Contact Underplating Material	Copper
Contact Type	Socket
Contact Mating Area Plating Material	Silver
Wire Contact Termination Area Plating Material	Silver
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	100 A

**Termination Features**

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

**Dimensions**

Wire Size	8.34 mm <sup>2</sup>
-----------	----------------------



### Operation/Application

Compatible With Wire Base Material	Copper
Circuit Application	Power

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


### Compatible Parts

 <p>TE Part # T2050001010-000 CNM-10</p>	 <p>TE Part # T2111028201-000 HMN-D2-FC</p>	 <p>TE Part # T3100000035-000 REMOV-HMN-D2</p>
---	---	---

### Customers Also Bought



TE Part #647402-4  
04P SL156 HSG W/RMP&TABS,OVSZ



TE Part #T1419320000-000  
H32A-AG



TE Part #T1500243000-000  
H24B-AG-LB



TE Part #3-1546306-0  
30P.374" DR BARRIER STRIP



TE Part #T1340160125-000  
H16B-TGH-RO-M25



TE Part #T1340240132-000  
H24B-TGH-RO-M32



TE Part #T2040322101-000  
HE-016-M 17-32



TE Part #HSA002N00420100000  
723 HTEC PLUG, SPEEDTEC



TE Part #T2120082201-100  
ZGG-8D (1-2 / 4-5 / 7-8)

TE Part #HKA008N00420100000  
723 HTEC EXTENSION, SPEEDTEC

## Documents

### Product Drawings

CNF-10

English

### CAD Files

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_T2050002010-000\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_T2050002010-000\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_T2050002010-000\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages



[Heavy Duty Connectors](#)

English

[HEAVY DUTY CONNECTORS](#)

English

[HEAVY DUTY CONNECTORS](#)

Japanese

---

[Product Specifications](#)

[Product Specification](#)

English