IXYS

High Voltage Power MOSFET

IXTA05N100HV
IXTA05N100
IXTP05N100

V_{DSS} = 1000V
I_{D25} = 750mA
$R_{DS(on)}$ ≤ 17Ω

N-Channel Enhancement Mode
Avalanche Rated



TO-263HV (IXTA)



TO-263 AA (IXTA)



TO-220AB (IXTP)



G = Gate D = Drain
S = Source Tab = Drain

Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25°C to 150°C	1000	V
V_{DGR}	T_J = 25°C to 150°C, R_{GS} = 1MΩ	1000	V
V_{GSS}	Continuous	±30	V
V_{GSM}	Transient	±40	V
I_{D25}	T_C = 25°C	750	mA
I_{DM}	T_C = 25°C, Pulse Width Limited by T_{JM}	3	A
I_A	T_C = 25°C	1	A
E_{AS}	T_C = 25°C	100	mJ
dv/dt	$I_S \le I_{DM}$, $V_{DD} \le V_{DSS}$, T_J =150°C	3	V/ns
P_D	T_C = 25°C	40	W
T_J		-55 ... +150	°C
T_{JM}		150	°C
T_{stg}		-55 ... +150	°C
T_L	Maximum Lead Temperature for Soldering	300	°C
T_{SOLD}	1.6 mm (0.062in.) from Case for 10s	260	°C
M_d	Mounting Torque (TO-220)	1.13 / 10	Nm/lb.in
Weight	TO-220	3.0	g
	TO-263	2.5	g
	TO-263HV	2.5	g

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
BV_{DSS}	V_{GS} = 0V, I_D = 250μA	1000			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 250μA	2.5		4.5	V
I_{GSS}	V_{GS} = ± 30V, V_{DS} = 0V			±100	nA
I_{DSS}	$V_{DS} = V_{DSS}$, V_{GS} = 0V			25	μA
	T_J = 125°C			500	μA
$R_{DS(on)}$	V_{GS} = 10V, I_D = 375mA, Note 1			17	Ω

Features

- High Voltage Package (TO-263HV)
- Fast Switching Times
- Avalanche Rated
- $R_{ds(on)}$ HDMOS™ Process
- Rugged Polysilicon Gate Cell structure
- Extended FBSOA

Advantages

- High Power Density
- Space Savings

Applications

- Switch-Mode and Resonant-Mode Power Supplies
- Flyback Inverters
- DC Choppers

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
g_{fs}	V_{DS} = 20V, I_D = 500mA, Note 1	0.55	0.93		S
C_{iss}	V_{GS} = 0V, V_{DS} = 25V, f = 1MHz		260		pF
C_{oss}			22		pF
C_{rss}			8		pF
$t_{d(on)}$	**Resistive Switching Times**		11		ns
t_r	V_{GS} = 10V, V_{DS} = 0.5 • V_{DSS}, I_D = 1A		19		ns
$t_{d(off)}$	R_G = 47Ω (External)		40		ns
t_f			28		ns
$Q_{g(on)}$	V_{GS} = 10V, V_{DS} = 0.5 • V_{DSS}, I_D = 1A		7.8		nC
Q_{gs}			1.4		nC
Q_{gd}			4.1		nC
R_{thJC}				3.1	°C/W
R_{thCS}	(TO-220)		0.50		°C/W

Source-Drain Diode

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
I_S	V_{GS} = 0V			750	mA
I_{SM}	Repetitive, Pulse Width Limited by T_{JM}			3	A
V_{SD}	I_F = I_S, V_{GS} = 0V, Note 1			1.5	V
t_{rr}	I_F = I_S, -di/dt = 100A/μs V_R = 100V, V_{GS} = 0V		710		ns

Note 1: Pulse test, t ≤ 300μs, duty cycle, d ≤ 2%.

TO-263HV Outline



PIN: 1 - Gate
2 - Source
3 - Drain

SYM	INCHES MIN	INCHES MAX	MILLIMETER MIN	MILLIMETER MAX
A	.170	.185	4.30	4.70
A1	.000	.008	0.00	0.20
A2	.091	.098	2.30	2.50
b	.028	.035	0.70	0.90
b2	.046	.054	1.18	1.38
C	.018	.024	0.45	0.60
C2	.049	.055	1.25	1.40
D	.354	.370	9.00	9.40
D1	.311	.327	7.90	8.30
E	.386	.402	9.80	10.20
E1	.307	.323	7.80	8.20
e1	.200 BSC		5.08 BSC	
(e2)	.163	.174	4.13	4.43
H	.591	.614	15.00	15.60
L	.079	.102	2.00	2.60
L1	.039	.055	1.00	1.40
L3	.010 BSC		0.254 BSC	
(L4)	.071	.087	1.80	2.20

TO-263AA Outline



PIN: 1 - Gate
2,4 - Source
3 - Drain



SYM	INCHES MIN	INCHES MAX	MILLIMETERS MIN	MILLIMETERS MAX
A	.160	.190	4.06	4.83
A1	.080	.110	2.03	2.79
b	.020	.039	0.51	0.99
b2	.045	.055	1.14	1.40
c	.016	.029	0.40	0.74
c2	.045	.055	1.14	1.40
D	.340	.380	8.64	9.65
D1	.315	.350	8.00	8.89
E	.380	.410	9.65	10.41
E1	.245	.320	6.22	8.13
e	.100 BSC		2.54 BSC	
L	.575	.625	14.61	15.88
L1	.090	.110	2.29	2.79
L2	.040	.055	1.02	1.40
L3	.050	.070	1.27	1.78
L4	0	.005	0	0.13

TO-220AB Outline



Pins: 1 - Gate 2 - Drain
3 - Source

SYM	INCHES MIN	INCHES MAX	MILLIMETERS MIN	MILLIMETERS MAX
A	.170	.190	4.32	4.83
b	.025	.040	0.64	1.02
b1	.045	.065	1.15	1.65
c	.014	.022	0.35	0.56
D	.580	.630	14.73	16.00
E	.390	.420	9.91	10.66
e	.100 BSC		2.54 BSC	
F	.045	.055	1.14	1.40
H1	.230	.270	5.85	6.85
J1	.090	.110	2.29	2.79
k	0	.015	0	0.38
L	.500	.550	12.70	13.97
L1	.110	.230	2.79	5.84
ØP	.139	.161	3.53	4.08
Q	.100	.125	2.54	3.18

Fig. 1. Output Characteristics @ T_J = 25ºC



Fig. 2. Output Characteristics @ T_J = 125ºC



Fig. 3. $R_{DS(on)}$ Normalized to I_D = 375mA Value vs. Junction Temperature



Fig. 4. $R_{DS(on)}$ Normalized to I_D = 375mA Value vs. Drain Current



Fig. 5. Maximum Drain Current vs. Case Temperature



Fig. 6. Input Admittance



Fig. 7. Transconductance



Fig. 8. Forward Voltage Drop of Intrinsic Diode



Fig. 9. Gate Charge



Fig. 10. Capacitance



Fig. 11. Forward-Bias Safe Operating Area @ T_C = 25ºC



Fig. 12. Forward-Bias Safe Operating Area @ T_C = 75ºC



Fig. 13. Maximum Transient Thermal Impedance