High Current Molded Power Inductor - PA4346.XXXANLT Series


















***** Footprint:** 14.0mm x 12.8mm Max

@ Current Rating: up to 50A

Inductance Range: 0.22uH to 68uH

Shielded construction and compact design

High current, low DCR, and high efficiency

Minimized acoustic noise and minimized leakage flux

200 Vdc Isolation between terminal and core

	Electi	rical Specificatio	ns @ 25°C - Oper	ating Temperatu	re -55°C to +155°C			
Part Number	Anductance ^{5,8}	Rated ³ Current	DC Resistance		Saturation ² Current	SRF		
	100KHz, 1V		TYP.	MAX.	TYP.	TPY. MHz	Mechanical	K Factor
	uH±20%		mΩ	mΩ	A			
PA4346.221ANLT	0.22	50.0	0.50	0.61	60.0	111	Footprint 1	104.6
PA4346.331ANLT	0.33	37.0	0.65	0.80	59.0	90	Footprint 1	
PA4346.361ANLT	0.36	36.0	0.68	0.84	59.0	72	Footprint 1	
PA4346.391ANLT	0.39	35.0	0.74	0.87	58.0	72	Footprint 1	
PA4346.471ANLT	0.47	34.0	0.77	0.90	58.0	63	Footprint 1	67.9
PA4346.501ANLT	0.50	33.0	0.95	1.10	55.0	60	Footprint 1	
PA4346.561ANLT	0.56	32.5	1.10	1.30	50.0	57	Footprint 1	
PA4346.681ANLT	0.68	31.0	1.30	1.55	42.0	52	Footprint 1	75.8
PA4346.821ANLT	0.82	29.0	1.40	1.70	38.0	48	Footprint 1	68.7
PA4346.102ANLT	1.00	27.0	1.60	1.90	34.0	38	Footprint 1	53.5
PA4346.122ANLT	1.20	24.0	2.40	2.80	30.0	31	Footprint 2	
PA4346.152ANLT	1.50	22.0	3.20	3.80	28.0	29	Footprint 2	43.7
PA4346.182ANLT	1.80	19.0	3.70	4.30	25.0	26	Footprint 2	
PA4346.222ANLT	2.20	15.5	4.1	4.80	23.0	21	Footprint 2	28.3
PA4346.332ANLT	3.30	14.0	6.0	7.00	20.5	17	Footprint 2	20.9
PA4346.472ANLT	4.70	12.5	8.8	10.2	16.0	14	Footprint 2	14.8
PA4346.562ANLT	5.60	12.0	10.0	12.0	15.5	12	Footprint 2	13.9
PA4346.602ANLT	6.00	11.5	12.5	15.0	15.2	11.5	Footprint	
PA4346.682ANLT	6.80	11.0	13.0	16.0	15.0	11	Footprint 2	12.4
PA4346.822ANLT	8.20	10.0	15.0	18.0	12.0	10	Footprint 2	10.5
PA4346.103ANLT	10.0	9.0	19.2	22.0	10.5	9	Footprint 2	13.6
PA4346.153ANLT	15.0	8.2	30.0	36.0	9.2	8	Footprint 2	10.4
PA4346.223ANLT	22.0	7.0	42.0	52.0	7.5	7	Footprint 2	9.2

High Current Molded Power Inductor - PA4346.XXXANLT Series



Electrical Specifications @ 25°C - Operating Temperature -55°C to +155°C										
Part Number	Inductance ^{5,8} 100KHz, 1V	Rated³ Current	DC Resistance		Saturation ² Current	SRF				
			TYP.	MAX.	TYP.	TPY.	Mechanical	K Factor		
	uH±20%	A	mΩ	mΩ	A	MHz				
PA4346.333ANLT	33	5.2	66	80	6.5	6	Footprint 2	6.5		
PA4346.473ANLT	47	4.3	78	94	5.2	5	Footprint 2	5.5		
PA4346.683ANLT	68	3.6	110	132	4.4	3	Footprint 2	4.4		

Notes:


- Actual temperature of the component during system operation (ambient plus temperature rise) must be within the standard operating range.
- The saturation current is the current at which the initial inductance drops by approximately 30% at the stated ambient temperature. The maximum allowable drop at this stated current is 40% of the initial inductance. This current is determined by placing the component in the specified ambient environment and applying a short duration pulse current (to eliminate self-heating effect) to the component.
- 3. The rated current is the DC current required to raise the component temperature by approximately 40°C. Take note that the components' performanc varies depending on the system condition. It is suggested that the component be tested at the system level, to verify the temperature rise of the component during system operation.
- 4. The part temperature (ambient+temp rise) should not exceed maximum operating temperature under worst case operating conditions. Circuit design, PCB trace size and

- thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.
- Please note that the inductance tolerance of all parts are ±20%, except those indicated by an * which are +/- 30%.
- Parts shown in bold are standard catalog parts and are available through sample stock and distribution. Parts in lighter font are available but are not necessarily held in sample stock or distribution and lead times may be longer. Please contact Pulse for availablity.
- 7. The mechanical dimensions are 100% tested in production but do not necessarily meet a product capability index (Cpk) 1.33 and therefore may not strictly conform to PPAP.
- 8. Special Characteristics 🗇


High Current Molded Power Inductor - PA4346.XXXANLT Series




Mechanical



Footprint 1






Footprint 2
Final Layout

SUGGESTED PAD LAYOUT

Series	Mechanical	A	В	(D	E	l	G	Н
PA4346.XXXANLT	Footprint 1	13.5 ±0.5	12.6±0.2	4.7±0.3	2.3±0.3	4.0±0.3	14.5	8.0	5.0
PA4346.XXXANLT	Footprint 2	13.5 ±0.5	12.6±0.2	4.7±0.3	2.3±0.3	4.7±0.3	14.5	8.0	5.0

All Dimensions in mm.

TAPE & REEL INFO



SURFACE MOUNTING TYPE, REEL/TAPE LIST									
FVDF	REEL SIZ	'E (mm)	TA	QTY					
FYPE	A	G	P ₁	W	$K_{_{0}}$	PCS/REEL			
PA4346.XXXANLT	Ø330	24.4	16	24	5.5	500			

High Current Molded Power Inductor - PA4346.XXXANLT Series





Typical Performance Curves




































High Current Molded Power Inductor - PA4346.XXXANLT Series































High Current Molded Power Inductor - PA4346.XXXANLT Series

Core Loss



Bp-p = K *L(uH) *delta I(A)

For More Information:

Americas - prodinfo_power_americas@yageo.com | Europe - prodinfo_power_emea@yageo.com | Asia - prodinfo_power_asia@yageo.com

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2023. Pulse Electronics, Inc. All rights reserved.

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

