




Kemtron | Kemtron 1201 Series

TE Internal #: 2420735-1

Extruded EMI Gasket, Conductive Strip, Silicone Binding, Silver Plated Aluminum (Ag/Al) Filler, Solid Round, 1 m [3.28 ft] Long, Kemtron 1201 Series

[View on TE.com >](#)

EMI & EMC Solutions > EMI Shielding > EMI Gaskets > Extruded EMI Gasket Conductive Strip



Gasket Type: **Extruded EMI Gasket**

Finished Type: **Conductive Strip**

Binding Material: **Silicone**

Filler Material: **Silver Plated Aluminum (Ag/Al)**

Gasket Shape: **Solid Round**

[All Extruded EMI Gasket Conductive Strip \(56\)](#)

Features

Product Type Features

Finished Type	Conductive Strip
Binding Material	Silicone
Filler Material	Silver Plated Aluminum (Ag/Al)

Electrical Characteristics

Resistance to Petroleum	No
Volume Resistivity (Max)	.008 Ω.cm

Body Features

Gasket Type	Extruded EMI Gasket
Gasket Shape	Solid Round

Dimensions

Product Length	1 m[3.28 ft]
Outside Diameter	1.6 mm[.062 in]



Usage Conditions

Operating Temperature Range	-55 – 160 °C[-67 – 320 °F]
-----------------------------	----------------------------

Other

Reuse Limits	Reusable More Than 3 Times
--------------	----------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





Also in the Series | [Kemtron 1201 Series](#)



EMI Gaskets(48)

Customers Also Bought



TE Part #4-1734839-0
FPC CONN. 0.5MM PITCH T/C,40P



TE Part #9-188275-0
MICRO-MATCH SMD FTE



TE Part #2420741-1
Extruded EMI Gasket Conductive Strip



TE Part #154743-E
SMCQ 68 F AB VV 7-03 CL * 0007 137
E002



TE Part #154766-E
SMCB 68 M AB VV 7-03 CL * 0007 137
E004

Documents

Product Drawings

[SSA Cord 1.6mm x 1m L](#)

English

Datasheets & Catalog Pages

[Performance Materials brochure](#)

English

[Datasheet - Conductive Elastomers](#)

English

Product Specifications

[Application Specification](#)

English