## SIEMENS

## Data sheet

## US2:84JUH92EMF



Duplex starter w/ alternator, Size 4, Three phase full voltage, Solid-state overload relay, OLR amp range 50-200A, 110V 50Hz / 120V 60Hz coil, Combination type, Two 150A circuit breakers, Enc NEMA type 4 painted steel, Water/dust tight for outdoors

Fi	aur	es	imi	lar
	90.	0.5		I CAI

product brand name	Class 84
design of the product	Duplex controller with two MCPs with alternator
special product feature	ESP200 overload relay
General technical data	
weight [lb]	106 lb
Height x Width x Depth [in]	56 × 29 × 10 in
touch protection against electrical shock	NA for enclosed products
installation altitude [ft] at height above sea level maximum	6560 ft
ambient temperature [°F]	
<ul> <li>during storage</li> </ul>	-22 +149 °F
during operation	-4 +104 °F
ambient temperature	
<ul> <li>during storage</li> </ul>	-30 +65 °C
during operation	-20 +40 °C
country of origin	USA
Horsepower ratings	
yielded mechanical performance [hp] for 3-phase AC motor	
• at 200/208 V rated value	40 hp
• at 220/230 V rated value	50 hp
• at 460/480 V rated value	100 hp
• at 575/600 V rated value	100 hp
Contactor	
size of contactor	NEMA controller size 4
number of NO contacts for main contacts	3
operating voltage for main current circuit at AC at 60 Hz maximum	600 V
operational current at AC at 600 V rated value	135 A
mechanical service life (switching cycles) of the main contacts typical	500000
Auxiliary contact	
number of NC contacts at contactor for auxiliary contacts	0
number of NO contacts at contactor for auxiliary contacts	1
number of total auxiliary contacts maximum	7
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)
Coil	
type of voltage of the control supply voltage	AC
control supply voltage	

	0 0)/
at DC rated value	00V
at AC at 50 Hz rated value	110 110 V
at AC at 60 Hz rated value	120 120 V 22 W
holding power at AC minimum	510 VA
apparent pick-up power of magnet coil at AC apparent holding power of magnet coil at AC	51 VA
operating range factor control supply voltage rated value	0.85 1.1
of magnet coil	0.00 1.1
percental drop-out voltage of magnet coil related to the input voltage	50 %
ON-delay time	18 34 ms
OFF-delay time	10 12 ms
Overload relay	
product function	
<ul> <li>overload protection</li> </ul>	Yes
<ul> <li>phase failure detection</li> </ul>	Yes
<ul> <li>asymmetry detection</li> </ul>	Yes
<ul> <li>ground fault detection</li> </ul>	Yes
<ul> <li>test function</li> </ul>	Yes
external reset	Yes
reset function	Manual, automatic and remote
trip class	CLASS 5 / 10 / 20 (factory set) / 30
adjustable current response value current of the current- dependent overload release	50 200 A
tripping time at phase-loss maximum	3 s
relative repeat accuracy	1 %
product feature protective coating on printed-circuit board	Yes
number of NC contacts of auxiliary contacts of overload relay	1
number of NO contacts of auxiliary contacts of overload relay	1
operational current of auxiliary contacts of overload relay	
• at AC at 600 V	5 A
• at DC at 250 V	1 A
contact rating of auxiliary contacts of overload relay according to UL	5A@600VAC (B600), 1A@250VDC (R300)
insulation voltage (Ui)	
with single-phase operation at AC rated value	600 V
with multi-phase operation at AC rated value	300 V
Enclosure	
degree of protection NEMA rating of the enclosure	NEMA Type 4
design of the housing	dustproof, waterproof & weatherproof
Circuit Breaker	
type of the motor protection	Motor circuit protector (magnetic trip only)
operational current of motor circuit breaker rated value	150 A
adjustable current response value current of instantaneous short-circuit trip unit	800 1500 A
Mounting/wiring	
mounting position	Vertical
fastening method	Surface mounting and installation
type of electrical connection for supply voltage line-side	Box lug
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded	1x (6 AWG 350 Kcmil) or 1x (4 AWG 350 Kcmil)
temperature of the conductor for supply maximum permissible	75 °C
material of the conductor for supply	AL or CU
type of electrical connection for load-side outgoing feeder	Box lug
tightening torque [lbf·in] for load-side outgoing feeder	200 200 lbf·in
type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi- stranded	1x (6 AWG 250 MCM)
temperature of the conductor for load-side outgoing feeder	75 °C

maximum permissible				
material of the conductor for load-side outgoing feeder	CU			
type of electrical connection of magnet coil	Screw-type terminals			
tightening torque [lbf·in] at magnet coil	5 12 lbf·in			
type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded	2x (16 12 AWG)			
temperature of the conductor at magnet coil maximum permissible	75 °C			
material of the conductor at magnet coil	CU			
type of electrical connection at contactor for auxiliary contacts	Screw-type terminals			
tightening torque [lbf-in] at contactor for auxiliary contacts	10 15 lbf·in			
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)			
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C			
material of the conductor at contactor for auxiliary contacts	CU			
type of electrical connection at overload relay for auxiliary contacts	Screw-type terminals			
tightening torque [lbf-in] at overload relay for auxiliary contacts	7 10 lbf·in			
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded	2x (20 14 AWG)			
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	75 °C			
material of the conductor at overload relay for auxiliary contacts	CU			
Short-circuit current rating				
design of the short-circuit trip	Instantaneous trip circuit breaker			
breaking capacity maximum short-circuit current (Icu)				
• at 240 V	100 kA			
• at 480 V	100 kA			
• at 600 V	25 kA			
certificate of suitability	NEMA ICS 2; UL 508; CSA 22.2, No.14			
Further information				
Industrial Controls - Product Overview (Catalogs, Brochures,)				
www.usa.siemens.com/iccatalog				
Industry Mall (Online ordering system)				
https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:84JUH92EMF				

Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/US/en/ps/US2:84JUH92EMF

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=US2:84JUH92EMF&lang=en

Certificates/approvals

https://support.industry.siemens.com/cs/US/en/ps/US2:84JUH92EMF/certificate

last modified:

1/25/2022 🖸