

NOT RECOMMENDED FOR NEW DESIGN USE <u>AH9485/AH9486</u>



AH5794

SINGLE PHASE HALL EFFECT LATCH FAN MOTOR DRIVER

Description

The AH5794 is a single chip solution for driving single-coil brushless direct current (BLDC) fans and motors. The integrated full-bridge driver output stage uses soft switching to minimize audible switching noise and electromagnetic interference (EMI) providing a low noise solution.

Low operating voltage down to 1.8V allows motor speed to be controlled by varying the supply voltage.

To help protect the motor coil, the AH5794 provides Rotor Lock Protection which shuts down the output drive if rotor lock is detected. The device automatically re-starts when the rotor lock is removed. Over temperature shutdown provides thermal protection for the device.

A Tachometer output is provided by open-drain Frequency Generator (FG) Pin which allows external interface to monitor motor rotation or speed. The FG output is the magnetic change frequency.


The AH5794 is available in space saving and low profile TSOT26 and U-DFN2020C-6 packages.


Features

- Supports Single-Coil Full-Wave BLDC Fan Drivers
- Built-in Hall Sensor and Input Amplifier
- Operating Voltage: 1.8V to 6V
- V_{DD} Voltage Speed Control
- Soft Switching for Low Noise DC Fan Motor Applications
- Rotor Lock Protection (Lock Detection, Output Shutdown and Automatic Re-Start)
- Thermal Protection
- Tachometer (FG) Output
- No External Timing Capacitor Reduces the Numbers of External Components Required
- Low Profile Package: TSOT26 and U-DFN2020C-6
- Halogen and Antimony Free "Green" Packages
- Lead Free Finish/ RoHS Compliant
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative.

https://www.diodes.com/quality/product-definitions/

Pin Assignments





Applications


- 3V/ 3.3V/ 5V BLDC Cooling Fans
- Netbook/ Notebook BLDC Fans
- Instruments Cooling Fans
- Low Voltage/ Low Power BLDC Motors

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



Typical Application Circuit



Pin Descriptions


Pin Name	Description
V _{DD}	Power Supply Pin
Vss	Ground Pin
01	Output Driving & Sinking Pin
O2	Output Driving & Sinking Pin
NC	No Connection
FG	Frequency Generator (Note 4)

Note: 4. The FG output is the same as the magnetic change frequency.

January 2021 © Diodes Incorporated



Functional Block Diagram (Note 5)



Note: 5. The AH5794 has an open-drain tachometer FG output that follows the magnetic change frequency. Typically a pull-up resistor of 10kΩ is recommended from FG pin to the supply voltage.





Absolute Maximum Ratings (TA = +25°C, unless otherwise noted, Note 6)

Symbol	Ch	Characteristics					
V_{DD}	Supply Voltage	Supply Voltage					
IO(PEAK)	Maximum Output Current (Peak)	1000	mA				
	5	TSOT26	650	14/			
PD	Power Dissipation	U-DFN2020C-6	750 (Note 7)	mW			
Tst	Storage Temperature Range		-65 to +150	°C			
ESD HBM	Human Body Model ESD Protection		4	kV			

Notes:

Recommended Operating Conditions (T_A = +25°C)

Symbol	Parameter	Conditions	Min	Max	Unit
V_{DD}	Supply Voltage at V _{DD} Pin	DC Supply Speed Control Mode	1.8	6.0	V
TA	Operating Ambient Temperature Range	Operating	-40	+105	°C

Electrical Characteristics (TA = +25°C, VDD = 5V)

Symbol	Characteristics	Conditions	Min	Тур.	Max	Unit
I _{DD}	Supply Current	No Load	_	2.2	1	mA
V	Output Voltage High	IOUT = 300mA	4.70	4.88	-	V
Voн	Output Voltage High	I _{OUT} = 500mA	4.5	4.8	-	V
Va	Output Voltage Law	I _{OUT} = 300mA	_	0.12	0.3	V
Vol	Output Voltage Low	I _{OUT} = 500mA	_	0.2	0.5	V
Voh +Vol	Cutava Valta as AN and BMCC Combined	I _{OUT} = 300mA	_	0.3	0.5	V
VOH +VOL	Output Voltage of N- and PMOS Combined	I _{OUT} = 500mA	_	0.5	-	V
Tsw	Output Switching Slope Duration	17Ω Load On O1/O2	_	200	-	μs
ILEAK	FG Output Leakage Current	_	_	_	5	μΑ
VFGOL	FG Output Voltage Low	IFG = 5mA	_	_	0.4	V
Ton	On Time	_	350	500	650	ms
R _{DR}	Duty Ratio	Toff/Ton	_	10	_	_
TJ_SDN_TH	IC Junction Temperature Thermal Shutdown Threshold	_	_	175	_	°C
Tj_sdn_hyst	IC Junction Temperature Thermal Shutdown Hysteresis	_	_	25	_	°C

^{6.} Stresses greater than the 'Absolute Maximum Ratings' specified above, can cause permanent damage to the device. These are stress ratings only; functional operation of the device at these or any other conditions exceeding those indicated in this specification is not implied. Device reliability may be affected by exposure to absolute maximum rating conditions for extended periods of time

may be affected by exposure to absolute maximum rating conditions for extended periods of time

7. U-DFN2020C-6 exposed pad soldered to minimum recommended landing pads (see Package Outline Dimension section) on a two-layer 2oz. copper FR4 PCB (1.6mm thickness) with no thermal vias in exposed PADs or any copper flood connecting to the landing pattern of the exposed pad.




Magnetic Characteristics (T_A = +25°C, V_{DD} = 1.8V to 6V, Note 8)


(1mT = 10G)


Symbol	Parameter	Min	Тур.	Max	Unit
Вор	Operate Point	10	25	50	
Brp	Release Point	-50	-25	-10	Gauss
B _{hy}	Hysteresis	-	50		


Note:

Operating Characteristics










^{8.} Magnetic characteristics may vary with supply voltage, operating temperature and after soldering.



Operating Characteristics (Notes 9, 10, 11 and 12)



Truth Table

01	O2	FG
L	H	L
Н	_	Н
L		X (Note 12)

Notes:

- 9. In "Normal spinning, the FG changes its state at each edge of O1.
 10. When the motor locks with South pole at the Hall element, O2 is kept on "L" and O1 is a clock with Ton/Toff ratio. When motor locks with North pole at the Hall element, O1 is kept on "L", O2 is a clock with Ton/Toff ratio.
 11. When "Re-start spinning" occurs, the motor speed ramps up to the "Normal Spinning" speed from zero. Speed ramp-up profile depends on motor characteristics.
- 12. X: H or L depends on magnetic pole North or South



Application Note

Motor Speed Control


DC Supply Voltage (VDD) Speed Control

Motor speed can be controlled by varying the V_{DD} supply voltage between 1.8V to 6V.

With 5V nominal motor, changing V_{DD} voltage between 5V to 1.8V, speed can be controlled from 100% to 36% typically.

Soft Switching

AH5794 uses soft switching of the motor coil current during commutation for to minimize audible switching noise and electromagnetic interference (EMI) to provide a low noise solution.






Thermal Performance Characteristics

(1) Package Type: TSOT26

T _A (°C)	25	50	60	70	75	80	85	90	95	100
P _D (mW)	651	521	469	417	391	365	339	313	286	260
T _A (°C)	105	110	115	120	125	130	135	140	145	150
P _D (mW)	234	208	182	156	130	104	78	52	26	0






Thermal Performance Characteristics (cont.)

(2) Package type: U-DFN2020C-6 (Note 13)

T _A (°C)	25	50	60	70	75	80	85	90	95	100
P _D (mW)	781	625	563	500	469	438	406	375	344	313
T _A (°C)	105	110	115	120	125	130	135	140	145	150
P _D (mW)	281	250	219	188	156	125	94	63	31	0




Note:

^{13.} U-DFN2020C-6 exposed pad soldered to minimum recommended landing pads (see Package Outline Dimension section) on a two-layer 2oz. copper FR4 PCB (1.6mm thickness) with no thermal vias in exposed PADs or any copper flood connecting to the landing pattern of the exposed pad.



Ordering Information




FDC: U-DFN2020C-6

Package	Packaging	7" Tape a	and Reel
Code	(Note 14)	Quantity	Part Number Suffix
WU	TSOT26	3000/Tape & Reel	-7
FDC	U-DFN2020C-6	3000/Tape & Reel	-7
	Code WU	Code (Note 14) WU TSOT26	Code (Note 14) Quantity WU TSOT26 3000/Tape & Reel

Note: 14. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information

(1) Package Type: TSOT26



Part Number	Package	Identification Code
AH5794-WU-7	TSOT26	J4

(2) Package Type: U-DFN2020C-6





XX: Identification Code

Y: Year : 0~9

<u>W</u>: Week: A~Z: 1~26 week; a~z: 27~52 week; z represents 52 and 53 week

 $X : A \sim Z : Internal code$


Part Number	Package	Identification Code
AH5794-FDC-7	U-DFN2020C-6	J4




Package Outline Dimensions (All Dimensions in mm)

Please see http://www.diodes.com/package-outlines.html for the latest version.

(1) Package type: TSOT26




(2) Package Type: U-DFN2020C-6





Taping Orientation

(1) Package Type: U-DFN2020C-6



Note: 15. The taping orientation of the other package type can be found on our website at https://www.diodes.com/assets/Packaging-Support-Docs/ap02007.pdf.



IMPORTANT NOTICE

- 1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2021 Diodes Incorporated

www.diodes.com