SMT Power Inductors

Round Wire Coils - PG0642NL Series







Height: 5.0mm Max

Footprint: 7.9mm x 7.6mm Max
 Saturation Current: up to 32Apk
 Inductance Range: 0.32µH to 5.4µH

Electrical Specifications @ 25°C – Operating Temperature –40°C to +125°C ¹										
Part ⁹ Number	Inductance ² @ Irated (µH TYP)	Irated³ (A)	DCR^4 (m Ω) (±6%)	Inductance @ 0A bc (µH ±20%)	Saturation ⁵ Current Isat (A TYP)	Heating ⁶ Current loc (A TYP)	Core Loss ⁷ Factor K2			
PG0642.401NL	0.32	20.0	3.3	0.40	32	20.0	33.6			
PG0642.681NL	0.54	17.5	4.3	0.68	25	17.5	46.5			
PG0642.102NL	0.80	14.5	5.8	1.00	22	14.5	58.2			
PG0642.152NL	1.20	13.3	6.8	1.50	18	13.3	75.7			
PG0642.222NL	1.70	10.0	12.7	2.20	14	10.0	84.7			
PG0642.332NL	2.60	9.5	16.6	3.30	13	9.5	107.0			
PG0642.472NL	3.70	9.0	18.4	4.70	10	9.0	140.1			
PG0642.682NL	5.40	6.0	26.4	6.80	8	6.0	176.2			

Notes:

- 1. Actual temperature of the component (ambient plus temperature rise) must be within the standard operating temperature range.
- 2. Inductance at Irated is a typical inductance value for the component taken at rated current.
- 3. The rated current listed is the lower of the saturation current (@ 25°C) or the heating current depending on which value is lower.
- 4. The DCR of the part is measured at an ambient temperature of 20C 3C from point a and b as shown above on the mechanical drawing.
- 5. The saturation current, Isar, is the current at which the component inductance drops by 20% (typical) at an ambient temperature of 25°C. This current is determined by placing the component in the specified ambient environment and applying a short duration pulse current (to eliminate self-heating effects) to the component.
- 6. The heating current, I_{DC}, is the DC current required to raise the component temperature by approximately 40°C. The heating current is determined by mounting the component on a typical PCB and applying current for 30 minutes. The temperature is measured by placing the thermocouple on top of the unit under test. Take note that the component's performance varies depending on the system

condition. It is suggested that the component be tested at the system level, to verify the temperature rise of the component during system operation.

7. Core Loss approximation is based on published core data:

Core Loss = K1 * (f) $^{1.48}$ * (K2 \triangle I) $^{1.97}$ Where: Core Loss = in Watts

K1 = 5.894E-10

f = switching frequency in kHz

K1 & K2 = core loss factors

△I = delta I across the component in Ampere

K2*∆I = one half of the peak to peak flux density across the component in Gauss

- 8. Unless otherwise specified, all testing is made at 100kHz, 0.1VAC.
- Optional Tape & Reel packaging can be ordered by adding a "T" suffix to the part number (i.e. PG0642.222NL becomes PG0642.222NLT). Pulse complies to industry standard tape and reel specification EIA481. The tape and reel for this product has a width (W=24mm), pitch (Po=12mm) and depth (Ko=5.5mm).


USA 858 674 8100 Germany 49 7032 7806 0 Singapore 65 6287 8998 Shanghai 86 21 62787060 China 86 755 33966678 Taiwan 886 3 4356768

pulseelectronics.com P670.B (05/15)


SMT Power Inductors


Round Wire Coils - PG0642NL Series

Mechanical



Part Number	X (Ref.)	
PG0642.401NL	1.2mm	
PG0642.681NL	1.2mm	
PG0642.102NL	1.1mm	
PG0642.152NL	1.1mm	
PG0642.222NL	0.8mm	
PG0642.332NL	0.7mm	
PG0642.472NL	0.7mm	
PG0642.682NL	0.7mm	





P670.B (05/15)

For More Information

2

For More Information										
Pulse Worldwide Headquarters	Pulse Europe Einsteinstrasse 1	Pulse China Headquarters B402. Shenzhen Academy of	Pulse North China Room 2704/2705	Pulse South Asia 135 Joo Seng Road	Pulse North Asia 3F. No. 198					
12220 World Trade Drive	D-71083 Herren-	Aerospace Technol-	Super Ocean Finance	#03-02	Zhongyuan Road					
San Diego, CA	berg	ogy Bldg.	Ctr.	PM Industrial Bldg.	Zhongli City					
92128	Germany	10th Kejinan Road	2067 Yan An Road	Singapore 368363	Taoyuan County 320					
U.S.A.		High-Tech Zone	West		Taiwan R. O. C.					
		Nanshan District	Shanghai 200336	Tal. CE (207 0000	Tel: 886 3 4356768					
Tel: 858 674 8100	Tel: 49 7032 78060	Shenzen, PR China 518057	China	Tel: 65 6287 8998 Fax: 65 6287 8998	Fax: 886 3 4356823 (Pulse) Fax: 886 3 4356820 (FRE)					
Fax: 858 674 8262	Fax: 49 7032 7806 135	Tel: 86 755 33966678	Tel: 86 21 62787060	rdx. 03 020/ 0990	rdx. 000 3 4330020 (FRE)					
1 47. 030 074 0202	1 dx. 43 7032 7000 133	Fax: 86 755 33966700	Fax: 86 2162786973							

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2015. Pulse Electronics, Inc. All rights reserved.