

FEATURES


- ❖ 350 watts peak pulse power per line ($t_P=8/20\mu s$)
- ❖ Protects one bi-directional I/O line
- ❖ Low clamping voltage
- ❖ Working voltages: 24V
- ❖ Low leakage current
- ❖ RoHS compliant



SOD-323

MAIN APPLICATIONS

- ❖ Cell phone handsets and accessories
- ❖ Microprocessor based equipment
- ❖ Personal digital assistants (PDA's)
- ❖ Notebooks, desktops, and servers
- ❖ Portable instrumentation
- ❖ Peripherals
- ❖ USB interface



PIN Configuration

MECHANICAL CHARACTERISTICS

- ❖ SOD-323 package
- ❖ Molding compound flammability rating: UL 94V-0
- ❖ Weight 5 milligrams (approximate)
- ❖ Quantity per reel: 3,000pcs
- ❖ Lead finish: lead free
- ❖ Marking code: HC

ABSOLUTE MAXIMUM RATINGS ($T_A=25^\circ\text{C}$, RH=45%-75%, unless otherwise noted)

Rating	Symbol	Value	Unit
Peak pulse power (tp=8/20μs waveform)	P_{PP}	350	W
ESD voltage (Contact discharge)	V_{ESD}	±30	kV
ESD voltage (Air discharge)		±30	
Lead soldering temperature	T_L	260	°C
Storage & operating temperature range	T_{STG}, T_J	-55~+150	°C

ELECTRICAL CHARACTERISTICS ($T_A=25^\circ\text{C}$)

Parameter	Symbol	Condition	Min.	Typ.	Max.	Unit
Reverse stand-off voltage	V_{RWM}				24	V
Reverse breakdown voltage	V_{BR}	$I_{BR}=1\text{mA}$	26.7			V
Reverse leakage current	I_R	$V_R=24\text{V}$			1	μA
Clamping voltage (tp=8/20μs)	V_C	$I_{PP}=1\text{A}$			43	V
Clamping voltage (tp=8/20μs)	V_C	$I_{PP}=3\text{A}$			56	V
Off state junction capacitance	C_J	0Vdc, f=1MHz		0.8		pF

RATINGS AND V-I CHARACTERISTICS CURVES ($T_A=25^\circ\text{C}$, unless otherwise noted)






**FIG.1:V- I curve characteristics
(Bi-directional)**

FIG.2: Pulse waveform (8/20μs)


FIG.3: Pulse derating curve

FIG.4: ESD clamping (8KV contact)


PACKAGE MECHANICAL DATA


Land Pattern

Symbol	Millimeter		Inches	
	Min	Max	Min	Max
A	1.60	1.80	0.063	0.071
B	0.25	0.35	0.010	0.014
C	2.50	2.70	0.098	0.106
D	0.00	1.00	0.000	0.039
E	1.20	1.40	0.047	0.055
F	0.08	0.15	0.003	0.006
L	0.475REF		0.019REF	
L1	0.25	0.40	0.010	0.016
H	0.00	0.10	0.000	0.004
P	3.00		0.118	
P1	0.80		0.031	