

DESCRIPTION

HSY8121BABC is awide input range, high-efficiency and high frequency DC-to-DC step-down switching regulator, capable of delivering up to 2A of output current. With a fixed switching frequency of 1MHz, this current mode PWM controlled converter allows the use of small external components, such as ceramic input and output caps, as well as small inductors.

HSY8121BABC also employs a forced PWM control scheme, thereby ensuring the minimum ripple voltage. Its input can withstand a voltage surgeas high as 30V, making it an ideal solution for industrial applications such as Surveillance Camera, LCDTV, Set Top Box, etc.

HSY8121BABC is available in SOT-23-6L package.


FEATURES

- ◆ Wide Input Range: 4.2V-28V
- Forced PWM control
- 1MHz switching frequency
- Capable of Delivering 2A
- No External Compensation Needed
- Current Mode Control
- Thermal Shutdown and UVLO
- Excellent Load and Line Transient
 Response Available in SOT23-6 Package

APPLICATIONS


- ◆ Surveillance
- Camera Set Top Box
- LCD TV

TYPICAL APPLICATION





PIN CONFIGURATION



ABSOLUTEMAXIMUM RATINGS

(Note: Exceeding these limits maydamage the device. Exposure to absolute maximum rating conditions for long periods mayaffect device reliability.)

IN,SW,ENVoltage		0.	3V to 30V
BST Voltage			
FB Voltage		(0.3V to 6V
Operating Temperature Rang	je	40	°C to 85°C
Storage Temperature Range		55°	C to 150°C
Thermal Resistance	θ JA	θ JC	
SOT-23-6L	180	90	°C/W
Lead Temperature (Soldering	10ssed	c)	260°C
ESD HBM (Human Body Mod	de)		2KV
ESD MM (Machine Mode)			200V

PIN DESCRIPTION

PIN#	NAME	DESCRIPTION
1	BST	Bootstrap pin. Connect a 10nF capacitor from this pin to SW
2	GND	Ground
3	FB	Feedback Input. Connect an external resistor divider from the output to FB and GND to set V _{OUT}
4	EN	Enable pin for the IC. Drive this pin high to enable the part, low to disable.
5	VIN	Supply Voltage. Bypass with a 4.7µFceramic capacitor to GND
6	sw	Inductor Connection. Connect an inductor Between SW and the regulator output.




ELECTRICAL CHACRACTERISTICS


(V_{IN}= 12V, V_{OUT}= 3.3V, unlessotherwise specified. Typical values are at TA = 25°C.)

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNIT
Input Voltage Range		4.2		28	V
Input UVLO	Rising, Hysteresis=340mV		4.2		V
Input Supply Current	Vin=12V, lout=0, Vfb=0.85V, no switching		750		μA
Input ShutdownCurrent			7	14	μA
FB Voltage		0.784	8.0	0.816	V
FB Input Current			0	1	μA
Switching Frequency			1000		kHz
Maximum Duty Cycle			99		%
Short Circuit Hiccup Time	On Time		2		mS
Short Circuit Flictup Time	Off Time		6		mS
FB Hiccup Threshold			0.2		V
High Side Switch On Resistance			160		mΩ
Low Side Switch On Resistance			95		mΩ
High Side Current Limit			3.5		Α
SW Leakage Current	IN=SW=12V			20	μA
ENRising Threshold			1.5		V
EN Falling Threshold			1.3		V
EN Input Current	Ven=2V		1		uA
Thermal Shutdown	Rising, Hysteresis =40°C		150		\mathcal{C}


TYPICAL CHARACTERISTICS


(Typical values are at $T_A=25^{\circ}C$ unless otherwise specified.)
























Switching Waveform at lout = 1A



FUNCTIONAL BLOCK DIAGRAM



FUNCTIONAL DESCRIPTION

The HSY8121BABC is a synchronous buck regulator ICs that integrates the PWM control, top and bottom switches on the same die to minimize the switching transition loss and conduction I

The HSY8121BABC is a wide input range, high efficiency, DC-to-DC step-down switching regulator, capable of delivering up to 2A of output current, integrated with a 160m high side and 95m low side MOSFET. It uses PWM current-mode control scheme. An error amplifier integrates error between the FB signal and the internal reference voltage. The output of the integrator is then compared to the sum of a current-sense signal and the slope compensation ramp. This operation generates a PWM signal that modulates the duty cycle of the power MOSFET to achieve regulation for output voltage.

Forced PWM Operation

AforcedPWM DC-DC regulator always switches at a fixed frequency even when the output load is small. This is to ensure a minimum output voltage ripple over the full load range. It may induce a relatively large (about 10mA when Vin=12V) input current when load is zero.

Enable

EN is a digital control pin that turns the HSY8121BABC on and off. Drive ENHigh to turn on the regulator, drive it Low to turnit off. An internal 1MΩ resistor from EN pin to GND allows EN to float to shutdown the chip. Connecting the EN pin through a pull up resistor or shorted EN to IN will automatically turn on the chip whenever plug in IN.



Over Current Protection and Hiccup

HSY8121BABC has a cycle-by-cycle over current limit for when the inductor current peak value is over the set current limit threshold. When the output voltage drop until FB falls below UV threshold (0.2V), the HSY8121BABC will enter hiccup mode. It will turn off the chip immediately for 6mS. After that, it will try to re-starts as normal for 2mS. After 2mS, if FB is still below UV threshold, then the chip enters hiccup mode again. If FB is higher than UV threshold, it will enter the normal mode.

Over-Temperature Protection

Thermal protection disables the output when the junction temperature rises to approximately 150°C, allowing thedevice to cooldown. When the junction temperature cools to approximately 110°C, the output circuitry is againenabled. Depending on power dissipation, thermal resistance, and ambient temperature, the thermal protection circuit may cycle on and off. This cycling limits regulator dissipation, protecting the device from damage as are sult of overheating.

APPLICATION INFORMATION

External Output Voltage Setting

In external Output Voltage Setting Version selected, the HSY8121BABC regulator is programmed using an external resistor divider. The output voltage is calculated using below equation.

$$V_{OUT} = V_{REF} \times (1 + \frac{R_u}{R_d})$$


Where: VREF = 0.8V typically (theinternal reference voltage)

Resistors Rdhas to be between 1kOhm to 12KOhmand thus Ru is calculated by following equation.

$$R_u = \left(\frac{V_{OUT}}{V_{RFF}} - 1\right) \times R_d$$

PCB LAYOUT GUIDE


For any high voltage buck, it is always crucial to have input capacitor placed as close to the chip's IN and GND pin without any via, because the input capacitor is to keep the chip's real input voltage from dropping too much when large switching current is drawn from the input node. A simple illustration of how to place input capacitor and draw the trace to the chip's IN and GND pins is show n below, and it is highly recommended to strictly follow this guide.







PACKAGE OUTLINE

Package: SOT-23-6L







	IVI I F1	Wax	l Wiin	Wax	
Α	1.050	1.250	0.041	0.049	
A1	0.000	0.100	0.000	0.004	
A2	1.050	1.150	0.041	0.045	
b	0.300	0.500	0.012	0.020	
С	0.100	0.200	0.004	0.008	
D	2.820	3.020	0.111	0.119	
E	1.500	1.700	0.059	0.067	
E1	2.650	2.950	0.104	0.116	
е	0.950	(BSC)	0.037(BSC)		
e1	1.800	2.000	0.071	0.079	
L	0.300	0.600	0.012 0.024		
θ	0°	8°	0° 8°		



Attention

- Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.
- HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.
- Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production.

 HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.