

Specification Sheet

Part Number: 169-60307



Tubing provides full coverage where spiral wrap or other coverings may not be suitable.

In harsh applications the tubing provides resistance to crushing, impact, and abrasion.

Tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat, cold, and sunlight on cables and wires.

Convoluted Tubing, Flame Retardant, Unslit, 0.25" Dia, PE, Gray, 2500 ft/ctn

Article Number 169-60307

Type CTPFR140UNSLIT

Color Gray (GY)

Quantity Per carton

Product Description

HellermannTyton's Convoluted Tubing, also known as Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires. The polyethylene flame-retardant material provides additional protection that is suitable for applications requiring a self-extinguishing material and complies with UL 94 V2 standards.

| | |
|--------------------------------|------------------------------------------------------------------------------|
| Short Description | Convuluted Tubing, Flame Retardant, Unslit, 0.25" Dia, PE, Gray, 2500 ft/ctn |
| Global Part Name | CTPFR140UNSLIT-PE-FR-GY |
| Length L (Imperial) | 2500.0 |
| Length L (Metric) | 762.0 |
| Variant | Unslit |
| Inner Diameter D (Imperial) | 0.276 |
| Inner Diameter D (Metric) | 7.01 |
| Diameter D (Imperial) | 0.398 |
| Diameter D (Metric) | 10.11 |
| Outside Diameter OD (Imperial) | 0.398 |
| Outside Diameter OD (Metric) | 10.11 |
| Nominal Diameter (Imperial) | 0.25 |
| Nominal Diameter (Metric) | 6.35 |
| Wall Thickness WT (Imperial) | 0.004 |
| Wall Thickness WT (Metric) | 0.102 |

| | |
|------------------------------|---------------------------------------|
| Material | Polyethylene, flame retardant (PE-FR) |
| Material Shortcut | PE-FR |
| Flammability | UL 94 V-2 |
| Halogen Free | No |
| UV Resistant (Yes/No) | No |
| Operating Temperature | -40°F to +185°F (-40°C to +85°C) |
| Reach Compliant (Article 33) | Yes |
| ROHS Compliant | Yes |
| Package Quantity (Imperial) | 2500 |
| Package Quantity (Metric) | 762.0 |
| Customs Number | 3926909988 |

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

