



### SPECIFICATIONS

Current Rating: 1.5 Amps  
 Insulation Resistance:  $1000\text{M}\Omega$  Min  
 Contact Resistance:  $20\text{m}\Omega$  Max  
 Withstanding Voltage: AC 500V  
 Operation Temperature:  $-40^\circ$  to  $+105^\circ$   
 Contact Material: Brass  
 Standard: PA6T  
 Insulator Material: Polyester  
 Contact Plating: Gold Flash  
 Max. Processing Temp:  $240^\circ\text{C}$  for 30-60seconds  
 ( $260^\circ\text{C}$  for 5 seconds)

RECOMMEND P. C. B LAYOUT  
 PCB TOLERANCE:  $\pm 0.05$  (TOP VIEW)

# 深圳市虹成电子有限公司

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
1	0.00	2.00	11	20.00	22.00	21	40.00	42.00	31	60.00	62.00
2	2.00	4.00	12	22.00	24.00	22	42.00	44.00	32	62.00	64.00
3	4.00	6.00	13	24.00	26.00	23	44.00	46.00	33	64.00	66.00
4	6.00	8.00	14	26.00	28.00	24	46.00	48.00	34	66.00	68.00
5	8.00	10.00	15	28.00	30.00	25	48.00	50.00	35	68.00	70.00
6	10.00	12.00	16	30.00	32.00	26	50.00	52.00	36	70.00	72.00
7	12.00	14.00	17	32.00	34.00	27	52.00	54.00	37	72.00	74.00
8	14.00	16.00	18	34.00	36.00	28	54.00	56.00	38	74.00	76.00
9	16.00	18.00	19	36.00	38.00	29	56.00	58.00	39	76.00	78.00
10	18.00	20.00	20	38.00	40.00	30	58.00	60.00	40	78.00	80.00

UNLESS OTHERWISE SPECIFIED TOLERANCE		DRAWING NAME:		2. 0FH 2xnPin H4.3 DIP	
X : $\pm 0.3$	X° : $\pm 5^\circ$	SIZE	A4	SCALE	N:1
X.X : $\pm 0.2$	X.X° : $\pm 1^\circ$	REV	A	UNIT	mm
X.XX : $\pm 0.1$	X.XX° : $\pm 0.5^\circ$	PROJECT	HC-PM200-4.3H-2x4PZ		PAGE 1/1
CHECKED: LI BEI LIN 12/03/07	CHECKED: / /	APPROVED: / /			