



Description

The IPD90N03S4L-03 uses advanced trench technology to provide excellent $R_{DS(ON)}$, low gate charge and operation with gate voltages as low as 4.5V. This device is suitable for use as a Battery protection or in other Switching application.



TO-252-2L

General Features

$V_{DS} = 30V$ $I_D = 160A$


$R_{DS(ON)} < 2.3 m\Omega @ V_{GS}=10V$

Application

Battery protection

Load switch

Uninterruptible power supply



Package Marking and Ordering Information

| Product ID | Pack | Brand | Qty(PCS) |
|----------------|-----------|------------|----------|
| IPD90N03S4L-03 | TO-252-2L | HXY MOSFET | 2500 |

Absolute Maximum Ratings ($T_C=25^\circ C$ unless otherwise noted)

| Symbol | Parameter | Rating | Units |
|-------------------------|--|------------|--------------|
| V_{DS} | Drain-Source Voltage | 30 | V |
| V_{GS} | Gate-Source Voltage | ± 20 | V |
| $I_D @ T_C=25^\circ C$ | Continuous Drain Current, $V_{GS} @ 10V^1$ | 160 | A |
| $I_D @ T_C=100^\circ C$ | Continuous Drain Current, $V_{GS} @ 10V^1$ | 80 | A |
| I_{DM} | Pulsed Drain Current ² | 450 | A |
| EAS | Single Pulse Avalanche Energy ³ | 580 | mJ |
| I_{AS} | Avalanche Current | 60 | A |
| $P_D @ T_C=25^\circ C$ | Total Power Dissipation ⁴ | 87 | W |
| T_{STG} | Storage Temperature Range | -55 to 150 | $^\circ C$ |
| T_J | Operating Junction Temperature Range | -55 to 150 | $^\circ C$ |
| $R_{\theta JA}$ | Thermal Resistance Junction-Ambient 1 | 62 | $^\circ C/W$ |
| $R_{\theta JC}$ | Thermal Resistance Junction-Case1 | 2.1 | $^\circ C/W$ |



Electrical characteristic ($T_J = 25^\circ\text{C}$ unless otherwise specified)

| Symbol | Parameter | Test conditions | Min. | Typ. | Max. | Unit |
|--------------------------------|---|---|------|------|------|---------------------|
| BV_{DSS} | Drain to source breakdown voltage | $V_{GS}=0V, I_D=250\mu A$ | 30 | | | V |
| $\Delta BV_{DSS} / \Delta T_J$ | Breakdown voltage temperature coefficient | $I_D=250\mu A$, referenced to 25°C | | 0.02 | | V/ $^\circ\text{C}$ |
| I_{DSS} | Drain to source leakage current | $V_{DS}=30V, V_{GS}=0V$ | | | 1 | μA |
| | | $V_{DS}=24V, T_J=125^\circ\text{C}$ | | | 50 | μA |
| I_{GSS} | Gate to source leakage current, forward | $V_{GS}=20V, V_{DS}=0V$ | | | 100 | nA |
| | Gate to source leakage current, reverse | $V_{GS}=-20V, V_{DS}=0V$ | | | -100 | nA |
| $V_{GS(TH)}$ | Gate threshold voltage | $V_{DS}=V_{GS}, I_D=250\mu A$ | 1.2 | | 2.4 | V |
| $R_{DS(ON)}$ | Drain to source on state resistance | $V_{GS}=4.5V, I_D=30A, T_J=25^\circ\text{C}$ | | 2.2 | 4.8 | m Ω |
| | | $V_{GS}=10V, I_D=30A, T_J=25^\circ\text{C}$ | | 1.6 | 2.3 | m Ω |
| | | $V_{GS}=10V, I_D=30A, T_J=125^\circ\text{C}$ | | 2.5 | | m Ω |
| G_{fs} | Forward transconductance | $V_{DS}=5V, I_D=30A$ | | 73 | | S |
| C_{iss} | Input capacitance | | | 6272 | | pF |
| C_{oss} | Output capacitance | $V_{GS}=0V, V_{DS}=15V, f=1\text{MHz}$ | | 1022 | | |
| C_{rss} | Reverse transfer capacitance | | | 718 | | |
| $t_{d(on)}$ | Turn on delay time | | | 20 | | ns |
| t_r | Rising time | $V_{DS}=15V, I_D=30A, R_G=4.7\Omega, V_{GS}=10V$ | | 58 | | |
| $t_{d(off)}$ | Turn off delay time | (note 4,5) | | 158 | | |
| t_f | Fall time | | | 77 | | |
| Q_g | Total gate charge | $V_{DS}=24V, V_{GS}=10V, I_D=30A, I_G=5\text{mA}$ | | 143 | | nC |
| Q_{gs} | Gate-source charge | (note 4,5) | | 17 | | |
| Q_{gd} | Gate-drain charge | | | 43 | | |
| R_g | Gate resistance | $V_{DS}=0V$, Scan F mode | | 4.2 | | Ω |
| I_S | Continuous source current | Integral reverse p-n Junction diode in the MOSFET | | | 110 | A |
| I_{SM} | Pulsed source current | | | | 440 | A |
| V_{SD} | Diode forward voltage drop. | $I_S=45A, V_{GS}=0V$ | | | 1.4 | V |
| t_{rr} | Reverse recovery time | $I_S=30A, V_{GS}=0V,$ | | 26 | | ns |
| Q_{rr} | Reverse recovery charge | $dI_F/dt=100A/\mu s$ | | 10 | | nC |

※. Notes

1. Repeattive rating : pulse width limited by junction temperature.
2. $L=0.5\text{mH}, I_{AS}=48A, V_{DD}=30V, R_G=25\Omega$, Starting $T_J=25^\circ\text{C}$
3. $I_{SD} \leq 30A, di/dt = 100A/\mu s, V_{DD} \leq BV_{DSS}$, Starting $T_J=25^\circ\text{C}$
4. Pulse Test : Pulse Width $\leq 300\mu s$, duty cycle $\leq 2\%$.



Typical Characteristics




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance Variation vs Drain Current and Gate Voltage




Figure 4. Body Diode Forward Voltage Variation vs Source Current




Figure 5. Capacitance Characteristics




Figure 6. Gate Charge Characteristics




Figure 7. Vds Drain-Source Voltage vs Gate Voltage




Figure 8. On-Resistance vs Gate Voltage




Figure 9. Maximum Safe Operating Area




Figure 10. Maximum Continuous Drain Current vs Temperature






Figure 11. Transient Thermal Response Curve





TestCircuit



Gate Charge Test Circuit & Waveform



Resistive Switching Test Circuit & Waveforms




Unclamped Inductive Switching Test Circuit & Waveforms





TO-252-2L Package Information



| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|---------------------------|--------|----------------------|-------|
| | Min. | Max. | Min. | Max. |
| A | 2.200 | 2.400 | 0.087 | 0.094 |
| A1 | 0.000 | 0.127 | 0.000 | 0.005 |
| b | 0.660 | 0.860 | 0.026 | 0.034 |
| c | 0.460 | 0.580 | 0.018 | 0.023 |
| D | 6.500 | 6.700 | 0.256 | 0.264 |
| D1 | 5.100 | 5.460 | 0.201 | 0.215 |
| D2 | 0.483 TYP. | | 0.190 TYP. | |
| E | 6.000 | 6.200 | 0.236 | 0.244 |
| e | 2.186 | 2.386 | 0.086 | 0.094 |
| L | 9.800 | 10.400 | 0.386 | 0.409 |
| L1 | 2.900 TYP. | | 0.114 TYP. | |
| L2 | 1.400 | 1.700 | 0.055 | 0.067 |
| L3 | 1.600 TYP. | | 0.063 TYP. | |
| L4 | 0.600 | 1.000 | 0.024 | 0.039 |
| phi | 1.100 | 1.300 | 0.043 | 0.051 |
| theta | 0° | 8° | 0° | 8° |
| h | 0.000 | 0.300 | 0.000 | 0.012 |
| V | 5.350 TYP. | | 0.211 TYP. | |



Attention

- Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.
- HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.
- Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.