



NOTES:  
 1. Material:  
 Insulator: PBT+30%GF, UL 94V-0,  
 Color: Black or Grey.  
 2. Temperature Range: -25°C to +85°C

PART NO.  
 Z-B810 \*\* 210000 \* 1  
 No. of Positions 10~64  
 Color  
 0=Black  
 8=Grey  
 9=White



UNITS: <input checked="" type="checkbox"/> mm <input type="checkbox"/> inch TOLERANCE LEVEL (UNLESS OTHERWISE SPECIFIED) A (ISO2768-m) B RANGE mm DEFINED TOLERANCE 0 ~ 6 ± 0.1 .X ± 0.38 6 ~ 30 ± 0.2 .XX ± 0.25 30 ~ 120 ± 0.3 .XXX ± 0.08 120 ~ 400 ± 0.5 ANGLE X° ± 1° ANGLE X° ± 2°			NAME: 2.54MM CRIMP TYPE IDC HOUSING PART NO: Z-B810**210000*1 APPD: Peter 廖小瓊 2023/11/16 CHKD: Peter 廖小瓊 2023/11/16 DRAW: Lily 袁麗星 2023/11/15 DESIGN: Lily 袁麗星 2023/11/15		nexttron NEXTRONICS ENGINEERING CORP. TITLE: CUSTOMER DWG. DWG NO: 010-0000-F48									
<table border="1"> <tr> <th>REV.</th> <th>DESCRIPTION</th> <th>DATE</th> </tr> <tr> <td>A2</td> <td>UPGRADE VERSION ECR-23042</td> <td>2023/10/18</td> </tr> <tr> <td>A1</td> <td>MODIFY</td> <td>2018/08/17</td> </tr> </table>	REV.	DESCRIPTION	DATE	A2	UPGRADE VERSION ECR-23042	2023/10/18	A1	MODIFY	2018/08/17					
REV.	DESCRIPTION	DATE												
A2	UPGRADE VERSION ECR-23042	2023/10/18												
A1	MODIFY	2018/08/17												

CONFIDENTIAL: THIS DOCUMENT CONTAINED THE INFORMATION IS PROPRIETARY AND CONFIDENTIAL TO Nexttronics Engineering Corp.  
 NO PERSON IS ALLOWED TO USE COPY, PUBLISH OR OTHERWISE DISCLOSE THE INFORMATION TO OTHERS, UNLESS BY THE PRIOR  
 WRITTEN EXPRESS AUTHORIZATION OF Nexttronics Engineering Corp. (C)COPYRIGHT- Nexttronics Engineering Corp.

USE SHOWN DIMENSIONS  
 DO NOT SCALE DRAWING