

# 承認書

## SPECIFICATION FOR APPROVAL

客戶名稱  
CUSTOMER

客戶料號  
CUS. P/N

尺寸  
DIMENSION




**CUF9-230C**

編號  
SERIAL NO.

NO. CF1025412658

日期  
DATE

2024年5月8日

出圖 DRAWING		
發行 ISSUE	復核 CHECKED	核準 APPROVAL
		
DATE: 2024/5/8		

承認 CUSTOMER APPROVAL



東莞市燦峰電子有限公司  
DONG GUAN CITY CAN FENG ELETRONICS CO., LTD

網址: www.canfengele.com E-mail: canfengdianzi@163.com

聯系方式

王小姐: 13556646144

洪先生: 13809826886






# 承認書

## SPECIFICATION FOR APPROVAL

規格 ITEM	CUF9-230C		編號 SERIAL NO.	NO. CF1025412658	
1. 形狀尺寸 (單位mm) ; SHAPE & DIMENSION(unit/mm);  			A	44.50 ± 0.5	mm
			B	40.50 ± 0.5	mm
			C	23.00 ± 0.8	mm
			D	17.00 ± 0.5	mm
			E		
			F		
			G		
			2. 電器性能檢測項目 ELECTTRONICAL REQUIREMENTS;		
<input type="checkbox"/> L		TEST FREQ		測試儀器 TESTING INSTRUMENTS	
<input type="checkbox"/> Q		TEST FREQ	KHZ MHZ	1. Q-METER: <input type="checkbox"/> HP-4342A <input type="checkbox"/> MQ-172	
<input checked="" type="checkbox"/> Z	Z1=45 Ω MIN 25MHZ	KHZ	Z3=	KHZ MHZ	2. LCR-METER: <input type="checkbox"/> TH2826
	Z2=90 Ω MIN 100MHZ	KHZ	Z4=	KHZ MHZ	3. IMPEDANCE ANALYZER: <input type="checkbox"/> HP-4191A <input type="checkbox"/> Agilent 16092A <input checked="" type="checkbox"/> HP4286A
溫度 TEMP	25±5℃	濕度 HUMIDITY	60±8%		4. L-METER: <input type="checkbox"/> TH-2775B
繞線: WINDING	Z: Φ0.5*100L(mm)*0.5TS			5. DIGITAL MINI-OHM METER: VP2941A	
3. 外觀 THE LIMIT OF BREAKACE:					
項目 Item			標準值 Standard Value		
一處缺陷的面积 Area of a breakage			≤1mm <sup>2</sup>		
总缺陷面积 ALL area of the breakage			≤2mm <sup>2</sup>		
缺陷深度 The depth of the breakge			≤0.4mm		
毛刺长度 The length of burr			≤0.2mm		
4. 包裝 PACKAGING:  內包裝采用泡塑盒, 外包裝采用紙箱, 每箱產品外面都蓋上标签 (包括品名、數量、批號、檢驗員)。 Inner packing gdopts foam plastics box, outer packing adopts carton and each carton should have a qualified label outside(include the variey, quantity, batch number and inspector).					

# 檢 測 數 據

## INSPECTION DATA

規 格 ITEM	CUF9-230C					編 號 SERIAL NO.	NO. CF1025412658					
1. 形壯尺寸(单位/毫米): SHAPE & DIMENSION(unit/mm):  							<input type="checkbox"/> L					
							<input type="checkbox"/> Q					KHZ MHZ
							<input checked="" type="checkbox"/> Z	Z1=45 Ω MIN	KHZ	Z1=	KHZ	
								25MHZ		Z2=90 Ω MIN	KHZ	Z4=
								100MHZ				
							溫 度 TEMP	25±5°C	濕 度 HUMIDITY	60±8%		
							繞 線: WINDING	Z: Φ 0.5*100L(mm)*0.5TS				
項 目 ITEM	電 氣 性 能 ELECTRONIC CHARACTERISTICS						尺 寸 DIMENSION(unit:mm)					
	Q	L(μH)	Z1(Ω)	Z2(Ω)	Z3(Ω)	Z4(Ω)	A	B	C	D	E	F
			45	90			44.5	40.5	23	17		
+			/	/			0.5	0.5	0.8	0.5		
-			0	0			0.5	0.5	0.8	0.5		
1			53.6	104.5			44.46	40.62	23.05	16.95		
2			55.1	103.8			44.32	40.54	23.07	17.03		
3			53.9	107.8			44.60	40.66	23.02	16.98		
4			53.2	106.8			44.36	40.55	23.12	16.97		
5			55.7	109.5			44.27	40.66	22.98	17.00		
6			56.2	106.5			44.69	40.59	22.93	16.93		
7			56.4	107.5			44.59	40.63	23.12	17.02		
8			57.2	106.2			44.80	40.66	23.12	16.98		
9			55.6	105.4			44.23	40.56	22.98	16.98		
10			54.8	103.5			44.54	40.47	23.00	16.86		
X			55.2	106.4			44.49	40.59	23.04	16.97		
Y/N			Y	Y			Y	Y	Y	Y		
2. 測試儀器 TESTING INSTRUMENTS HP4286A  							檢 測 INSPECTION	復 核 CHECK	確 認 APPROVAL			
												


# 阻抗 - 频率曲线

IMPEDANCE V.S.FREQUENCY ( Z-Y )

规格 ITEM	CUF9-230C	编号 SERIAL NO.	NO. CF1025412658
------------	-----------	------------------	------------------

材质特性：  
MATERIAL CHARACTERISTICS

材料 牌号 Material	初始磁 导率 Initial Permeability	比损耗因子 Relative Loss Factor	比温度系数 Relative Temperature Coefficient	饱和磁通密度 Saturation Magnetic Flux Density	剩磁 Reman- ence	矫顽力 Coercivi- ty	居里温度 Curie Tempera- ture	电阻率 Electric Resistiv- ity	使用范围 Applied Frequency Range	密度 Densit- y
Unit symbol	$\mu_i$ $\pm 20\%$	$\tan \delta / \mu_i$ $\times 10^{-6}$	$\alpha \mu_i \gamma$ $\times 10^{-6}$	Bs (MT)	Br (MT)	HC (A/m)	Tc (°C)	$\rho$ ( $\Omega \cdot m$ )	F Mhz	d g/cm <sup>3</sup>
F9	850	16(0.1MHz)	5-10	350(1600A/m)	200	20	>110	>10 <sup>5</sup>	0.1-1.5	4.8



测试条件； TESTING CONDITION;	检测 INSPECTION	复核 CHECK	确认 APPROVAL
1. 测试仪器： HP 4286A Testing Equipment:			
2. 测试频率区间： 1MHZ-1000MHZ Testing Frequency Range:			
3. 测试绕组： $\Phi 0.5 \times 100L(mm) \times 0.5TS$ Testing Coil Specification:			