


PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 2A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~ +85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer Nylon66 UL94-V0(2)
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-PH-2A-G	6.00	2.00
3	HC-PH-3A-G	8.00	4.00
4	HC-PH-4A-G	10.00	6.00
5	HC-PH-5A-G	12.00	8.00
6	HC-PH-6A-G	14.00	10.00
7	HC-PH-7A-G	16.00	12.00
8	HC-PH-8A-G	18.00	14.00
9	HC-PH-9A-G	20.00	16.00
10	HC-PH-10A-G	22.00	18.00
11	HC-PH-11A-G	24.00	20.00
12	HC-PH-12A-G	26.00	22.00
13	HC-PH-13A-G	28.00	24.00
14	HC-PH-14A-G	30.00	26.00
15	HC-PH-15A-G	32.00	28.00
16	HC-PH-16A-G	34.00	30.00

Ordering Information



			GENREL TOLERANCE		制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审核 CHECK					
			X.X	±0.30	批准 APPROVAL		产品名称 TITLE	PH (2.0) 直针 增强	版本 REV.	A
1			初版发行				产品料号 PART NO.	HC-PH-NA-G	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°	投影 Projection		材料 MATERIAL		页次 SHEET	1/1