

承認書

SPECIFICATION FOR APPROVAL

客戶名稱
CUSTOMER

客戶料號
CUS. P/N

尺寸
DIMENSION




CFS9-23.5x6.5x15x19.5-1.4

編號
SERIAL NO.

NO. CF1025411628

日期
DATE

2024年5月8日

出圖 DRAWING		
發行 ISSUE	復核 CHECKED	核準 APPROVAL
		
DATE: 2024/5/8		

承認 CUSTOMER APPROVAL



东莞市灿峰电子有限公司

DONG GUAN CITY CAN FENG ELETRONICS CO., LTD

网址: www.canfengele.com E-mail: canfengdianzi@163.com


联系方式

王小姐: 13809826886

洪先生: 13809826886






承認書

SPECIFICATION FOR APPROVAL

規格 ITEM	CFS9-23.5x6.5x15x19.5-1.4	編號 SERIAL NO.	NO. CF1025411628
1. 形狀尺寸 (單位mm) ; SHAPE & DIMENSION(unit/mm);		A	23.50 ± 0.6 mm
		B	6.50 ± 0.5 mm
		C	15.00 ± 0.6 mm
		D	19.50 ± 0.5 mm
		E	1.40 ± 0.5 mm
		F	
		G	
		2. 電器性能檢測項目 ELECTTRONICAL REQUIREMENTS;	
<input type="checkbox"/> L		TEST FREQ	測試儀器 TESTING INSTRUMENTS
<input type="checkbox"/> Q		TEST FREQ	KHZ MHZ 1. Q-METER: <input type="checkbox"/> HP-4342A <input type="checkbox"/> MQ-172
<input checked="" type="checkbox"/> Z	Z1=30 Ω MIN 25MHZ	KHZ	Z3= KHZ MHZ 2. LCR-METER: <input type="checkbox"/> TH2826
	Z2=100 Ω MIN 100MHZ	KHZ	Z4= KHZ MHZ 3. IMPEDANCE ANALYZER: <input checked="" type="checkbox"/> HP-4191A <input type="checkbox"/> Agilent 16194A <input type="checkbox"/> E4991A
溫度 TEMP	25±5℃	濕度 HUMIDITY	60±8%
繞線: WINDING	Z: Φ0.5*100L(mm)*0.5TS		4. L-METER: <input type="checkbox"/> TH-2775B 5. DIGITAL MINI-OHM METER: VP2941A
3. 外觀 THE LIMIT OF BREAKAGE:			
項目 Item		標準值 Standard Value	
一處缺陷的面积 Area of a breakage		≤1mm ²	
总缺陷面积 ALL area of the breakage		≤2mm ²	
缺陷深度 The depth of the breakge		≤0.4mm	
毛刺长度 The length of burr		≤0.2mm	
4. 包裝 PACKAGING:			
內包裝采用泡塑盒, 外包裝采用紙箱, 每箱產品外面都蓋上标签 (包括品名、數量、批號、檢驗員)。 Inner packing gdopts foam plastics box, outer packing adopts carton and each carton should have a qualified label outside(include the variey, quantity, batch number and inspector).			

檢 測 數 據

INSPECTION DATA

規 格 ITEM	CFS9-23.5x6.5x15x19.5-1.4					編 號 SERIAL NO.	NO. CF1025411628						
1. 形狀尺寸(单位/毫米): SHAPE & DIMENSION(unit/mm):							<input type="checkbox"/> L						
							<input type="checkbox"/> Q				KHZ MHZ		
							<input checked="" type="checkbox"/> Z		Z1=30 Ω MIN KHZ 25MHZ		Z1= KHZ MHZ		
									Z2=100 Ω MIN KHZ 100MHZ		Z4= KHZ MHZ		
							溫 度 TEMP		25±5°C		濕 度 HUMIDITY 60±8%		
							繞 線: WINDING		Z: Φ 0.5*100L(mm)*0.5TS				
項 目 ITEM	电 气 性 能 ELECTRONIC CHARACTERISTICS						尺 寸 DIMENSION(unit:mm)						
	Q	L(μH)	Z1(Ω)	Z2(Ω)	Z3(Ω)	Z4(Ω)	A	B	C	D	E	F	
			30	100			23.5	6.5	15	19.5	1.4		
+			/	/			0.6	0.5	0.6	0.5	0.5		
-			0	0			0.6	0.5	0.6	0.5	0.5		
1			46.1	139.0			23.48	6.52	15.03	19.44	1.40		
2			46.2	138.0			23.41	6.51	15.05	19.54	1.40		
3			46.4	135.0			23.45	6.53	15.01	19.48	1.40		
4			47.7	133.0			23.41	6.58	15.08	19.46	1.40		
5			46.6	139.7			23.36	6.50	14.98	19.50	1.40		
6			47.9	135.9			23.50	6.59	14.95	19.42	1.40		
7			46.4	139.6			23.55	6.51	15.08	19.52	1.41		
8			49.3	140.4			23.43	6.53	15.08	19.48	1.40		
9			46.3	138.6			23.48	6.55	14.98	19.48	1.41		
10			47.9	139.4			23.52	6.57	15.00	19.34	1.40		
X			47.1	137.9			23.46	6.54	15.02	19.47	1.40		
Y/N			Y	Y			Y	Y	Y	Y	Y		
2. 測試儀器 TESTING INSTRUMENTS HP 4191A							檢 測 INSPECTION		復 核 CHECK		確 認 APPROVAL		
													


阻抗 - 頻率曲綫

IMPEDANCE V.S.FREQUENCY (Z-Y)

規格 ITEM	CFS9-23.5x6.5x15x19.5-1.4	編號 SERIAL NO.	NO. CF1025411628
------------	---------------------------	------------------	------------------

材质特性：
MATERIAL CHARACTERISTICS

材料 牌号 Material	初始磁 导率 Initial Permeability	比损耗因子 Relative Loss Factor	比温度系数 Relative Temperature Coefficient	饱和磁通密度 Saturation Magnetic Flux Density	剩磁 Reman- ence	矫顽力 Coercivi- ty	居里温度 Curie Tempera- ture	电阻率 Electric Resistiv- ity	使用范围 Applied Frequency Range	密度 Densit- y
Unit symbol	μ_i $\pm 20\%$	$\tan \delta / \mu_i$ $\times 10^{-6}$	$\alpha \mu_i \gamma$ $\times 10^{-6}$	Bs (MT)	Br (MT)	HC (A/m)	Tc (°C)	ρ ($\Omega \cdot m$)	F Mhz	d g/cm ³
F9	850	16(0.1MHz)	5-10	350(1600A/m)	200	20	>110	>10 ⁵	0.1-1.5	4.6



测试条件； TESTING CONDITION;	檢 測 INSPECTION	復 核 CHECK	确 認 APPROVAL
1. 测试仪器： HP 4191 A Testing Equipment:			
2. 测试频率区间： 1MHZ-1000MHZ Testing Frequency Range:			
3. 测试绕组： Φ0.5*100L(mm)*0.5TS Testing Coil Specification:			