ISOLATION TRANSFORMERS FOR BATTERY MANAGEMENT SYSTEMS



HR601233E

Electrical Specification @25°C

RoHS Compliant (Pb Free)

Operating Temperature Range: −40°C ~ +125°C

Isolation: 4300VDC 1mA 60S (Primary to Secondary)
OCL: 150uH Minimum, 450uH Maximum @100KHz 100mV

Turns Ratio: 1 : 1 $\pm 2\%$ (Primary : Secondary)

PRI DC Resistance: 0.45 Ohms Maximum SEC DC Resistance: 0.85 Ohms Maximum

PRI Leakage Inductance: 0.5uH Maximum @100KHz 100mV SEC Shorted

Insertion Loss: -0.25dB Maximum @4MHz

Return Loss: -20dB Minimum @4MHz (Z OUT =100 OHM ± 1)

Crosstalk: -50dB Minimum @4MHz


CMRR: -35dB Minimum @1MHz ~ 10 MHz / -20dB Minimum @10MHz ~ 1000 MHz

Insulation Resistance: $400 \text{M}\,\Omega$ Minimum Creepage Distance: 10 mm Minimum


Design Construction: Functional insulation

Qualification: PER AEC-Q200 Working Voltage: 1600VDC

Schematics



Mechanical Dimensions



Dimensions in mm

Unless otherwise specified, Tol.: .xx ± 0.25

REV.: 02 1 of 1