
RD*G SERIES SPACE-SAVING D-SUBMINIATURE


General

The "RD*G" Series Right-angled D-Subminiature connectors are specially developed to answer the needs for smaller and lighter equipment such as personal computers peripherals and workstations. The PCB mounting section has been reduced in size while the mating section maintains the same configuration as the conventional models. Female 9, 15 and 25 position sizes sre available.



Features

- 35% Space-saving is achieved in terms of depth and mounting area as compared to the conventional models (HIROSE's RD %D)
- (2) Weight is approximately 10% less than conventional models.
- (3) Full interchangeability in terms of mating with conventional D-Subminiature connectors. The mating section meets the international standard.
- (4) For smoother insertion and withdrawal, reliable partly gold-plated tulip-shaped contacts are used (same as the conventional models).
- (5) The lock pin grounding system which solders directly to the substrate eliminates troublesome hold down hardware.
- (6) Since they are fixed to the insulator (caulked), the metallic shells and lock pins do not become loose even when the lock screws are removed. This has improved assembly productivity of the units.



- (7) Two lock pin lengths for substrate thickness: t-1.2mm (0.05") and t-1.6mm (0.062") are available.
- (8) These are two Dip post lengths of 3.5mm and 2.8mm.
- (9) The new connectors are suitable for robotic insertion.
- (10) UL94V-0 insulator material offers excellent heat resistant and chemical resistant capability.
- (11) Metal shell structure offers improved grounding and EMI immunity.

Application

Electronic equipment such as personal computers, peripherals, workstations, measuring instruments, communications equipment, FA and control devices.


Electrical and Environmental

Electrical performance				
Current capacity	3A			
Voltage rating	350V AC			
Insulation resistance	5,000 ohms min. at 500V DC			
Contact resistance	25m ohms max at 100mA DC			
Withstanding voltage	1,250V AC r.m.s. for one minute			

Materials


	Materials				
Shell	Shell Copper Nickel plating				
Insulator	Insulator PBT Black (UL94V-0)				
Contact	tact Copper alloy Nickel plating + selective gold plating				
Lock pin Copper alloy Tin plating		Tin plating			

Ordering Informations



- (1) Series name: D Sub-right angled
- (2) Shell size: E (9), A (15), B (25)
- (3) Model type: G=Space saving type
- (4) Dip post length: Blank=3.5mm (.138") 1=2.8mm (.110")
- (5) No of contacts: 9, 15, 25
- (6) Connector style: S=Female
- (7) Mounting style: E=Grounding lock pin
- (8) Applicable board thickness: 1=(t1.6mm) 1.6mm (0.62["]), 2=(t1.2mm) 1.2mm(0.50["])
- (9) Specification contents(50): Nickel plating


Female Connector



							Uı	nit: mm
HRS No	Part No.	No. of Contacts	А	В	С	D	Applicable substrate thickness	RoHS
CL211-5200-7-50	RDEG-9SE1 (50)	9	30.81	24.99	16.34		1.6	
CL211-5201-0-50	RDEG-9SE2 (50)	9	30.81	1 24.99	9 10.54		1.2	1
CL211-5204-8-50	RDAG-15SE1 (50)	15	15 00.14 00.00	24.66	3.5	1.6		
CL211-5205-0-50	RDAG-15SE2 (50)	15	39.14	33.32	24.00		1.2	
CL211-5206-3-50	RDBG-25SE1 (50)	- 25 53.04	52.04	47.04 38.3	4 38.38		1.6	- YES
CL211-5207-6-50	RDBG-25SE2 (50)		33.04		30.30		1.2	
CL211-5250-5-50	RDEG1-9SE1 (50)	0	9 30.81 2	24.99	24.99 16.34	2.8	1.6	
CL211-5251-8-50	RDEG1-9SE2 (50)	9					1.2	
CL211-5254-6-50	RDAG1-15SE1 (50)	15	39.14	33.32	24.66		1.6	
CL211-5255-9-50	RDAG1-15SE2 (50)		15	39.14	33.32	24.00	2.0	1.2
CL211-5256-1-50	RDBG1-25SE1 (50)	25	53.04	47.04	38.38		1.6	
CL211-5257-4-50	RDBG1-25SE2 (50)	20	55.04	47.04	30.30		1.2	

Jul.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.

Locking Screw




	HRS No	Part No.	Female thread size	No. of washers	Applicable panel thickness	Packaging unit (per bag)	RoHS
	CL211-5180-1-01	RDG-LNA (01)		0	1.6~2.0		
	CL211-5181-4-01	RDG-LNA-W1 (01)	$\mathrm{M2.6} \times 0.45$	1	0.8~1.2	100pieces	
ſ	CL211-5182-7-01	RDG-LNA-W2 (01)		2	0~0.4		YES
	CL211-5183-0-01	RDG-LNA (4-40) (01)		0	$1.6 \sim 2.0$		ILS
	CL211-5184-2-01	RDG-LNA (4-40)-W1 (01)	No.4-40UNC	1	0.8~1.2	100pieces	
	CL211-5185-5-01	RDG-LNA (4-40)-W2 (01)		2	0~0.4		

*All models are nickel-plated

Panel Mounting Dimensions

For hexagon locking screws




	U	nit: mm
Shell Size	а	b
Е	24.99	20.2
А	33.32	28.6
В	47.04	42.3


PC Board Layout (mm)

- RDEG-9SE1 (50) (Substrate thickness t=1.6)
- RDEG1-9SE1 (50) (Substrate thickness t=1.6)
- RDEG-9SE2 (50) (Substrate thickness t=1.2)
- RDEG1-9SE2 (50) (Substrate thickness t=1.2)

 $9-\phi1$ 2.74 2.74 1.37 4.11 24.99Edge of substrate (Open side of connector)



• RDEG1-15SE2 (50) (Substrate thickness t=1.2)



- RDEG-25SE1 (50) (Substrate thickness t=1.6)
- RDEG1-25SE1 (50) (Substrate thickness t=1.6)
- RDEG-25SE2 (50) (Substrate thickness t=1.2)
- RDEG1-25SE2 (50) (Substrate thickness t=1.2)

