

SILICON BRIDGE RECTIFIERS

Features

- ◆ The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- ◆ Ideal for printed circuit boards
- ◆ Low reverse leakage
- ◆ High forward surge current capability
- ◆ High temperature soldering guaranteed: 260°C/10 seconds, 5 lbs. (2.3kg) tension

Mechanical Data

Case : JEDEC KBPC-25 Molded plastic body




Terminals : Solder plated, solderable per MIL-STD-750, Method 2026

Polarity : Polarity symbol marking on body

Mounting Position : Any

Weight : 1.02 ounce, 29 grams

KBPC-25



Dimensions in inches and (millimeters)

Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter	SYMBOLS	MDD KBPC35005	MDD KBPC3501	MDD KBPC3502	MDD KBPC3504	MDD KBPC3506	MDD KBPC3508	MDD KBPC3510	MDD KBPC3512	UNITS
Marking Code										
Maximum repetitive peak reverse voltage	V _{RRM}	50	100	200	400	600	800	1000	1200	V
Maximum RMS voltage	V _{RMS}	30	70	140	280	420	560	700	840	V
Maximum DC blocking voltage	V _{DC}	50	100	200	400	600	800	1000	1200	V
Maximum average forward output rectified current at T _c =55°C (Note 1)	I _(AV)									A
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I _{FSM}									A
Rating for Fusing(t<8.3ms)	I ² t									A ² s
Maximum instantaneous forward voltage drop per bridge element at 17.5A	V _F									V
Maximum DC reverse current T _A =25°C at rated DC blocking voltage T _A =100°C	I _R									µA
Dielectric Strength, Terminals to case, AC 1 minute	V _{dis}									mA
Typical Thermal Resistance (Note 2)	R _{θJC}									°C/W
Operating junction temperature range	T _J									°C
storage temperature range	T _{STG}									°C

NOTES:

1. Unit mounted on 9" x 3.5" x 4.6" thick(23cmx9cmx11.8cmcm)Al.plate.
2. Between junction and case, With heatsink

Ratings And Characteristic Curves

FIG1:Io-Tc Curve




FIG2:Surge Forward Current Capability




FIG3:Instantaneous Forward Voltage





FIG4:Typical Reverse Characteristics



The curve above is for reference only.