

### **SOT-23 Plastic-Encapsulate ESD Protection Diodes**

### **DESCRIPTION**

The SMxxOC Series is designed for applications requiring transient overvoltage protection capability. They are intended for use in voltage and ESD sensitive equipment such as computers, printers, business machines, communication systems, medical equipment and other applications. These devices are ideal for situations where board space is at a premium.

This series has been specifically designed to protect sensitive components which are connected to power, data and transmission lines from overvoltage caused by ESD(electrostatic discharge), CDE (Cable Discharge Events), and EFT (electrical fast transients).


### **Features**

- ♦ 130 Watts Peak Pulse Power per (8/20µs)
- ◆ IEC61000-4-2 (ESD) ±15kV (air), ±8kV (contact)
- ◆ IEC61000-4-4 (EFT) 40A (5/50ns)
- Protects two bidirectional line
- Low clamping voltage
- ◆ Low leakage current
- Working voltages: 5.0V, 12V
- Meets MSL 1 Requirements


# **Applications**

- Cell Phone Handsets and Accessories
- Microprocessor based equipment
- Personal Digital Assistants (PDA's)
- Notebooks, Desktops, and Servers
- Portable Instrumentation
- Networking and Telecom
- Serial and Parallel Ports
- Quick charger

## **Pin Configuration**



### **Circuit Diagram**



# **Mechanical Characteristics**

◆ Package: SOT-23

♦ Flammability Rating: UL 94V-0

◆ Terminal: Matte tin plated.

◆ High temperature soldering guaranted:
 260 ℃ /10s

Packaging: Tape and Reel

## Absolute Maximum Ratings (T<sub>A</sub>=25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	Vesd	± 30 ± 20	KV
Peak Pulse Power(tp=8/20us waveform)	P <sub>PP</sub>	130	W
Operating Temperature	T <sub>OPT</sub>	−55 to +150	°C
Storage Temperature	Tstg	-55 to +150	°C
Lead Solder Temperature – Maximum (10 Second Duration)	TL	260(10 sec.)	°C

The above data are for reference only.



# **SMxxOC Series**

# **Bi-directional TVS Diodes Array**


### Electrical Characteristics (TA=25°C unless otherwise specified)


PART NUMBER	DEVICE MARKING	V <sub>RWM</sub> (V) (max.)	V <sub>B</sub> (V) (min.)	I <sub>T</sub> (mA)	V <sub>C</sub> @1A (V) (max.)	(V (max.)		I <sub>R</sub> (μΑ) (max.)	C <sub>⊤</sub> (pF) (max.)
SM05OC	CO05	5.0	5.6	1	8.5	16.0	8	1	15
SM12OC	CO12	12.0	13.3	1	19	26.0	5	0.2	15


The above data are for reference only.




#### **ELECTRICAL CHARACTERISTICS CURVE**









The curve above is for reference only.

http://www.microdiode.com Rev:2024A2 Page :3






# **Bi-directional TVS Diodes Array**


# **Outlitne Drawing**

### SOT-23 Package Outline Dimensions



Symbol	Dimens	ions In Mi	llimeters
Syllibol	Min	Тур	Max
Α	0.89	1.00	1.40
A1	0.01	0.06	0.10
b	0.37	0.44	0.50
С	0.09	0.13	0.20
D	2.80	2.90	3.10
Е	1.20	1.30	1.60
E1	2.10	2.40	2.80
е	1.78	1.90	2.04
L	0.10		0.30
L1	0.35	0.54	0.69
θ	0°		10°

# **Suggested Pad Layout**



#### Note:


- 1. Controlling dimension:in/millimeters.
- 2. General tolerance: ±0.05mm.
- 3. The pad layout is for reference purposes only.





## **SOT-23 Tape and Reel**

#### SOT-23 Embossed Carrier Tape




#### Packaging Description:


SOT-23 parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film,adhesive laye,sealant, and anti-static sprayed agent. These reeled parts In standard option are shipped with 3,000 units per 7" or 17.8cm diameter reel. The reels are clear in color and is made of polystyrene plastic (anti-static coated).

Dimensions are in millimeter										
Pkg type         A         B         C         d         E         F         P0         P         P1         W							W			
SOT-23	3.15	2.77	1.22	Ø1.50	1.75	3.50	4.00	4.00	2.00	8.00

#### SOT-23 Tape Leader and Trailer



#### SOT-23 Reel



Dimensions are in millimeter									
Reel Option         D         D1         D2         G         H         I         W1         W2								W2	
7"Dia	Ø178.00	54.40	13.00	R78.00	R25.60	R6.50	9.50	12.30	

REEL	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)	G.W.(kg)
3000 pcs	7 Inch	45,000 pcs	203×203×195	180,000 pcs	438×438×220	