

# 规格承认书

SPECIFICATION FOR APPROVAL

客户 CUSTOMER : 适用所有

品名 PRODUCT : 水泥电阻器 (SQM)

规格 TYPE : SQM1W-20W

客户承认印 CUSTOMER APPROVED

 广东翔胜电子科技有限公司  
Guang Dong VICO Electronic Technology Co., Ltd

地址: 广东省东莞市大朗镇莞樟路大朗段746号301室  
电话: 0769--86732158 传真: 0769--86666888

一式二份 翔胜一份 客户一份

出图	业务	审核	核准
DRAWING	SALES	AUDITING	APPROVED
			

翔胜电子技术品质部

编号: SQMS2023

日期: 2023年2月22日



无卤  
(F, Cl, Br, I)


# CEMENT

## CEMENT TYPE RESISTORS (WIREWOUND&FLUTING) 水泥电阻器

CEMENT (1W. 2W. 3W. 5W. 7W. 10W. 20W)


### FEATURES 特点

- 1 LOW NOISE  
低杂音
- 2 INSULATION FULLY CAN BE USED IN P. C. B  
使用于电路板, 绝缘良好
- 4 USE FLUTING REPLACES WIREWOUND, CAN MANUFACTURE THE HIGH RESISTANCE RANGE (OVER 100)  
使用刻槽代替绕线, 可制作高阻抗电阻。
- 5 SUPPER HEAT DISSIPATION; WITHOUT ANNUAL SHIFT ON RESISTANCE VALUE.  
耐热性久, 电阻系数直承直线变化
- 6 INSTANT OVERLOAD CAPABILITY; WITHOUT ANNUAL SHIFT ON RESISTANCE VALUE.  
耐短时间过负载, 阻值长时间无变化



### CONSTRUCTION 结构图

- A CERAMIC CORE (HIGE THERMAL CONDUCTIVITY)  
高品质陶瓷棒心
- B SOLDER PLATED COPPER LEAD WIRE  
铜质导线
- C FIRE PROOF INSULATION CEMENT  
不燃性绝缘材质
- D CERAMIC CASE  
瓷质外盒
- E WIREWOUND RESISTORS OR GROOVE RESISTANCE  
绕线电阻或刻槽电阻



### TYPE DESIGNATION 品名构成

例: SQM5W-5Ω ±5%-9P

SQM	5W	5Ω	±5%	9	P
↓	↓	↓	↓	↓	↓
品名 PRODUCT CODE	额定功率 RATED POWER	阻值范围 RESISTANCE	误差值 TOLERANCE	线径	形状
SQP SQP水泥电阻	1W 10W	0Ω 1-100KΩ	±10%:K	0:0.40CU S:0.40CP	散装   P
SQM SQM水泥电阻	2W 20W		±5%:J	2:0.50CU X:0.50CP	
SQZ SQZ水泥电阻	3W		±2%:G	6:0.60CU T:0.60CP	
SQH SQH水泥电阻	5W		±1%:F	9:0.70CU Q:0.70CP	
MPR MPR水泥电阻	7W			A:0.75CU D:0.80CP	
				C:0.80CU	

NOTE1注解: RATED VOLTAGE 额定电压 =  $\sqrt{\text{POWER RATING 额定功率} * \text{RESISTANCE VALUE 公称阻值}}$

# CEMENT

## CEMENT TYPE RESISTORS (WIREWOUND&FLUTING) 水泥电阻器

CHARACTERISTICS 特性项目	SPECIFICATIONS 规格值	TEST METHODS JIS C 5202 测试方法 JIS C 5202标准		
DC RESISTANCE 直流阻抗值	J (±5%)	RESISTANCE VALUE TEST AT ROOM TEMPERATURE 25°C 阻值测试在室温25°C		
T. C. R温度系数	0.1Ω--0.5Ω ±1000PPM/°C 0.5Ω以上 ±300PPM/°C (按阻值高低而定)	R2-R1—— X 10 <sup>6</sup> PPM/°C R1 (T2-T1) R1: RESISTANCE VALUE AT ROOM TEMPERATURE (T1) 常温 (T1) 阻抗值 R2: RESISTANCE VALUE AT ROOM TEMPERATURE +100°C (T2) 常温+100°C 阻抗值		
LOAD LIFE 负荷寿命	RESISTANCE CHANGE RATE IS ±(5%+0.05Ω) MAX WITH EVIDENCE OF RESISTOR DAMAGE. 阻抗值变化率±(5%+0.05Ω), 不可有损伤	RESISTANCE CHANGE AFTER 1000H(1.5H ON, 0.5H OFF) AT RATED VOLTAGE IN A HUMIDITY CHAMBER CONTROLLED AT 40+/-2°C AND 90-95% RELATIVE HUMIDITY. (when the test voltage exceeds the working voltage, consider using the working voltage) 温度40+/-2°C, 相对湿度90-95%于恒温恒湿箱中, 加额定直流电压测试1.5小时停止0.5小时, 连续1000小时。(当实验电压超过最高使用电压, 采用最高使用电压)		
	RESISTANCE CHANGE RATE IS (5%+0.05Ω) MAX WITH NO EVIDENCE OF RESISTOR DAMAGE. 阻抗值变化率(5%+0.05Ω) 以内, 电阻器不可有损伤	RESISTANCE CHANGE AFTER 1000H OPERATING AT RATED VOLTAGE WITH DUTY CYCLE OF 1.5H ON 0.5H OFF AT 70°C±2°C (when the test voltage exceeds the working voltage, consider using the working voltage) 温度70+/-2°C, 加额定直流电压测试1.5小时停止0.5小时, 连续1000小时 (当实验电压超过最高使用电压时, 采用最高使用电压)		
SHORT TIME OVER LOAD 短时间过负荷	±(2%+0.05Ω)	RESISTANCE CHANGE AFTER THE APPLICATION OF A POTENTIAL 2.5 T RATED VOLTAGE FOR 5 SE (when the test voltage exceeds the maximum overload, consider using the maximum overload voltage) 额定电压X2.5倍, 测试5秒 (当实验电压超过最高过负荷时, 采用最高过负荷电压)		
PULSE OVER LOAD 断续过负荷	RESISTANCE CHANGE RATE IS ±(2%+0.05Ω) MAX, WITH NO EVIDENCE OF RESISTOR DAMAGE 阻抗值变化率±(2%+0.05Ω) 以内, 电阻器不可有损伤	RESISTANCE CHANGE AFTER 10000C(1SEC ON, 25SEC OFF) AT 4T RATED VOLTAGE (AC) when the test voltage exceeds the maximum overload, consider using the maximum overload voltage) 额定电压*4倍 (交流电压), 测试1秒停止25秒, 测试10000次。(当实验电压超过最高过负荷电压, 采用最高过负荷电压)		
HUMIDITY 耐湿性	RESISTANCE CHANGE RATE IS ±(1%+0.05Ω) MAX, WITH NO EVIDENCE OF RESISTOR DAMAGE 阻抗值变化率±(1%+0.05Ω) 以内, 电阻器不可有损伤	RESISTANCE CHANGE AFTER 240H EXPOSURE IN A HUMIDITY TEST CHAMBER CONTROLLED AT 40±2°C AND 90-95% RELATIVE HUMIDITY 温度 40±2°C, 相对湿度90-95%于恒温箱中不加电压连续放置240小时		
INSULATION RESISTANCE 绝缘阻抗	>100MΩ			
ELECTRIC WITHSTANDING VOLTAGE 绝缘耐电压	NO EVIDENCE OF FLASH OVER MECHANICAL DAMAGE ARCING OR INSULATION BREAKDOWN. 浆料不可烧损, 绝缘不可破坏	ELECTRIC RESISTANCE BOTH ENDS THE CONJUNCTION LINE PUT ON THE METALS V TYPE THE SLOT, ACCORDING TO THE ELECTRIC VOLTAGE PROVISION OF THE CHARACTERISTIC WATCH 60 SECONDS INFLICTION 电阻两端导线置于金属V型槽上, 依特性表之电压规定施加60秒		
TEMPERATURE CYCLING 温度循环	RESISTANCE CHANGE RATE IS ±(1%+0.05Ω) MAX, WITH NO EVIDENCE OF RESISTOR DAMAGE. 阻抗值变化率±(1%+0.05Ω) 以内, 电阻器不可有损伤	STEP 步骤、	TEMPERATURE 温度	TIME (MIN) 放置时间
		1	-55°C±2°C	30
		2	ROOM TEMP 室温	10-15
		3	85°C±2°C	30
4	ROOM TEMP 室温	10-15		
RESISTANCE TO SOLDERING HEAT 耐热性	RESISTANCE CHANGE RATE IS ±(2%+0.05Ω) MAX, WITH NO EVIDENCE OF RESISTOR DAMAGE. 阻抗值变化率±(1%+0.05Ω) 以内, 电阻器不可有损伤	PUT THE LEAD LINE OF RESISTANCE INTO THE SOLDERING ABOUT 3.2 TO 4.8MM PLEASE TAKE IMPLEMENTATION ON THE BASIS OF THE TABLE BELOW 将电阻两端导线浸入锡炉约3.2至4.8mm依下表规定实施		
		TEMPERATURE 温度		DIP TIME 放置时间
		350°C±10°C		3±0.5 SEC
260°C±5°C		10±1.0 SEC		
EFFECT OF SOLDERING 焊接影响		±(2%+0.05Ω)		
LN COMBUSTIBILITY 不燃性	EX 16TIMES V 5MIN			


# CEMENT

CEMENT TYPE RESISTORS (WIREWOUND&FLUTING) 水泥电阻器

## POWER CHARACTERISTIC 电力特性

POWER PATED 额定功率 ITEM	1W	2W	3W	5W	7W	10W	20W	
项目								
MAX WORKING VOLTAGE 最高使用电压	300V	350V	350V	500V	500V	750V	750V	
MAX OVERLOAD VOLTAGE 最高过负荷电压	600V	700V	700V	700V	1000V	1000V	1000V	
MAX INTERMITTENCE OVER LOAD VOLTAGE 最高断续过负荷	1000V	1000V	1000V	1000V	1000V	1500V	1500V	
ELECTRIC WITHSTANDING VOLTAGE 绝缘耐电压	1000V	1000V	1000V	1000V	1000V	1000V	1000V	
RESISTANCE TOLERANCE 阻抗误差值	J (±5%)							
	WIRWOUND TYPE 绕线形式							
RANGE (OHM) 阻抗值范围	MIN	0.1 Ω	0.1 Ω	0.1 Ω	0.1 Ω	0.1 Ω	0.1 Ω	0.1 Ω
	MAX	30 Ω	50 Ω	100 Ω	100 Ω	100 Ω	200 Ω	200 Ω
	FLUTING TYPE 刻槽形式							
	MIN	31 Ω	51 Ω	101 Ω	101 Ω	101 Ω	201 Ω	501 Ω
MAX	100K	100K	100K	100K	100K	100K	100K	


SQM



# CEMENT

CEMENT TYPE RESISTORS (WIREWOUND&FLUTING) 水泥电阻器


## POWER DERATING CURVE 负载衰减曲线




NOTE注解:

- 1 RATED AMBIENT TEMPERATURE :70°C  
额定周围温度: 70°C
- 2 OPERATING TEMPERATURE RANGE:-55°C~+155°C  
使用温度范围: -55°C~+155°C
- 3 FOR RESISTORS IPERATED IN AMBIENT TEMPERATURE OVER 70°C, POWER RATING SHALL BE DERATED IN ACCORDANCE WITH THE FIGURE  
周围温度70°C以上使用时, 根据降功率曲线将减轻额定功率

## 温度上升曲线 TEMPERATURE RISE



## 热上升曲线 HEAT RISE CHART



# CEMENT

CEMENT TYPE RESISTORS (WIREWOUND&FLUTING) 水泥电阻器

SQM

TYPE 品名	DIMENSIONS (mm) 尺寸					
	W±1.0	W1±1.0	H±1.0	Φd±0.05	P±1.0	L±1.0
1W	10	5	10	0.50	5	5
2W	11	7	20	0.60	5	5
3W	12	8	25	0.60	5	5
5W	13	10	25	0.70	5	5
7W	13	10	39	0.75	5	5
10W	13	10	51	0.75	5	5
10W	16	12	35	0.75	7.5	5
20W	20	12	45	0.75	7.5	5

