

FLEXO® PET A VERSATILE BUNDLING AND PROTECTION SOLUTION • EXPANDS UP TO 150% FMVSS 302 APPROVAL

The FLEXO® Original braided from 10 mil polyethylene terephthalate (PET) monofilament yarns. The material has a wide operating temperature range, is resistant to chemical degradation, UV radiation, and abrasion. Used in electronics, automotive, marine and industria wire harnessing applications where cost efficiency and durability are critical. The unique braided construction and wide expandability allows quick and easy installation over large connectors and long runs.

SIZING CHART

Nominal	Do:## #	Min	Max	*Put-Ups		Available	Lbs/
Size	Part #	Expansion	Expansion	M	L	Colors	100'
¹ / ₁₆ "	PTN0.06	3/64"	3/32"	250′	1,000'		0.22
1/8"	PTN0.13	3/32"	1/4"	225'	1,000'		0.20
1/4"	PTN0.25	1/8"	⁷ / ₁₆ "	200'	1,000'		0.30
⁵ / ₁₆ "	PTN0.31	5/32"	¹⁵ / ₃₂ "	200'	1,000'		0.50
3/8"	PTN0.38	³ / ₁₆ "	1/2"	125'	500'		0.57
⁷ / ₁₆ "	PTN0.44	7/32"	5/8"	100'	500'		0.68
1/2"	PTN0.50	1/4"	3/4"	100'	500'		0.77
⁹ / ₁₆ "	PTN0.56	⁵ / ₁₆ "	⁷ /8"	100'	500'	more	0.81
5/8"	PTN0.63	3/8"	1"	100'	500'	than	0.95
3/4"	PTN0.75	1/2"	1¼"	75'	250'	40	1.20
1"	PTN1.00	5/8"	1%"	65'	250'		1.34
1¼"	PTN1.25	3/4"	13/4"	50'	250'		1.60
1½"	PTN1.50	1"	21/8"	40'	200'		1.96
1¾"	PTN1.75	1¼"	2¾"	30'	200'		2.45
2"	PTN2.00	1½"	3½"	50'	200'		2.60
2½"	PTN2.50	1¾"	35%"	50'	100'		3.80
3"	PTN3.00	2½"	4¾"	50'	100'		4.00
3 END CONSTRU	CTION						
1/4"	PT30.25	1/8"	3/8"	200'	1,000'	4	0.39
9 MIL CONSTRUC	CTION						
4"	PT94.00BK	4"	6½"	50'	100'	BK	3.80
PET LEAN							
3/4"	PTL0.75BK	1/2"	1¼"	75'	250'	BK	1.04
1¼"	PTL1.25BK	3/4"	1¾"	50'	250'	BK	1.19

*Put-Ups: **"M"** = Shop Spool and **"L"** = Bulk Spool



GENERAL PURPOSE

Technical Data Sheet



FEATURES

Material	Polyethylene Terephthalate
Grade	PTN
Monofilament Diameter	.010"
Drawing Number	TF001PET-WD
Cutting	Hot Knife

ABRASION

Abrasion Resistance	HIGH
Abrasion Test Machine	Taber 5150
Abrasion Test Wheel	Calibrase H-18
Abrasion Test Load	500g
Room Temperature	77°F
Humidity	72%
Two Broken Filaments	300 Test Cycles
Approx 6 Broken Filaments	500 Test Cycles
Material Destroyed	1,150 Test Cycles
Pre-Test Weight	4,547.4 mg
Post-Test Weight	4,133.9 mg
Test End Loss Of Mass Point Of Destruction	413.5 mg

PHYSICAL PROPERTIES

Monofilament Diameter (ASTM D-204)	.010"
Flammability Rating	UL94
Recommended Cutting	Hot KnifeK
Colors	40+
Wall Thickness	.025"
Tensile Strength (Yarn) (ASTM D-2256 Lbs)	7.5
Specific Gravity (ASTM D-792)	1.38
Moisture Absorption % (ASTM D-570)	.12
Hard Vacuum Data (ASTM E-595 at 10-5 torr)	
TML	.19
CVCM	.00
WVR	.16
Smoke D-Max (ASTM E-662)	56
Outgassing	Medium
Oxygen Index (ASTM D-2863)	21

CERTIFICATIONS



COLORS

40+ (see next pages)

FLAMMABILITY

Rating	UL94VO, FAR25, FMVSS-302

OPERATING TEMPERATURES

Melt Point (ASTM D-2117)	482°F / 250°C
Maximum Continuous (Mil-I-23053)	257°F / 125°C
Minimum Continuous (Mil-I-23053)	-94°F / -70°C

CHEMICAL RESISTANCE

1=No Effect 2=Little Effect 3=Affected	4=More Affected 5=Severely Affected
Aromatic Solvents	2
Aliphatic Solvents	1
Chlorinated Solvents	3
Weak Bases	1
Salts	1
Strong Bases	2
Salt Water (0-S-1926)	1
Hydraulic Fluid (MIL-H-5606)	1
Lube Oil (MIL-L-7808)	1
De-Icing Fluid (MIL-A-8243)	1
Strong Acids	3
Strong Oxidants	2
Esters/Ketones	1
UV Light	1
Petroleum	1
Fungus (ASTM G-21)	1
Halogen Free	Yes
RoHS	Yes
SVHC	None


www.TECHFLEX.com

104 Demarest Road • Sparta, NJ 07871 • 1 (833) SLEEVING • (973) 300-9242 • fax: (973) 300-9409

© 2023 Techflex® - Any unauthorized reproduction, in whole or part, in any medium whatsoever, without the express written permission of Techflex® is strictly forbidden. Techflex® product names and logos are registered trademarks of Techflex®, unless otherwise attributed. The contents and illustrations contained herein are believed to be reliable. Techflex® makes no warranties as to their accuracy or completeness and disclaims any liability in connection with their use. Techflex's® only obligations are those in standard terms of sale for these products and Techflex's will not be liable for any consequential or other damages arising due to misuse of these products or typographical errors or omissions. Users should make their own evaluation to determine the suitability of these products for their unique and specific applications.

GENERAL PURPOSE Supplemental Color Sheet

































































GENERAL PURPOSE Supplemental Color Sheet



THE POSSIBILITIES ARE ENDLESS WITH CUSTOM COMBINATION COLORS MANUFACTURED BY TECHFLEX®!



































