

6-positions Vertical Type SRRN Series

Number of wafer		1	
Poles			2
Positions			5
Changeover angle			30±3°
Changeover timing			Non shorting
Rotational torque			70±30mN·m
Actuator configuration			Round
Actuator length			L: 20mm
Operating temperature range			-30℃ to +65℃
Rating (max.)/(min.) (Resistive load)			0.15A 12V DC/50µA 3V DC
Electrical performance	Contact resistance (Initial performance/After lifetime)		50m Ω max./100m Ω max.
	Insulation resistance		100MΩ min. 500V DC
	Voltage proof		500V AC for 1 minute
Mechanical performance	Terminal strength		5N for 1 minute
performance	Actuator strength	Rotational direction	1N·m
		Push direction	100N
	Wobble of actuator (load at the tip of shaft: 5N)	Measuring position from mounting surface	15mm
		Shaft wobble (max. value)	
		Applicable mounting dimension	
Durability	Operating life without load		10,000 cycles 70m Ω max.
	Operating life with load (at max. rated		10,000 cycles 100m Ω max.


Environmental Cold $-40\pm2\%$ for 96h performance Dry heat $85\pm2\%$ for 96h

Damp heat $40\pm2\%$, 90 to 95%RH for 96h

Minimum order unit (pcs.) Japan 60


Export 240

Dimensions



Terminal Configuration

Unit: mm



Circuit Diagram

Number of poles	2	
Circuit diagram		
Dummy terminals	5-positions	7 8

- 1. Standard poles per step.
- 2. The following mark in the above table indicate a stopper with the shaft turned fully counterclockwise when viewed from direction A of the diagrams.




Packing Specifications


Number of packages (pcs.)	s 1 case / Japan	60
	1 case / export packing	240
Export package measurements (mm)		400×270×270

Shaft Style

* Round Shaft



Attached Parts



The following parts are included with the product.

Soldering Conditions

Reference for Dip Soldering

Items	Preheating temperature -		
	Preheating time	-	
Dip soldering	Soldering temperature	260±5℃	
	Duration of immersion	10±1s	
Reference for Hand Solde	ring		
Soldering temperature		350±10℃	
Soldering time		3+1/0s	

Notes are common to this series/models.

- 1. This site catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
- 2. All the axis are cutting shafts.
- 3. Please place purchase orders per minimum order unit (integer).
- 4. Products other than those listed in the above chart are also available. Please contact us for details.