


2.0(H)mm, 2.0mm-travel Type SSSS7 Series


Travel		2mm	
Actuator directions			Horizontal
Actuator length			2mm
Poles Positions		1	
		3	
Operating force			Refer to the dimensions.
Changeover timing		Non shorting	
Soldering	oldering		Reflow
Operation			Standard
Operating temperature range Rating (max.)/(min.) (Resistive load)		-40°C to +85°C	
		0.3A 4V DC/50μA 3V DC	
Electrical performance	Contact resistance (Initial performance/After lifetime)		70m Ω max./130m Ω max.
	Insulation resistance		100MΩ min. 500V DC
	Voltage proof		500V AC for 1 minute
Mechanical	Terminal strength		3N for 1 minute
performance	Actuator strength	Operating direction	10N
		Pulling direction	10N
Durability	Operating life without load		10,000 cycles 100m Ω max.
	Operating life with load (at max. rated load)		10,000 cycles 130m Ω max.
Environmental performance	Cold		-20°C 500h

Dry heat		85℃ 500h	
Damp h	eat	60℃, 90 to 95%RH 500h	
Minimum order unit (pcs.)	Japan	2,000	
	Export	8,000	

Dimensions




Land Dimensions




Viewed from direction A in the dimensions.

Detail of (a)




Circuit Diagram



Packing Specifications





Number of packages (pcs.)	1 reel	2,000	
	1 case / Japan	4,000	
	1 case / export packing	8,000	
Reel width W(mm)		25.4	
Tape width (mm)		24	

Export package measurements (mm)

406×406×190

Soldering Conditions

Example of Reflow Soldering Condition


1. Heating method

Double heating method with infrared heater.

2. Temperature measurement

Thermocouple 0.1 to 0.2 Φ CA (K) or CC (T) at soldering portion (copper foil surface). A heat resisting tape should be used for fixed measurement.

3. Temperature profile



- (1) The condition mentioned above is the temperature on the mounting surface of a PC board. There are cases where the PC board's temperature greatly differs from that of the switch, depending on the PC board's material, size, thickness, etc. The above-stated conditions shall also apply to switch surface temperatures.
- (2) Soldering conditions differ depending on reflow soldering machines. Prior verification of soldering condition is highly recommended.

Reference for Hand Soldering

Soldering temperature	320±5℃
Soldering time	3s max.

Notes are common to this series/models.

- 1. This site catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
- 2. Please place purchase orders per minimum order unit (integer).
- 3. Products other than those listed in the above chart are also available. Please contact us for details.
- 4. Please contact us for automotive use products.