



RECOMMEND P. C. B LAYOUT  
PCE TOLERANCE:  $\pm 0.05$  (TOF VIEW)

### SPECIFICATIONS

- Current Rating: 1.5 Amps
- Insulation Resistance:  $1000M \Omega$  Min
- Contact Resistance:  $20m \Omega$  Max
- Withstanding Voltage: AC 500V
- Operation Temperature:  $-40^\circ$  to  $+105^\circ$
- Contact Material: Brass
- Standard: PA6T
- Insulator Material: polyester
- Contact Plating: Gold Flash
- Max. Processing Temp:  $240^\circ$  C for 30-60 seconds  
( $260^\circ$  C for 5 seconds)

# 深圳市虹成电子有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE  
 X :  $\pm 0.30$  X° :  $\pm 5^\circ$   
 X.X :  $\pm 0.25$  X.X° :  $\pm 1^\circ$   
 X.XX :  $\pm 0.20$  X.XX° :  $\pm 0.5^\circ$

DRAWN NAME: 2.0FH H4.3 2xnPin SMT W4.5 U型 PC6.2 PB4.6 6T  
 SIZE A4 SCALE N:1 PROUCT NO. HC-PM200-4.3H-2x6PS  
 REV A UNIT mm PROJECT PAGE 1/1

CHECKED: 陈超凡 2023/03/23

CHECKED: / / APPROVED: / /

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
	0.00	2.00	11	20.00	22.00	21	40.00	42.00	31	60.00	62.00
2	2.00	4.00	12	22.00	24.00	22	42.00	44.00	32	62.00	64.00
3	4.00	6.00	13	24.00	26.00	23	44.00	46.00	33	64.00	66.00
4	6.00	8.00	14	26.00	28.00	24	46.00	48.00	34	66.00	68.00
5	8.00	10.00	15	28.00	30.00	25	48.00	50.00	35	68.00	70.00
6	10.00	12.00	16	30.00	32.00	26	50.00	52.00	36	70.00	72.00
7	12.00	14.00	17	32.00	34.00	27	52.00	54.00	37	72.00	74.00
8	14.00	16.00	18	34.00	36.00	28	54.00	56.00	38	74.00	76.00
9	16.00	18.00	19	36.00	38.00	29	56.00	58.00	39	76.00	78.00
10	18.00	20.00	20	38.00	40.00	30	58.00	60.00	40	78.00	80.00