



JIANGSU CHANGJIANG ELECTRONICS TECHNOLOGY CO., LTD

SOT-323 Plastic-Encapsulate Diodes


DAN217U SWITCHING DIODE

FEATURES

- Small surface mounting type
- Two diode elements are connected in series

MARKING:A7

SOT-323



Maximum Ratings and Electrical Characteristics, Single Diode @Ta=25 °C

Parameter	Symbol	Limit	Unit
Peak reverse voltage	V _{RM}	80	V
DC reverse voltage	V _R	80	V
Maximum (peak) forward current	I _{FM}	300	mA
Average forward current	I _o	100	mA
Surge current (1μs) (10ms)	I _{FSM}	400 1000	mA
Power dissipation	P _D	200	mW
Junction temperature	T _j	150	°C
Storage temperature	T _{stg}	-55~+150	°C
Operating temperature range	T _{opr}	-40~+100	°C

ELECTRICAL CHARACTERISTICS (Ta=25°C unless otherwise specified)

Parameter	Symbol	Test conditions	Min	Max	Unit
Reverse breakdown voltage	V _(BR)	I _R = 100μA	80		V
Reverse voltage leakage current	I _R	V _R =70V		0.2	μA
Forward voltage	V _F	I _F =100mA		1200	mV

Typical Characteristics

DAN217U

