


Technical Data Sheet

1.8mm Round Subminiature Infrared LED

PIR42-21C/L415/TR8



Features

- Compatible with infrared and vapor phase reflow solder process.
- Low forward voltage
- Good spectral matching to Si photodetector
- Pb free
- The product itself will remain within RoHS compliant version.

Descriptions

- PIR42-21C/L415/TR8 is an infrared emitting diode in miniature SMD package which is molded in a water clear plastic with spherical top view lens.
- The device is spectrally matched with silicon photodiode and phototransistor.

Applications

• Infrared applied system


Device Selection Guide

LED Dowt No	Chip	Lens Color	
LED Part No.	Material		
PIR42-21C/L415/TR8	GaAlAs	Water clear	

Everlight Electronics Co., Ltd. Device No : DIR-0000696 http://www.everlight.com Prepared date : 20-Mar-2012 Rev 1 Page: 1 of 8 Prepared by : Darren Yu



Package Dimensions



Notes: 1.All dimensions are in millimeters 2.Tolerances unless dimensions ±0.1mm

Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Units
Continuous Forward Current	$I_{\rm F}$	65	mA
Reverse Voltage	V _R	5	V
Operating Temperature	T _{opr}	-40 ~ +85	°C
Storage Temperature	T _{stg}	-40 ~ +100	°C
Soldering Temperature	T _{sol}	260	°C
Power Dissipation at(or below)	P _d	170	mW
25°C Free Air Temperature			

Notes: *1:Soldering time \leq 5 seconds.

http://www.everlight.com Prepared date : 20-Mar-2012

EVERLIGHT

PIR42-21C/L415/TR8

Electro-Optical Characteristics (1a=25 ()							
Parameter	Symbol	Condition	Min.	Тур.	Max.	Units	
Radiant Intensity	Ie	I _F =20mA	7	11		mW/sr	
Peak Wavelength	λp	I _F =20mA	720	730	740	nm	
Spectral Bandwidth	Δλ	I _F =20mA		24		nm	
Forward Voltage	V _F	I _F =20mA	1.5	1.95	2.3	V	
Reverse Current	I _R	V _R =5V			10	μΑ	
View Angle	2 _{01/2}	I _F =20mA		30		deg	

Electro-Optical Characteristics (Ta=25°C)



Everlight Electronics Co., Ltd.http://www.everlight.comRev 1Page: 3 of 8Device No : DIR-0000696Prepared date : 20-Mar-2012Prepared by : Darren YuVer.:1Release Date:04/24/2012狀態:Approved(正式發行)



Wavelength λ (nm)


 $I_F = 20 \text{ m A}$ $Ta = 25 \circ C$

Typical Electro-Optical Characteristics Curves

Fig.1 Forward Current vs. Ambient

Fig.2 Spectral Distribution

Temperature







Everlight Electronics Co., Ltd. Device No: DIR-0000696

http://www.everlight.com Prepared date : 20-Mar-2012 Rev 1 Page: 4 of 8 Prepared by : Darren Yu

EVERLIGHT

PIR42-21C/L415/TR8

Typical Electro-Optical Characteristics Curves




Fig.4 Relative Radiant Intensity vs. Angular Displacement

Precautions For Use

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).


2. Storage

- 2.1 Do not open moisture proof bag before the products are ready to use.
- 2.2 Before opening the package, the LEDs should be kept at 30° C or less and 90%RH or less.
- 2.3 The LEDs should be used within a year.
- 2.4 After opening the package, the LEDs should be kept at 30° C or less and 70%RH or less.
- 2.5 The LEDs should be used within 168 hours (7 days) after opening the package.
- 2.6 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.
 Baking treatment : 60±5°C for 24 hours.



3. Soldering Condition

3.1 Pb-free solder temperature profile




- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.

4.Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 280° C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



Ver.:1 Release Date:04/24/2012 狀態:Approved(正式發行)


Prepared date : 20-Mar-2012

Prepared by : Darren Yu



Package Dimensions

1.Reel Dimensions




Unit: mm

Everlight Electronics Co., Ltd.http://www.everlight.comRev 1Page: 7 of 8Device No : DIR-0000696Prepared date : 20-Mar-2012Prepared by : Darren Yu


Ver.:1 Release Date:04/24/2012 狀態:Approved(正式發行)



Packing Procedure



Label Form Specification



Notes

- 1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
- 2. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 3. These specification sheets include materials protected under copyright of EVERLIGHT corporation. Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent.

EVERLIGHT ELECTRONICS CO., LTD. Office: No 6-8,Zhonghua Rd., Shulin Dist., New Taipei City 23860, Taiwan, R.O.C Tel: 886-2-2685-6688 Fax: 886-2-2685-6897 http://www.everlight.com

Everlight Electronics Co., Ltd.http:\\www.everlight.comRev 1Page: 8 of 8Device No : DIR-0000696Prepared date : 20-Mar-2012Prepared by : Darren YuVer.:1 Release Date:04/24/2012狀態:Approved(正式發行)