

SURFACE MOUNT SWITCHING DIODES


VOLTAGE 120-250 Volt POWER 200mWatt


FEATURES

- Fast switching speed.
- · Surface mount package ideally suited for automatic insertion
- Electrically identical to Standard JEDEC
- High conductance
- Lead free in compliance with EU RoHS 2011/65/EU directive
- Green molding compound as per IEC61249 Std. . (Halogen Free)

MECHANICAL DATA

- Case: SOD-323, Plastic
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 0.00014 ounces, 0.0041 grams





MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified. For capacitive load, derate current by 20%.

PARAMETER			BAV19WS BAV20WS BAV21		BAV21WS	UNITS
Marking Code			A8	A80	A82	
Reverse Voltage			100	150	200	V
Peak Reverse Voltage		Vrm	120	200 250		V
Rectified Current (Average), Half Wave Rectifi Resistive Load and f <u>></u> 50 Hz	cation with	Ιo	200			mA
Peak Forward Surge Current, 0.001ms		I FSM	4			А
er Dissipation Derate Above 25°C		Ртот	200			mW
Maximum Forward Voltage at 0.1A		VF	1			V
Maximum DC Reverse Current at Rated DC Blocking Voltage $T_{\rm J}{=}25^{\circ}{\rm C}$		l r	0.1			μA
Typical Junction Capacitance (Note 1)		СЈ	5			pF
Maximum Reverse Recovery Time (Note 2)		Trr	50			ns
Maximum Thermal Resistance	(Note 3) (Note 4)	Reja Rejc	640 260			°C / W
Operating Junction and Storage Temperature Range		Тј,Тѕтс	-55 to +150			°C

NOTE :


1.CJ at VR=0, f=1MHZ

2.From IF=10mA to IR=1mA, VR=6Volts, RL=100 Ω

3.Mounted with minmum recommended pas eize, PC Board FR4


4.Mounted on a FR4 PCB, single-sided copper, with 100cm² copper pad area







MOUNTING PAD LAYOUT




ORDER INFORMATION

Packing information

T/R - 12K per 13" plastic Reel

T/R - 5K per 7" plastic Reel





Packing Code XX				Version Code XXXXX			
Packing type	1 st Code	Packing size code	2 nd Code	HF or RoHS	1 st Code	2 nd ~5 th Code	
Tape and Ammunition Box (T/B)	A	N/A	0	HF	0	serial number	
Tape and Reel (T/R)	R	7"	1	RoHS	1	serial number	
Bulk Packing (B/P)	В	13"	2				
Tube Packing (T/P)	т	26mm	X				
Tape and Reel (Right Oriented) (TRR)	S	52mm	Y				
Tape and Reel (Left Oriented) (TRL)	L	PANASERT T/B CATHODE UP (PBCU)	U				
FORMING	F	PANASERT T/B CATHODE DOWN (PBCD)	D				





Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.