

Unit: inch(mm)

0.040(1.00)

0.033(0.85)

0.012(0.30) 0.007(0.20)

0.048(1.20)

0.031(0.80)

## SS3020HE SERIES

#### SURFACE MOUNT SCHOTTKY BARRIER RECTIFIER

CURRENT

VOLTAGE

#### FEATURES

 Plastic package has Underwriters Laboratory Flammability Classification 94V-O

20~200 Volt

- · For surface mounted applications in order to optimize board space
- Low power loss, high efficiency
- High surge capacity
- Lead free in compliance with EU RoHS 2.0
- Green molding compound as per IEC 61249 standard

#### **MECHANICAL DATA**

- Case: SOD-123HE molded plastic
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026
- Polarity: Color band denotes cathode end

· Approx weight: 0.0006 ounces, 0.0184 grams

Cathode Anode

3 Ampere

SOD-123HE

0.075(1.90)

0.114(2.90) 0.106(2.70)

0.154(3.90)

0.137(3.50)

0.091(2.30)

0.074(1.90)

#### MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified. Resistive or inductive load.


PARAMETER	SYMBOL	SS3020- HE	SS3030- HE	SS3040- HE	SS3060- HE	SS30100- HE	SS30150- HE	SS30200- HE	UNITS
Marking Code	-	EA	EB	EC	ED	EF	EH	EJ	-
Maximum Recurrent Peak Reverse Voltage	V <sub>RRM</sub>	20	30	40	60	100	150	200	V
Maximum RMS Voltage	V <sub>RMS</sub>	14	21	28	42	70	105	140	V
Maximum DC Blocking Voltage	V <sub>DC</sub>	20	30	40	60	100	150	200	V
Maximum Average Forward Current	I <sub>F(AV)</sub>	3							А
Peak Forward Surge Current : 8.3ms single half sine-wave superimposed on rated load	I <sub>fsm</sub>	80							A
Maximum Forward Voltage at 3A (Note 1)	V <sub>F</sub>	0.52 0.65 0.8 0.86 0.86			0.86	V			
Maximum DC Reverse Current TJ=25°C	I <sub>R</sub>		160		100	20	20	20	μA
Typical Thermal Resistance (Note 2)	R <sub>ejl</sub> R <sub>eja</sub>	20 105							°C / W
Operating Junction Temperature Range	TJ	-55 to +125 -55 to +150						٥C	
Storage Temperature Range	T <sub>stg</sub>	-55 to +125 -55 to +150						°C	

#### NOTES :


1. Pulse Test with PW =300µsec, 1% Duty Cycle.


2. Mounted on 50cm<sup>2</sup> FR-4 PCB Board

















































#### **ORDER INFORMATION**

Packing information


T/R - 10K per 13" plastic Reel

T/R - 3K per 7" plastic Reel









Packing Code XX					Version Code XXXXX			
Packing type	1 <sup>st</sup> Code	Packing size code	2 <sup>nd</sup> Code	HF or RoHS	1 <sup>st</sup> Code	2 <sup>nd</sup> ~5 <sup>th</sup> Code		
Tape and Ammunition Box (T/B)	A	N/A	0	HF	0	serial number		
Tape and Reel (T/R)	R	7"	1	RoHS	1	serial number		
Bulk Packing (B/P)	В	13"	2					
Tube Packing (T/P)	т	26mm	X					
Tape and Reel (Right Oriented) (TRR)	S	52mm	Y					
Tape and Reel (Left Oriented) (TRL)	L	PANASERT T/B CATHODE UP (PBCU)	U					
FORMING	F	PANASERT T/B CATHODE DOWN (PBCD)	D					





# Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.