





5~6 Pin



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C ~ +85°C
- 4、Contact Resistance: 30mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer Nylon UL94-V0(2)
PIN Brass Tin-plated



Circuit	Part NO.	Dimensions mm		
		A	B	C
2	HC-XHD-2PW	2.50	7.40	6.90
3	HC-XHD-3PW	5.00	9.90	9.40
4	HC-XHD-4PW	7.50	12.40	11.90
5	HC-XHD-5PW	10.00	14.90	14.40
6	HC-XHD-6PW	12.50	17.40	16.90
7	HC-XHD-7PW	15.00	19.90	19.40
8	HC-XHD-8PW	17.50	22.40	21.90
9	HC-XHD-9PW	20.00	24.90	24.40
10	HC-XHD-10PW	22.50	27.40	26.90
11	HC-XHD-11PW	25.00	29.90	29.40
12	HC-XHD-12PW	27.50	32.40	31.90

		GENREL TOLERANCE		制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
		DIM	TOL	审核 CHECK				
		X.X	±0.30	批准 APPROVAL	产品名称 TITLE	2.50 单排 弯针	版本 REV.	A
1		初版发行			产品料号 PART NO.	HC-XHD-NPW	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°	投影 Projection	材料 MATERIAL	页次 SHEET	1/1