ULTRA LOW CAPACITANCE STEERING DIODE/TVS ARRAY



DESCRIPTION

The PLR0502 is an ultra low capacitance (0.6pF) steering diode and TVS array combo. This device provides circuit protection for interfaces and wireless bus applications and portable electronics. The PLR0502 is ideally suited to protect USB(1.0-3.0) data I/O ports against the effects of ESD and EFT.

The PLR0502 meets the requirements of IEC 61000-4-2 (ESD) and IEC 61000-4-4 (EFT). At higher operating frequencies or faster edge rates, insertion loss and signal integrity are a major concern. The PLR0502 offers a ultra low capacitance and low leakage current in a SOT-543 package.

FEATURES

- Compatible with IEC 61000-4-2 (ESD): Air 15kV, Contact 8kV
- Compatible with IEC 61000-4-4 (EFT): 40A 5/50ns
- 200 Watts Peak Pulse Power per Line (tp = 8/20µs)
- ESD Protection > 25 kilovolts
- Low Clamping Voltage
- Unidirectional Configuration
- Protects 2 I/O Ports and Power Supply
- Ultra Low Capacitance: 0.6pF
- RoHS Compliant
- REACH Compliant

MECHANICAL CHARACTERISTICS


- Molded JEDEC SOT-543 Package
- Approximate Weight: 3 milligrams
- Lead-Free Pure-Tin Plating (Annealed)
- Solder Reflow Temperature: Pure-Tin - Sn, 100: 260-270°C
- 8mm Tape and Reel Per EIA Standard 481
- Flammability Rating UL 94V-0

Ethernet - 10/100 Base TFireWire

APPLICATIONS

- Wireless Communications
- USB 1.0, USB 2.0 & USB 3.0

PIN CONFIGURATION



TYPICAL DEVICE CHARACTERISTICS

MAXIMUM RATINGS @ 25°C Unless Otherwise Specified							
PARAMETER	SYMBOL	VALUE	UNITS				
Operating Temperature	TL	-55 to 150	°C				
Storage Temperature	T _{stg}	-55 to 150	°C				
Peak Pulse Power (tp = $8/20\mu$ s) - See Figure 1	P _{PP}	200	Watts				
Peak Forward Voltage - I $_{\rm F}$ = 1A, 8/20 μ s	V _F	1.5	Volts				


ELECTRICAL CHARACTERISTICS PER LINE @ 25°C Unless Otherwise Specified								
PART NUMBER	DEVICE MARKING	RATED STAND-OFF VOLTAGE V _{WM} VOLTS	MINIMUM BREAKDOWN VOLTAGE @1mA V _(BR) VOLTS	MAXIMUM CLAMPING VOLTAGE (Fig. 2) (Note 2) @I _p = 1A V _c VOLTS	MAXIMUM CLAMPING VOLTAGE (Fig. 2) (Note 2) @ 8/20µs V _c @ I _{pp}	MAXIMUM LEAKAGE CURRENT @V _{wm} Ι _p μΑ	MAXIMUM CAPACITANCE (Per Data Line) (Fig. 5) (Note 1) @0V, 1MHz C _{J(SD)} pF	
PLR0502	В5	5.0	6.0	9.8	20.0V @ 10.0A	1	0.6	
NOTE								

NOTE


05245

1. As shown in Figure 5, REF 1 is connected to ground, REF 2 is connected to + V_{cc} and input applies to V_{cc} = 5V, V_{sign} = 30mV, F = 1MHz.

2. Measured across pin 1 to pin 4.



TYPICAL DEVICE CHARACTERISTICS








FIGURE 5 INPUT CAPACITANCE CIRCUIT REF2 V_{SIGN} G +V_{cc}

SOT-543 PACKAGE INFORMATION

OUTLINE DIMENSIONS							
DIM	MILLIN	IETERS	INCHES				
	MIN	MAX	MIN	MAX			
А	1.50	1.70	0.059	0.067			
В	1.10	1.30	0.043	0.051			
С	0.50	0.60	0.020	0.024			
D	0.17	0.27	0.007	0.011			
G	0.50 BSC		0.020 BSC				
J	0.08	0.18	0.003	0.007			
К	0.10	0.30	0.004	0.012			
S	1.50	1.70	0.059	0.067			
R	0.05	0.15	0.002	0.006			





NOTES

05245


1. Controlling dimension: inches.

2. Dimensioning and tolerances per ANSI Y14.5M, 1985.

3. Dimensions are exclusive of mold flash and metal burrs.


4. Do not connect center stub.

PAD LAYOUT DIMENSIONS							
DIM	MILLIMETERS	INCHES					
DIN	NOMINAL	NOMINAL					
А	1.02	0.040					
В	1.20	0.048					
С	0.30	0.012					
D	0.51	0.020					
NOTES 1. Controlling dimension: inches.							



TAPE AND REEL

05245



SPECIFICATIONS												
REEL DIA.	TAPE WIDTH	A0	В0	ко	D	E	F	w	P0	P2	Р	tmax
178mm (7")	8mm	1.78 ± 0.05	1.78 ± 0.05	0.69 ± 0.05	1.50 ± 0.10	1.75 ± 0.10	3.50 ± 0.05	8.00 ± 0.30	4.00 ± 0.10	2.00 ± 0.05	4.00 ± 0.10	0.25
NOTES 1. Dimensions are in millimeters. 2. Surface mount product is taped and reeled in accordance with EIA-481. 3. Suffix - T7 = 7" Reel - 3,000 pieces per 8mm tape. 4. Marking on Part - marking code (see page 2).												

Package outline, pad layout and tape specifications per document number 06074.R3 3/11.

ORDERING INFORMATION							
BASE PART NUMBER LEADFREE SUFFIX TAPE SUFFIX QTY/REEL REEL SIZE TUBE QT							
PLR0502	-LF	-T7	3,000	7″	n/a		
This device is only available in a Lead-Free configuration.							

COMPANY INFORMATION

COMPANY PROFILE

In business more than 20 years, ProTek Devices[™] is a privately held semiconductor company. The company offers a product line of overvoltage protection and overcurrent protection components. These include transient voltage suppressor array (TVS arrays) avalanche breakdown diode, steering diode TVS array and electronics SMD chip fuses. These components deliver circuit protection in electronic systems from numerous overvoltage and overcurrent events. They include lightning; electrostatic discharge (ESD); nuclear electromagnetic pulses (NEMP); inductive switching; and electromagnetic interference (EMI) / radio frequency interference (RFI). ProTek Devices also offers high performance interface and linear products. They include analog switches; multiplexers; LED drivers; LED wafer die for ESD protection; audio control ICs; RF and related high frequency products.

CONTACT US

Corporate Headquarters

2929 South Fair Lane Tempe, Arizona 85282 USA

By Telephone

General: 602-431-8101 Sales: & Marketing: 602-414-5109 Customer Service: 602-414-5114 Product Technical Support: 602-414-5107

By Fax

General: 602-431-2288

By E-mail:

Sales: <u>sales@protekdevices.com</u> Customer Service: <u>service@protekdevices.com</u> Technical Support: <u>support@protekdevices.com</u>

ProTek Devices (Asia Pacific) Pte. Ltd.

8 Ubi Road 2, #06-19 Zervex Singapore - 408538 Tel: +65-67488312 Fax: +65-67488313

Web www.protekdevices.com

COPYRIGHT © ProTek Devices 2007 - This literature is subject to all applicable copyright laws and is not for resale in any manner.

SPECIFICATIONS: ProTek reserves the right to change the electrical and or mechanical characteristics described herein without notice.

DESIGN CHANGES: ProTek reserves the right to discontinue product lines without notice and that the final judgement concerning selection and specifications is the buyer's and that in furnishing engineering and technical assistance. ProTek assumes no responsibility with respect to the selection or specifications of such products. ProTek makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ProTek assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability without limitation special, consequential or incidental damages.

LIFE SUPPORT POLICY: ProTek Devices products are not authorized for use in life support systems without written consent from the factory.