



NOTES:
 1. Material:
 Insulator: PBT+30%GF, UL 94V-0,
 Color: Black or Grey.
 2. Temperature Range: -25°C to +85°C

PART NO.
 Z-B810 ** 210000 * 1
 No. of Positions 10~64
 Color
 0=Black
 8=Grey
 9=White



UNITS: <input checked="" type="checkbox"/> mm <input type="checkbox"/> inch SIZE: A3 NAME: 2.54MM CRIMP TYPE IDC HOUSING			TOLERANCE LEVEL (UNLESS OTHERWISE SPECIFIED) B		
A (ISO2768-m)			B		
RANGE	mm	DEFINED TOLERANCE	PART NO: Z-B810**210000*1		
0 ~ 6	± 0.1	.X	2023/11/16		
6 ~ 30	± 0.2	.XX	2023/11/16		
30 ~ 120	± 0.3	.XXX	APPD: Peter廖小瓊		
120 ~ 400	± 0.5		CHKD: Peter廖小瓊		
ANGLE	X° ± 1°	ANGLE	DRAW: Lily寶麗星		
			DESIGN: Lily寶麗星 2023/11/15		
TITLE: CUSTOMER DWG.			DWG NO: 010-0000-F48		
SCALE: NA			SHEET: 1/1		REV: A2

A2	UPGRADE VERSION ECR-23042	2023/10/18
A1	MODIFY	2018/08/17
REV.	DESCRIPTION	DATE

CONFIDENTIAL: THIS DOCUMENT CONTAINED THE INFORMATION IS PROPRIETARY AND CONFIDENTIAL TO Nexttronics Engineering Corp. NO PERSON IS ALLOWED TO USE COPY, PUBLISH OR OTHERWISE DISCLOSE THE INFORMATION TO OTHERS, UNLESS BY THE PRIOR WRITTEN EXPRESS AUTHORIZATION OF Nexttronics Engineering Corp. (C)COPYRIGHT- Nexttronics Engineering Corp.

USE SHOWN DIMENSIONS DO NOT SCALE DRAWING