



NOTES:
 1. Material:
 Insulator: PBT+30%GF, UL 94V-0,
 Color: Black or Grey.
 2. Temperature Range: -25°C to +85°C

PART NO.
 Z-B810 ** 210000 * 1
 No. of Positions 10~64
 Color
 0=Black
 8=Grey
 9=White



UNITS: <input checked="" type="checkbox"/> mm <input type="checkbox"/> inch SIZE: A3 NAME: 2.54MM CRIMP TYPE IDC HOUSING			TOLERANCE LEVEL (UNLESS OTHERWISE SPECIFIED) B		
A (ISO2768-m)			B		
RANGE	mm	DEFINED TOLERANCE	PART NO: Z-B810**210000*1		
0 ~ 6	± 0.1	.X ± 0.38	TITLE: CUSTOMER DWG.		
6 ~ 30	± 0.2	.XX ± 0.25	APPD: Peter廖小瓊 2023/11/16		
30 ~ 120	± 0.3	.XXX ± 0.08	CHKD: Peter廖小瓊 2023/11/16		
120 ~ 400	± 0.5	/	DRAW: /		
ANGLE	X° ± 1°	ANGLE	X° ± 2°	DESIGN: Lily寶麗星 2023/11/15	
REV.	DESCRIPTION	DATE	SCALE	SHEET	REV.
A2	UPGRADE VERSION ECR-23042	2023/10/18	NA	1/1	A2
A1	MODIFY	2018/08/17	DWG NO: 010-0000-F48		

CONFIDENTIAL: THIS DOCUMENT CONTAINED THE INFORMATION IS PROPRIETARY AND CONFIDENTIAL TO Nexttronics Engineering Corp. NO PERSON IS ALLOWED TO USE COPY, PUBLISH OR OTHERWISE DISCLOSE THE INFORMATION TO OTHERS, UNLESS BY THE PRIOR WRITTEN EXPRESS AUTHORIZATION OF Nexttronics Engineering Corp. (C)COPYRIGHT- Nexttronics Engineering Corp.

USE SHOWN DIMENSIONS DO NOT SCALE DRAWING