

# **AC6963B2 Datasheet**

**Zhuhai Jieli Technology Co.,LTD**

**Version: V1.0**

**Date: 2020.11.11**

# AC6963B2 Features

## CPU

- 32-bit DSP supports hardware Float Point Unit (FPU)
- Up to 160MHz programmable processor
- 64Vectored interrupts
- 4 Levels interrupt priority

## DSP Audio Processing

- SBC, AAC Audio decodes supported for BT audio
- mSBC voice codecs supported for BT phone
- Supports MP2, MP3, WMA, APE, FLAC, AAC, MP4, M4A, WAV, AIF, AIFC audio decoding
- Packet Loss Concealment (PLC) for voice processing
- Acoustic echo cancellation/suppression (AEC,AES)
- Single/Dual MIC Environmental Noise Cancellation (ENC)
- Multi-band DRC limiter
- 10-band EQ configuration for voice Effects

## Audio Codec

- Two channels 16-bit DAC, SNR >= 95dB
- One channels 16-bit ADC , SNR >= 90dB
- Sampling rates of 8KHz/11.025KHz/16KHz/22.05KHz/24KHz/32KHz/44.1KHz/48KHz are supported
- One analog MIC amplifier, build-in MIC bias generator
- Supports two PDM digital MIC inputs
- Two channels Mono analog MUX
- Supports cap-less, single-ended, and differential mode at the DAC path
- Supports 16ohm and 32ohm Speaker loading

## Bluetooth

- Compliant with Bluetooth V5.1+BR+EDR+BLE specification
- Meet class1 class2 and class3 transmitting

power requirement

- Support GFSK and  $\pi/4$  DQPSK all packet types
- Provides +6dbm transmitting power
- receiver with -90dBm sensitivity
- Fast AGC for enhanced dynamic range
- Supports a2dp/avctp/avdtp/avrcp/hfp/spp/smp/att/gap/gatt/rfcomm/sdp/l2cap profile

## Peripherals

- One full speed USB 2.0 OTG controller
- Six multi-function 32-bit timers, support capture and PWM mode
- Three full-duplex basic UART, UART0 and UART1 supports DMA mode
- One hardware IIC interface supports host and device mode
- 10-bit ADC for analog sampling
- External wake up/interrupt on all GPIOs

## PMU

- Low voltage LDO for internal digital and analog circuit supply
- 3uA current consumption in the soft-off mode
- Built-in LDO for the core, I/O, Bluetooth and flash
- VBAT is 2.2V to 5.5V
- VDDIO is 2.2V to 3.6V

## Packages

- QFN20(3mm\*3mm)

## Temperature

- Operating temperature: -40°C to +70°C
- Storage temperature: -65°C to +150°C

## Applications

- Bluetooth Stereo speaker
- Bluetooth TWS speaker

## Confidential

The information contained herein is the exclusive property of JIELI and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission of JIELI.

# 1、 Pin Definition

## 1.1 Pin Assignment




Figure 1-1 AC6963B\_QFN20

## 1.2 Pin Description

Table 1-1 AC6963B\_QFN20 Pin Description

PIN NO.	Name	I/O Type	Drive (mA)	Function	Other Function
1	VCOM	P	/		
2	DACL	O	/		DAC Left Channel
	DACR	O	/		DAC Right Channel
3	PB7	I/O	24/8	GPIO	AMUX1R: Analog Channel1 Right; SPI2DOA: SPI2 Data Out(A); IIC_SDA_C: IIC DAT(C); ADC9: ADC Input Channel 9; PWM5: Timer5 PWM Output; UART1RXA: Uart1 Data In(A);
4	PB6	I/O	24/8	GPIO	AMUX1L: Analog Channel1 Left; SPI2CLKA: SPI2 Data Out(A); IIC_SCL_C: IIC SCL(C); ADC8: ADC Input Channel 8; TMR3: Timer3 Clock Input; UART1TXA: Uart1 Data Out(A);
	LDO_IN	P	/		Battery Charger In
5	PB5	I/O	8	GPIO (High Voltage Resistance)	SPI2DIA: SPI2 Data Input(A); PWM3: Timer3 PWM Output; CAP1: Timer1 Capture; UART0TXC: Uart0 Data Out(C); UART0RXC: Uart0 Data In(C);
6	VBAT	P	/		Battery Power Supply
7	VDDIO	P	/		IO Power 3.3v
8	PB1	I/O	24/8	GPIO (pull up)	Long Press Reset; SPI1DOA: SPI1 Data Out(A); ADC5: ADC Input Channel 5; TMR2: Timer2 Clock Input; UART0RXB: Uart0 Data In(B);
9	FMIP	I	/		FM Antenna
10	BT_RF	/	/		BT Antenna
11	BT_SOCI	I	/		BT OSC In
12	BT_SOCO	O	/		BT OSC Out
13	PC5	I/O	24/8	GPIO	SD0CLKA: SD0 Clock(A); SPI1DOB: SPI1 Data Out(B);

### Confidential

The information contained herein is the exclusive property of JIELI and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission of JIELI.

					IIC_SDA_B: IIC SDA(B); ADC12: ADC Input Channel 12; TMR1: Timer1 Clock Input; UART2RXD: Uart2 Data In(D);
14	PC4	I/O	24/8	GPIO	SD0CMDA: SD0 Command(A); SPI0_DAT3AB(3): SPI0 Data3(AB); SPI1CLKB: SPI1 Clock(B); IIC_SCL_B: IIC SCL(B); ADC11: ADC Input Channel 11; PWM1: Timer1 PWM Output; UART2TXD: Uart2 Data Out (D);
15	PC3	I/O	24/8	GPIO	SD0DAT0A: SD0 Data0(A); SPI0_DAT2B(2): SPI0 Data2(B); SPI1DIB: SPI1 Data In(B); CAP2: Timer2 Capture; UART0TXD: Uart0 Data Out (D); UART0RXD: Uart0 Data In(D);
	USBDM	I/O	4	USB Negative Data (pull down)	SPI2DOB: SPI2 Data Out(B); IIC_SDA_A: IIC SDA(A); ADC14: ADC Input Channel 14; UART1RXD: Uart1 Data In(D);
16	USBDP	I/O	4	USB Positive Data (pull down)	SPI2CLKB: SPI2 Clock(B); IIC_SCL_A: IIC SCL(A); ADC13: ADC Input Channel 13; UART1TXD: Uart1 Data Output(D);
17	PA4	I/O	24/8		SD0CMDC: SD0 Command(C) AMUX0R: Analog Channel0 Right; PLNK_DAT1: PLNK Data1; UART1_RTS: Uart1 Request to send; ADC3: ADC Input Channel 3; TMR4: Timer4 Clock Input; UART2RXA: Uart2 Data In(A);
18	PA3	I/O	24/8		SD0DATC: SD0 Data(C); AMUX0L: Analog Channel0 Left; PLNK_SCLK: PLNK Serial Clock; UART1_CTS: Uart1 Clear to send; ADC2: ADC Input Channel 3; PWM5: Timer5 PWM Output; UART2TXA: Uart1 Data Output(D);
	PA2	I/O	24/8	GPIO	MIC_BIAS: Microphone Bias Output CAP3: Timer3 Capture;
	PA0	I/O	/		SDPG: SD Power Supply ADC0: ADC Input Channel 0;

**Confidential**

The information contained herein is the exclusive property of JIELI and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission of JIELI.

					CLKOUT0 UART1TXC: Uart1 Data Output(C);
19	PA1	I/O	24/8	GPIO	ADC1: ADC Input Channel 1; PWM4: Timer4 PWM Output; UART1RXC: Uart0 Data In(C);
	MIC	I	/		MIC: MIC Input Channel ;
20	DACVSS	P	/		DAC Ground

**Confidential**

The information contained herein is the exclusive property of JIELI and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission of JIELI.

## 2、Electrical Characteristics

### 2.1 Absolute Maximum Ratings

Table 2-1

Symbol	Parameter	Min	Max	Unit
Topt	Operating temperature	-40	+85	°C
Tstg	Storage temperature	-65	+150	°C
VBAT	Supply Voltage	-0.3	5.5	V
LDO_IN	Charger Voltage	-0.3	6	V
V <sub>3.3IO</sub>	3.3V IO Input Voltage	-0.3	3.6	V

Note : The chip can be damaged by any stress in excess of the absolute maximum ratings listed below

### 2.2 PMU Characteristics

Table 2-2

Symbol	Parameter	Min	Typ	Max	Unit	Test Conditions
LDO_IN	Loading current	—	—	250	mA	VBAT = 4.2V
VBAT	Voltage Input	2.2	3.7	5.5	V	LDO_IN = 5V
V <sub>VDDIO</sub>	Voltage output	—	3.3	—	V	VBAT = 4.2V, 100mA loading

### 2.3 Battery Charge

Table 2-3

Symbol	Parameter	Min	Typ	Max	Unit	Test Conditions
LDO_IN	Charge Input Voltage	4.5	5	5.5	V	—
V <sub>Charge</sub>	Charge Voltage	4.15	4.2	4.25	V	—
I <sub>Charge</sub>	Charge Current	20		250	mA	Charge current at fast charge mode

### 2.4 IO Input/Output Electrical Logical Characteristics

Table 2-4

IO input characteristics						
Symbol	Parameter	Min	Typ	Max	Unit	Test Conditions

#### Confidential

The information contained herein is the exclusive property of JIELI and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission of JIELI.

V <sub>IL</sub>	Low-Level Input Voltage	-0.3	–	0.3* VDDIO	V	VDDIO = 3.3V
V <sub>IH</sub>	High-Level Input Voltage	0.7* VDDIO	–	VDDIO+0.3	V	VDDIO = 3.3V
<b>IO output characteristics</b>						
V <sub>OL</sub>	Low-Level Output Voltage	–	–	0.33	V	VDDIO = 3.3V
V <sub>OH</sub>	High-Level Output Voltage	2.7	–	–	V	VDDIO = 3.3V

## 2.5 Internal Resistor Characteristics

Table 2-5

Port	General Output	High Drive	Internal Pull-Up Resistor	Internal Pull-Down Resistor	Comment
PA1~PA4 PB1 PB6,PB7 PC3~PC5	8mA	24mA	10K	10K	1、PB1 default pull up 2、USBDM & USBDP default pull down 3、internal pull-up/pull-down resistance   accuracy ±20%
PA0	8mA	–	10K	10K	
USBDP	4mA	–	1.5K	15K	
USBDM	4mA	–	180K	15K	

## 2.6 DAC Characteristics

Table 2-6

Parameter	Min	Typ	Max	Unit	Test Conditions
Frequency Response	20	–	20K	Hz	1KHz/0dB 10Kohm loading With A-Weighted Filter
THD+N	–	-75	–	dB	
S/N	–	95	–	dB	
Crosstalk	–	-90	–	dB	
Output Swing	–	1	–	V <sub>rms</sub>	
Dynamic Range	–	90	–	dB	1KHz/-60dB 10Kohm loading With A-Weighted Filter
DAC Output Power	11	–	–	mW	32ohm loading

## 2.7 ADC Characteristics

Table 2-7

Parameter	Min	Typ	Max	Unit	Test Conditions
Dynamic Range	–	80	–	dB	1KHz/-60dB

### Confidential

The information contained herein is the exclusive property of JIELI and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission of JIELI.



S/N	-	90	91	dB	1KHz/-60dB
THD+N	-	-70	-	dB	
Crosstalk	-	-90	-	dB	

## 2.8 BT Characteristics

### 2.8.1 Transmitter

#### Basic Data Rate

Table 2-8

Parameter	Min	Typ	Max	Unit	Test Conditions
RF Transmit Power		4	6	dBm	25°C, Power Supply VBAT=5V 2441MHz
RF Power Control Range		20		dB	
20dB Bandwidth		950		KHz	
Adjacent Channel	+2MHz	-40		dBm	
	-2MHz	-38		dBm	
Transmit Power	+3MHz	-44		dBm	
	-3MHz	-35		dBm	

#### Enhanced Data Rate

Table 2-9

Parameter	Min	Typ	Max	Unit	Test Conditions
Relative Power		-1		dB	25°C, Power Supply VBAT=5V 2441MHz
$\pi/4$ DQPSK Modulation Accuracy	DEVM RMS	6		%	
	DEVM 99%	10		%	
	DEVM Peak	15		%	
Adjacent Channel	+2MHz	-40		dBm	
	-2MHz	-38		dBm	
Transmit Power	+3MHz	-44		dBm	
	-3MHz	-35		dBm	

### 2.8.2 Receiver

#### Basic Data Rate

Table 2-10

Parameter	Min	Typ	Max	Unit	Test Conditions
Sensitivity		-90		dBm	25°C, Power Supply VBAT=5V 2441MHz
Co-channel Interference Rejection		-13		dB	
Adjacent Channel Interference Rejection	+1MHz	+5		dB	
	-1MHz	+2		dB	
	+2MHz	+37		dB	

#### Confidential

The information contained herein is the exclusive property of JIELI and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission of JIELI.

	-2MHz		+36		dB
	+3MHz		+40		dB
	-3MHz		+35		dB

**Enhanced Data Rate****Table 2-11**

Parameter	Min	Typ	Max	Unit	Test Conditions
Sensitivity		-90		dBm	25°C, Power Supply, VBAT=5V 2441MHz
Co-channel Interference Rejection		-13		dB	
Adjacent Channel Interference Rejection	+1MHz	+5		dB	
	-1MHz	+2		dB	
	+2MHz	+37		dB	
Interference Rejection	-2MHz	+36		dB	
	+3MHz	+40		dB	
	-3MHz	+35		dB	

**2.9 FM Receiver Characteristics****Table 2-12**

Parameter	Min	Typ	Max	Unit	Test Conditions
Input Frequency	76		108	MHz	
Usable Sensitivity	3	4	8	dB $\mu$ V EMF	(S+N)/N=26dB
Adjacent Channel Selectivity		48		dB	$\pm$ 200kHz
IIP3		88		dB $\mu$ V EMF	$\Delta$ f1=200 kHz, $\Delta$ f2=400 kHz
Audio Output Voltage	0		3	V	Empty Load
Audio Frequency Response	20		20k	Hz	DacTest
Audio (S+N)/N		58		dB	
Stereo Separation		40		dB	
Audio Total Harmonic Distortion (THD)		0.4		%	

**Confidential**

The information contained herein is the exclusive property of JIELI and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission of JIELI.

### 3、 Package Information

#### 3.1 QFN20(3mm\*3mm)




Figure 3-1. AC6963B\_QFN20 Package

## 4、 Revision History

Date	Revision	Description
2020.11.11	V1.0	Initial Release

### Confidential

The information contained herein is the exclusive property of JIELI and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission of JIELI.