

AC6969A2 Datasheet

Zhuhai Jieli Technology Co.,LTD

Version: V1.1

Date: 2021.11.22

AC6969A2 Features

CPU

- 32-bit DSP supports hardware Float Point Unit (FPU)
- Up to 160MHz programmable processor
- 64 Vectored interrupts
- 4 Levels interrupt priority

DSP Audio Processing

- SBC, AAC Audio decodes supported for BT audio
- mSBC voice codecs supported for BT phone
- Supports MP2, MP3, WMA, APE, FLAC, AAC, MP4, M4A, WAV, AIF, AIFC audio decoding
- Packet Loss Concealment (PLC) for voice processing
- Acoustic echo cancellation/suppression (AEC, AES)
- One analog MIC Environmental Noise Cancellation (ENC)
- Multi-band DRC limiter
- 10-band EQ configuration for voice Effects

Audio Codec

- Two channels 16-bit DAC, SNR \geq 95dB
- One channels 16-bit ADC, SNR \geq 90dB
- Sampling rates of 8KHz/11.025KHz/16KHz/22.05KHz/24KHz/32KHz/44.1KHz/48KHz are supported
- One analog MIC amplifier, build-in MIC bias generator
- Supports two PDM digital MIC inputs
- Two channels Mono analog MUX
- Supports cap-less, single-ended, and differential mode at the DAC path
- Supports 16ohm and 32ohm Speaker loading

Bluetooth

- Compliant with Bluetooth V5.3+BR+EDR+BLE specification
- Meet class2 and class3 transmitting power

requirement

- Support GFSK and $\pi/4$ DQPSK all packet types
- Provides maximum +6dBm transmitting power
- receiver with minimum -90dBm sensitivity
- Fast AGC for enhanced dynamic range
- Supports
 - a2dp \avctp \avdtp \avrcp \hfp \spp \smp \att \gap \gatt \rfcomm \sdp \l2cap profile
 - a2dp 1.3.2 \avctp 1.4 \avdtp 1.3 \avrcp 1.6.2 \hfp 1.8 \spp 1.2 \rfcomm 1.1 \pnp 1.3 \hid 1.1.1 \sdp core5.3 \l2cap core 5.3

Peripherals

- One full speed USB 2.0 OTG controller
- Six multi-function 32-bit timers, support capture and PWM mode
- Three full-duplex basic UART, UART0 and UART1 supports DMA mode
- One hardware IIC interface supports host and device mode
- 10-bit ADC for analog sampling
- External wake up/interrupt on all GPIOs

PMU

- Low voltage LDO for internal digital and analog circuit supply
- 3uA current consumption in the soft-off mode
- Built-in LDO for the core, I/O, Bluetooth and flash
- VBAT is 2.2V to 5.5V
- VDDIO is 2.2V to 3.6V

Packages

- SOP16

Temperature

- Operating temperature: -40°C to +85°C
- Storage temperature: -65°C to +150°C

Confidential

The information contained herein is the exclusive property of JIELI and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission of JIELI.

Applications

 Bluetooth TWS Earphone



Confidential

The information contained herein is the exclusive property of JIELI and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission of JIELI.

1、 Pin Definition

1.1 Pin Assignment

VDDIO	○			PA1
VBAT	1		16	DACVSS
LDO_IN/PB5	2		15	DACL
BT_AVDD	3		14	DACR
PB3	4	AC6969A2	13	USBDP/PA2/PA3
PB1	5	(SOP16)	12	USBDM/PC5
BT_RF	6		11	BT_OSCO
VSSIO	7		10	BT_OSCI
	8		9	

Figure 1-1 AC6969A_SOP16 Package Diagram

1.2 Pin Description

Table 1-1 AC6969A_SOP16 Pin Description

PIN NO.	Name	I/O Type	Drive (mA)	Function	Other Function
1	VDDIO	P	/		IO Power 3.3v
2	VBAT	P	/		Battery Power Supply
3	LDO_IN	P	/		Battery Charger In
	PB5	I/O	8	GPIO (High Voltage Resistance)	PWM3: Timer3 PWM Output; CAP1: Timer1 Capture; UART0TXC: Uart0 Data Out(C); UART0RXC: Uart0 Data In(C);
4	BT_AVDD	P	/		BT Power
5	PB3	I/O	24	GPIO	ADC6: ADC Input Channel 6; PWM2: Timer2 PWM Output; UART2RXB: Uart2 Data In(B);
6	PB1	I/O	24/8	GPIO (pull up)	Long Press Reset; ADC5: ADC Input Channel 5; TMR2: Timer2 Clock Input; UART0RXB: Uart0 Data In(B);
7	BT_RF	/	/		BT Antenna
8	VSSIO	P	/		Ground
9	BT_SOCI	I	/		BT OSC In
10	BT_SOCO	O	/		BT OSC Out
11	USBDM	I/O	4	USB Negative Data (pull down)	IIC_SDA_A: IIC SDA(A); ADC14: ADC Input Channel 14; UART1RXD: Uart1 Data In(D);
	PC5	I/O	24/8	GPIO	IIC_SDA_B: IIC SDA(B); ADC12: ADC Input Channel 12; TMR1: Timer1 Clock Input; UART2RXD: Uart2 Data In(D);
12	USBDP	I/O	4	USB Positive Data (pull down)	IIC_SCL_A: IIC SCL(A); ADC13: ADC Input Channel 13; UART1TXD: Uart1 Data Output(D);
	PA3	I/O	24/8		UART1_CTS: Uart1 Clear to send; ADC2: ADC Input Channel 3; PWM5: Timer5 PWM Output; UART2TXA: Uart1 Data Output(D);
	PA2	I/O	24/8	GPIO	MIC_BIAS: Microphone Bias Output

Confidential

The information contained herein is the exclusive property of JIELI and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission of JIELI.

					CAP3: Timer3 Capture;
13	DACR	O	/		DAC Right Channel
14	DACL	O	/		DAC Left Channel
15	DACVSS	P	/		DAC Ground
16	PA1	I/O	24/8	GPIO	MIC: MIC Input Channel ; ADC1: ADC Input Channel 1; PWM4: Timer4 PWM Output; UART1RXC: Uart0 Data In(C);

Confidential

The information contained herein is the exclusive property of JIELI and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission of JIELI.

2、Electrical Characteristics

2.1 Absolute Maximum Ratings

Table 2-1

Symbol	Parameter	Min	Max	Unit
Tamb	Ambient Temperature	-40	+85	°C
Tstg	Storage temperature	-65	+150	°C
VBAT	Supply Voltage	-0.3	4.5	V
V _{3.3IO}	3.3V IO Input Voltage	-0.3	VDDIO+0.3	V
LDO_IN	Charge Input Voltage	-0.3	6.5	V

2.2 PMU Characteristics

Table 2-2

Symbol	Parameter	Min	Typ	Max	Unit	Test Conditions
LDO_IN	Loading current	–	–	300	mA	VBAT = 4.2V
VBAT	Voltage Input	2.2	3.7	5.5	V	
V _{VDDIO}	Voltage output	–	3.3	–	V	VBAT = 4.2V, 100mA loading
V _{BT_AVDD}	Voltage output	–	1.3	–	V	VBAT=4.2V, 100mA loading

2.3 IO Input/Output Electrical Logical Characteristics

Table 2-3

IO input characteristics						
Symbol	Parameter	Min	Typ	Max	Unit	Test Conditions
V _{IL}	Low-Level Input Voltage	-0.3	–	0.3* VDDIO	V	VDDIO = 3.3V
V _{IH}	High-Level Input Voltage	0.7* VDDIO	–	VDDIO+0.3	V	VDDIO = 3.3V
IO output characteristics						
V _{OL}	Low-Level Output Voltage	–	–	0.33	V	VDDIO = 3.3V
V _{OH}	High-Level Output Voltage	2.7	–	–	V	VDDIO = 3.3V

Confidential

The information contained herein is the exclusive property of JIELI and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission of JIELI.

2.4 Internal Resistor Characteristics

Table 2-4

Port	General Output	High Drive	Internal Pull-Up Resistor	Internal Pull-Down Resistor	Comment
PA1~PA3 PB1 PC5	8mA	24mA	10K	10K	1、PB1 default pull up 2、USBDM & USBDP default pull down 3、internal pull-up/pull-down resistance accuracy $\pm 20\%$
PB3	24mA	–	10K	10K	
PB5	8mA	–	10K	10K	
USBDP	4mA	–	1.5K	15K	
USBDM	4mA	–	180K	15K	

2.5 DAC Characteristics

Table 2-5

Parameter	Min	Typ	Max	Unit	Test Conditions
Frequency Response	20	–	20K	Hz	1KHz/0dB 10Kohm loading With A-Weighted Filter
THD+N	–	-75	–	dB	
S/N	–	95	–	dB	
Crosstalk	–	-90	–	dB	
Output Swing	–	1	–	Vrms	
Dynamic Range	–	95	–	dB	1KHz/-60dB 10Kohm loading With A-Weighted Filter
DAC Output Power	–	20	–	mW	32ohm loading

2.6 ADC Characteristics

Table 2-6

Parameter	Min	Typ	Max	Unit	Test Conditions
Dynamic Range	–	90	–	dB	Fsample=44.1kHz Fin=1KHz 2mVpp Input
S/N	–	90	91	dB	Fsample=44.1kHz Fin=1KHz 1.2Vpp Input
THD+N	–	-70	–	dB	
Crosstalk	–	-90	–	dB	

Confidential

The information contained herein is the exclusive property of JIELI and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission of JIELI.

2.7 BT Characteristics

2.7.1 Transmitter

Basic Data Rate

Table 2-7

Parameter	Min	Typ	Max	Unit	Test Conditions
RF Transmit Power		4	6	dBm	25°C, Power Supply VBAT=5V 2441MHz
RF Power Control Range		20		dB	
20dB Bandwidth		950		KHz	
Adjacent Channel	+2MHz	-40		dBm	
	-2MHz	-38		dBm	
Transmit Power	+3MHz	-44		dBm	
	-3MHz	-35		dBm	

Enhanced Data Rate

Table 2-8

Parameter	Min	Typ	Max	Unit	Test Conditions
Relative Power		-1		dB	25°C, Power Supply VBAT=5V 2441MHz
$\pi/4$ DQPSK Modulation Accuracy	DEVM RMS	6		%	
	DEVM 99%	10		%	
	DEVM Peak	15		%	
Adjacent Channel	+2MHz	-40		dBm	
	-2MHz	-38		dBm	
Transmit Power	+3MHz	-44		dBm	
	-3MHz	-35		dBm	

2.7.2 Receiver

Basic Data Rate

Table 2-9

Parameter	Min	Typ	Max	Unit	Test Conditions
Sensitivity		-90		dBm	25°C, Power Supply VBAT=5V 2441MHz
Co-channel Interference Rejection		-13		dB	
Adjacent Channel	+1MHz	+5		dB	
	-1MHz	+2		dB	
	+2MHz	+37		dB	
Interference Rejection	-2MHz	+36		dB	
	+3MHz	+40		dB	
	-3MHz	+35		dB	

Confidential

The information contained herein is the exclusive property of JIELI and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission of JIELI.

Enhanced Data Rate**Table 2-10**

Parameter		Min	Typ	Max	Unit	Test Conditions
Sensitivity			-90		dBm	25°C, Power Supply VBAT=5V 2441MHz
Co-channel Interference Rejection			-13		dB	
Adjacent Channel	+1MHz		+5		dB	
	-1MHz		+2		dB	
	+2MHz		+37		dB	
Interference Rejection	-2MHz		+36		dB	
	+3MHz		+40		dB	
	-3MHz		+35		dB	

Confidential

The information contained herein is the exclusive property of JIELI and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission of JIELI.

3、 Package Information

3.1 SOP16




Figure 3-1. AC6969A_SOP16 Package

3、Revision History

Date	Revision	Description
2020.03.14	V1.0	Initial Release
2021.11.22	V1.1	Update Bluetooth Vision and profiles, Update Audio characters

Confidential

The information contained herein is the exclusive property of JIELI and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission of JIELI.