


Technical Data Data Sheet N00848, Rev. B




MBRF20100CTR SCHOTTKY RECTIFIER



Features

- 175°C T_J operation
- Center tap configuration
- Low forward voltage drop
- High purity, high temperature epoxy encapsulation for enhanced mechanical strength and moisture resistance
- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability
- This is a Pb Free Device
- . All SMC parts are traceable to the wafer lot
- Additional testing can be offered upon request

Circuit Diagram



Applications

- Switching power supply
- Converters
- Free-Wheeling diodes
- Reverse battery protection

Maximum Ratings:

Characteristics	Symbol	Condition	Max.	Units	
Peak Repetitive Reverse Voltage	V_{RRM}	-			
Working Peak Reverse Voltage	V_{RWM}		100	V	
DC Blocking Voltage	V_R				
Average Rectified Forward Current	I _{F (AV)}	50% duty cycle @Tc=133°C, rectangular	10(Per Leg)	A	
		wave form	20(Per Device)		
Peak One Cycle Non-Repetitive	l	8.3ms, Half Sine pulse	150	Α	
Surge Current(Per Leg)	I _{FSM}	0.5itis, i iaii 5itie puise	130	_ ^	

Electrical Characteristics:

Characteristics	Symbol	Condition	Тур.	Max.	Units	
Forward Voltage Drop(Per Leg)*	V _{F1}	@ 5A, Pulse, T _J = 25 °C	0.76	0.80	V	
		@ 10A, Pulse, T _J = 25 °C	0.85	0.90	V	
	V_{F2}	@ 5A, Pulse, T _J = 125 °C	0.62	0.70	V	
		@ 10A, Pulse, T _J = 125 °C	0.70	0.80	V	
Reverse Current(Per Leg)*	I _{R1}	@V _R = rated V _R , T _J = 25 °C	0.002	1.0	mA	
	I _{R2}	@V _R = rated V _R , T _J = 125 °C	0.3	15	mA	
Repetitive peak reverse current	I _{RRM}	tp = 2 μs square F= 1 kHz	•	1	Α	
Junction Capacitance(Per Leg)	C⊤	$@V_R = 5V, T_C = 25 ^{\circ}C, f_{SIG} = 1MHz$	200	250	pF	
RSM Isolation Voltage (t = 1.0 second, R. H. < =30%, T _A = 25 °C)	Viso	Clip mounting, the epoxy body away from the heatsink edge by more than 0.110" along the lead direction.	-	4500	V	
,		Clip mounting, the epoxy body is inside the heatsink.	-	3500		
		Screw mounting, the epoxy body is inside the heatsink.	-	1500		

- China Germany Korea Singapore United States
 - http://www.smc-diodes.com sales@ smc-diodes.com •



Technical Data Data Sheet N00848, Rev. B

* Pulse width < 300 µs, duty cycle < 2%



Thermal-Mechanical Specifications:

Characteristics	Symbol	Condition	Specification	Units
Junction Temperature	TJ	-	-55 to +175	°C
Storage Temperature	T _{stg}	-	-55 to +175	°C
Typical Thermal Resistance Junction to Case	R _θ JC	DC operation	4.5	°C/W
Approximate Weight	wt	-	2	g
Case Style	ITO-220AB			

Ratings and Characteristics Curves




Fig.1-Typical Junction Capacitance

Fig.2-Typical Reverse Characteristics




Fig.3-Typical Instantaneous Forward Voltage Characteristics


- China Germany Korea Singapore United States
 - http://www.smc-diodes.com sales@ smc-diodes.com •



Technical Data Data Sheet N00848, Rev. B




Mechanical Dimensions ITO-220AB



SYMBOL	Millimeters				
STWIDUL	MIN.	TYP.	MAX.		
Α	4.30	4.50	4.70		
A1	1.10	1.30	1.50		
A2	2.80	3.00	3.20		
A3	2.50	2.70	2.90		
b	0.50	0.60	0.75		
b1	1.10	1.20	1.35		
b2	1.50	1.60	1.75		
b3	1.20	1.30	1.45		
b4	1.60	1.70	1.85		
С	0.50	0.60	0.75		
D	14.80	15.00	15.20		
E	9.96	10.16	10.36		
е		2.55			
e1		5.10			
H1	6.50	6.70	6.90		
L	12.70	13.20	13.70		
L1	1.60	1.80	2.00		
L2	0.80	1.00	1.20		
L3	0.60	0.80	1.00		
ΦP1(上□)	3.30	3.50	3.70		
ΦP2 (下口)	2.99	3.19	3.39		
Q	2.50	2.70	2.90		
Θ1		5°			
Θ2		4°			
Θ3		10°			
Θ4		5°			
Θ5		5°			

Tube Specification



Marking Diagram



Where XXXXX is YYWWL

MBR = Device Type F = Package type 20 = Forward Current (20A) 100 = Reverse Voltage (100V) CTR = Configuration

 SSG
 = SSG

 YY
 = Year

 WW
 = Week

 L
 = Lot Number

Cautions: Molding resin

Epoxy resin UL:94V-0

Ordering Information

Device	Package	Shipping
MBRF20100CTR	ITO-220AB (Pb-Free)	50 pcs/ tube

For information on tape and reel specifications, including part orientation and tape sizes, please refer to our tape and reel packaging specification.

- China Germany Korea Singapore United States
 - http://www.smc-diodes.com sales@ smc-diodes.com •

MBRF20100CTR



Technical Data Data Sheet N00848, Rev. B



DISCLAIMER:

- 1- The information given herein, including the specifications and dimensions, is subject to change without prior notice to improve product characteristics. Before ordering, purchasers are advised to contact the SMC Diode Solutions sales department for the latest version of the datasheet(s).
- 2- In cases where extremely high reliability is required (such as use in nuclear power control, aerospace and aviation, traffic equipment, medical equipment, and safety equipment), safety should be ensured by using semiconductor devices that feature assured safety or by means of users' fail-safe precautions or other arrangement.
- 3- In no event shall SMC Diode Solutions be liable for any damages that may result from an accident or any other cause during operation of the user's units according to the datasheet(s). SMC Diode Solution assumes no responsibility for any intellectual property claims or any other problems that may result from applications of information, products or circuits described in the datasheets.
- 4- In no event shall SMC Diode Solutions be liable for any failure in a semiconductor device or any secondary damage resulting from use at a value exceeding the absolute maximum rating.
- 5- No license is granted by the datasheet(s) under any patents or other rights of any third party or SMC Diode Solutions.
- 6- The datasheet(s) may not be reproduced or duplicated, in any form, in whole or part, without the expressed written permission of SMC Diode Solutions.
- 7- The products (technologies) described in the datasheet(s) are not to be provided to any party whose purpose in their application will hinder maintenance of international peace and safety nor are they to be applied to that purpose by their direct purchasers or any third party. When exporting these products (technologies), the necessary procedures are to be taken in accordance with related laws and regulations..