

SEA & LAND ELECTRONIC CORP.

WWW.SEALAND-PPTC.COM



ALPHA-TOP TECHNOLOGY CORP.

### APPROVAL SHEET

MODEL NO.:	SMD1210-025	
CUSTOMER:		
CUSTOMER'S API	PROVAL:	
AUTHODIZED OLO	NATURE (OT AMP	
AUTHORIZED SIG	NATURE/STAMP:	
DATE		

MANUFACTURER:

HEAD OFFICE:

13F.,No.120-10,Sec.3,Zhongshan Rd.,Zhonghe Dist.,New Taipei City 23544,Taiwan

Tel: 886-2-8221-2567 Fax:882-2-2225-7268

E-mail:service@chipfast.com.tw

China Branch:

Factory Building B)Shuangpeng,Weibu Village, Qiuchang Town, Huiyang District, Huizhou City, Guangdong Province, P.R.C.)

Tel: 86-752-3562001 Fax:86-752-3558696 E-mail:service@atpptc.com

Submitted by: Chung Cheng Approved by: YC Lin DATE: 2-Mar-22

SEA & LAND ELECTRONIC CORP.



## SMD1210-025

#### Features

- Surface Mount Devices
- Lead free device
- Surface Mount packaging
- for automated assembly

#### Applications

Almost anywhere there is a low voltage power supply, up to 30V and a load to be

h protected, including:

■ Computer mother board, Modem.■ Telecommunication equipments.

Alpha-Top (Sea&Land Alliance)

#### Performance Specification

	V		V				Maximum P <sub>d</sub> Time To Trip		Resistance		Agency Approval	
Model	Marking	▼ max	max	@25°C	@25°C	Max.	Current	Time	$\mathrm{Ri}_{\mathrm{min}}$	R1max	UL	Approvar TUV
		(Vdc)	(A)	(A)	(A)	(W)	(A)	(Sec)	$(\Omega)$	$(\Omega)$	UL	100
SMD1210-025	α <b>C</b>	30	100	0.25	0.50	0.6	8.0	0.02	0.400	4.500		

Ihold = Hold Current. Maximum current device will not trip in 25°C still air.

Itrip = Trip Current. Minimum current at which the device will always trip in 25°C still air.

Vmax = Maximum operating voltage device can withstand without damage at rated current (Imax).

Imax = Maximum fault current device can withstand without damage at rated voltage (Vmax).

Pd = Power dissipation when device is in the tripped state in 25°C still air environment at rated voltage.

Rimin/max = Minimum/Maximum device resistance prior to tripping at 25°C.

R1<sub>max</sub> = Maximum device resistance is measured one hour post reflow.

**CAUTION**: Operation beyond the specified ratings may result in damage and possible arcing and flame.

#### **Environmental Specifications**

Test	Conditions	Resistance change					
Passive aging	+85°C, 1000 hrs.	±5% typical					
Humidity aging	+85°C, 85% R.H., 168 hours	±5% typical					
Thermal shock	+85°C to -40°C, 20 times	±33% typical					
Resistance to solvent	MIL-STD-202,Method 215	No change					
Vibration	MIL-STD-202, Method 201	No change					
Ambient operating conditions : - 40 °C to +85 °C							
Maximum surface temperature of the device in the tripped state is 125 °C							

#### AGENCY APPROVALS:

Regulation/Standard:



2015/863/EU

HF

EN14582


#### I<sub>hold</sub> Versus Temperature

Inold Volume Tollipolate	u. 0									
Model		Maximum ambient operating temperature (T <sub>mao</sub> ) vs. hold current (I <sub>hold</sub> )								
Model	-40°C	-20°C	0°C	25°C	40°C	50°C	60°C	70°C	85°C	
SMD1210-025	0.34	0.31	0.28	0.25	0.21	0.19	0.17	0.15	0.12	

Construction And Dimension (Unit:mm)

Model	Model		В				D	E
Model	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Min.
SMD1210-025	3.00	3.43	2.35	2.80	0.40	0.90	0.30	0.10

#### **Dimensions & Marking**



**α** = Trademark

C = Part identification

# Recommended Pad Layout (mm) $1.0\pm0.1$ $1.0\pm0.1$ $1.0\pm0.1$ $1.0\pm0.1$ $1.0\pm0.1$ $1.0\pm0.1$

2.0±0.1

#### **Termination Pad Characteristics**

Terminal pad materials :

Tin-plated Nickel-Copper


Terminal pad solderability:

Meets EIA specification RS186-9E and ANSI/J-STD-002 Category 3.


#### Rework

Use standard industry practices, the removal device must be replaced with a fresh one.

#### **Thermal Derating Curve**




#### Typical Time-To-Trip At 25°C



# NARNING:

- · Use PPTC beyond the maximum ratings or improper use may result in device damage and possible electrical arcing and flame.
- PPTC are intended for protection against occasional over current or over temperature fault conditions and should not be used when repeated fault conditions or prolonged trip events are anticipated.
- · Device performance can be impacted negatively if devices are handled in a manner inconsistent with recommended electronic, thermal, and mechanical procedures for electronic components.
  · Use PPTC with a large inductance in circuit will generate a circuit voltage (L di/dt) above the rated voltage of the PPTC.
- Avoid impact PPTC device its thermal expansion like placed under pressure or installed in limited space.
- · Contamination of the PPTC material with certain silicon based oils or some aggressive solvents can adversely impact the performance of the devices. PPTC SMD can be cleaned by standard methods.
- Requests that customers comply with our recommended solder pad layouts and recommended reflow profile. Improper board layouts or reflow profile could negatively impact solderability performance of our devices.




- · Recommended reflow methods: IR, vapor phase oven, hot air oven.
- Devices are not designed to be wave soldered to the bottom side of the board.
- Recommended maximum paste thickness is 0.25 mm (0.010 inch).
- Devices can be cleaned using standard method and solvents.

Note: If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.


#### Tape And Reel Specifications (mm)

Coverning Specifications	EIA 481-2
Governing Specifications	
W	$8.0 \pm 0.20$
P0	$4.0 \pm 0.10$
P1	4.0 ± 0.10
P2	2.0 ± 0.10
A0	2.90± 0.20
B0	3.65± 0.20
B1max.	4.35
D0	1.5± 0.10
F	3.5 ± 0.10
E1	1.75 ± 0.10
E2min.	6
Tmax.	0.3
T1max.	0.06
K0	1.00 ± 0.1
Leader min.	390
Trailer min.	160
Reel Dimensions	
A max.	180
N min.	50
W1	9.00 ±2.00
W2max.	15

#### **EIA Tape Component Dimensions**



#### **EIA Reel Dimensions**



#### Storage And Handling

- Storage conditions : 40°C max, 70% R.H.
- Devices may not meet specified performance if storage conditions are exceeded.

# Order Information Packaging

SMD1210	025	Tape & Reel Quantity
Product name	Hold	
Size 3225 mm / 1210 inch	Current	4,500 pcs/reel
SMD: surface mount device	0.25A	

Tape & reel packaging per EIA481-1

#### Labeling Information

