

1. DESCRIPTION

These monolithic data selectors/multiplexers contain full on-chip binary decoding to select the desired data source.


The **XD74LS151** have a strobe input which must be at a low logic level to enable these devices. A high level at the strobe forces the W output high, and the Y output (as applicable) low.

The **XD74LS151** feature complementary W and Y outputs.


2. FEATURES

- Others Select One-of-Eight Data Sources
- All Perform Parallel-to-Serial Conversion
- All Permit Multiplexing from N Lines to One Line
- Also For Use as Boolean Function Generator
- Input-Clamping Diodes Simplify System Design
- Fully Compatible with Most TTL Circuits

3. PIN CONFIGURATIONS




4. LOGIC DIAGRAM



| INPUTS | | | | OUTPUTS | |
|--------|---|---|----------------|---------|-----------------|
| SELECT | | | STROBE | Y | W |
| C | B | A | \overline{G} | | |
| X | X | X | H | L | H |
| L | L | L | L | D0 | $\overline{D0}$ |
| L | L | H | L | D1 | $\overline{D1}$ |
| L | H | L | L | D2 | $\overline{D2}$ |
| L | H | H | L | D3 | $\overline{D3}$ |
| H | L | L | L | D4 | $\overline{D4}$ |
| H | L | H | L | D5 | $\overline{D5}$ |
| H | H | L | L | D6 | $\overline{D6}$ |
| H | H | H | L | D7 | $\overline{D7}$ |

5. SCHEMATICS OF INPUTS AND OUTPUTS



6. ABSOLUTE MAXIMUM RATINGS OVER OPERATING FREE-AIR TEMPERATURE RANGE (UNLESS OTHERWISE NOTES)

| | |
|--|----------------|
| Supply voltage, V_{CC} | 7V |
| Input voltage, V_I : 74LS151..... | 7V |
| Operating free-air temperature range: SOP package..... | 0°C to 70°C |
| DIP package..... | 0°C to 70°C |
| Storage temperature range, T_{stg} | -65°C to 150°C |

† Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

7. RECOMMENDED OPERATING CONDITIONS

| | | 74LS151 | | | UNIT |
|-----------------|--------------------------------|---------|-----|------|------|
| | | MIN | NOM | MAX | |
| V _{CC} | Supply voltage | 4.75 | 5 | 5.25 | V |
| I _{OH} | High-level output current | | | -400 | μA |
| I _{OL} | Low-level output current | | | 8 | mA |
| T _A | Operating free-air temperature | 0 | | 70 | °C |

8. ELECTRICAL CHARACTERISTICS OVER RECOMMENDED OPERATING FREE-AIR RANGE (UNLESS OTHERWISE NOTED)

| PARAMETER | | TEST CONDITIONS [†] | 74LS151 | | | UNIT |
|-----------------|---|--|------------------------|------------------|------|------|
| | | | MIN | TYP [‡] | MAX | |
| V _{IH} | High-level input voltage | | 2 | | | V |
| V _{IL} | Low-level input voltage | | | | 0.8 | V |
| V _{IK} | Input clamp voltage | V _{CC} = MIN, I _I = -18 mA | | | -1.5 | V |
| V _{OH} | High-level output voltage | V _{CC} = MIN, V _{IL} = 0.8 V, V _{IH} = 2 V, I _{OH} = -400 μA | 2.7 | 3.4 | | V |
| V _{OL} | Low-level output voltage | V _{CC} = MIN, V _{IH} = 2 V, V _{IL} = V _{IL} MAX | I _{OL} = 4 mA | 0.25 | 0.4 | V |
| | | | I _{OL} = 8 mA | 0.35 | 0.5 | |
| I _I | Input current at maximum input voltage | V _{CC} = MAX, V _I = 7 V | | | 0.1 | mA |
| I _{IH} | High-level input current | V _{CC} = MAX, V _I = 2.7 V | | | 20 | μA |
| I _{IL} | Low-level input current | V _{CC} = MAX, V _I = 0.4 V | | | -0.4 | mA |
| I _{OS} | Short-circuit output current [§] | V _{CC} = MAX | -20 | | -100 | mA |
| I _{CC} | Supply current | V _{CC} = MAX, Output open, All inputs at 4.5V | | 6.0 | 10 | mA |

[†] For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

[‡] All typical values are at V_{CC} = 5 V, T_A = 25°C.

[§] Not more than one output should be shorted at a time.

9. SWITCHING CHARACTERISTICS, VCC = 5 V, TA = 25°C

switching characteristics, VCC = 5 V, TA = 25°C

| PARAMETER† | FROM (INPUT) | TO (OUTPUT) | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|------------|-------------------------|-------------|--------------------------|-----|-----|-----|------|
| tPLH | A,B, or C (4 levels) | Y | CL = 15 pF, RL = 2 kΩ | | 27 | 43 | ns |
| tPHL | | | | | 18 | 30 | |
| tPLH | A,B, or C (3 levels) | W | | | 14 | 23 | ns |
| tPHL | | | | | 20 | 32 | |
| tPLH | Strobe G | Y | | | 26 | 42 | ns |
| tPHL | | | | | 20 | 32 | |
| tPLH | Strobe G | W | | | 15 | 24 | ns |
| tPHL | | | | | 18 | 30 | |
| tPLH | Any D | Y | | | 20 | 32 | ns |
| tPHL | | | | | 16 | 26 | |
| tPLH | Any D | W | | | 13 | 21 | ns |
| tPHL | | | | | 12 | 20 | |

† tPLH = propagation delay time, low-to-high-level output


tPHL = propagation delay time, high-to-low-level output

10. ORDERING INFORMATION

Ordering Information

| Part Number | Device Marking | Package Type | Body size (mm) | Temperature (°C) | MSL | Transport Media | Package Quantity |
|-------------|----------------|--------------|----------------|------------------|------|-----------------|------------------|
| XD74LS151 | XD74LS151 | DIP16 | 19.05 * 6.35 | -0 to 70 | MSL3 | Tube 25 | 1000 |

11. DIMENSIONAL DRAWINGS



[if you need help contact us. Xinluda reserves the right to change the above information without prior notice]