


## BAV99


DIODE

HIGH CONDUCTANCE ULTRA  
FAST DIODE


## ■ EQUIVALENT



For 3 Pin Package



For 6 Pin Package



## ■ ORDERING INFORMATION

Ordering Number	Package	Pin Assignment						Packing
		1	2	3	4	5	6	
BAV99G-AE3-R	SOT-23	K1	A2	K2A1	-	-	-	Tape Reel
BAV99G-AL3-R	SOT-323	K1	A2	K2A1	-	-	-	Tape Reel
BAV99G-AN3-R	SOT-523	K1	A2	K2A1	-	-	-	Tape Reel
BAV99G-AL6-R	SOT-363	A1	K1	A2K2	A2	K2	A1K1	Tape Reel

Note: Pin Assignment: A: Anode K: Cathode

	(1) R: Tape Reel (2) AE3: SOT-23, AL3: SOT-523, AN3: SOT-523, AL6: SOT-363 (3) G: Halogen Free and Lead Free
--	---

## ■ MARKING

SOT-23 / SOT-323 / SOT-523	SOT-363

■ ABSOLUTE MAXIMUM RATINGS ( $T_A = 25^\circ\text{C}$ , unless otherwise specified.)

PARAMETER		SYMBOL	RATINGS	UNIT
Working Inverse Voltage		$W_{IV}$	70	V
Average Rectified Current		$I_{F(AV)}$	200	mA
DC Forward Current		$I_{FM}$	600	mA
Recurrent Peak Forward Current		$I_{FRM}$	700	mA
Non-repetitive Peak	Pulse width = 1.0 second	$I_{FSM}$	1.0	A
Forward Surge Current	Pulse width = 1.0 microsecond		2.0	A
Power Dissipation	SOT-23	$P_D$	350	mW
	SOT-523		150	mW
	SOT-323/SOT-363		200	mW
Junction Temperature		$T_J$	+150	$^\circ\text{C}$
Storage Temperature		$T_{STG}$	-65 ~ +150	$^\circ\text{C}$

Notes: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged.

Absolute maximum ratings are stress ratings only and functional device operation is not implied.

2. These are steady state limits. The factory should be consulted on applications involving pulsed or low duty cycle operations.



■ THERMAL DATA

PARAMETER		SYMBOL	RATINGS	UNIT
Junction to Ambient	SOT-23	$\theta_{JA}$	357	$^\circ\text{C}/\text{W}$
	SOT-523		833	$^\circ\text{C}/\text{W}$
	SOT-323/SOT-363		625	$^\circ\text{C}/\text{W}$





■ ELECTRICAL CHARACTERISTICS ( $T_A = 25^\circ\text{C}$ , unless otherwise specified.)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Breakdown Voltage	$V_R$	$I_R = 100\mu\text{A}$	70			V
Maximum Instantaneous Forward Voltage	$V_{FM}$	$I_F = 1.0\text{mA}$			775	mV
		$I_F = 10\text{mA}$			855	mV
		$I_F = 50\text{mA}$			1.0	V
		$I_F = 150\text{mA}$			1.25	V
Peak Forward Voltage	$V_{SM}$	$I_F = 10\text{mA}, t_R = 20\text{nS}$			1.75	V
Maximum Instantaneous Reverse Current	$I_{RM}$	$V_R = 70\text{V}$ $V_R = 25\text{V}, T_A = 150^\circ\text{C}$ $V_R = 70\text{V}, T_A = 150^\circ\text{C}$			2.5 30 50	$\mu\text{A}$
Diode Capacitance	$C_O$	$V_R = 0, f = 1.0\text{MHz}$			1.5	pF
Reverse Recovery Time	$t_{RR}$	$I_F = I_R = 10\text{mA}, I_{RR} = 1.0\text{mA}$ $R_L = 100\Omega$			6.0	ns




■ TYPICAL CHARACTERISTICS



GENERAL RULE: The Reverse Current of a diode will approximately double for every ten (10) Degree C increase in Temperature



■ TYPICAL CHARACTERISTICS(Cont.)



UTC assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all UTC products described or contained herein. UTC products are not designed for use in life support appliances, devices or systems where malfunction of these products can be reasonably expected to result in personal injury. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice.