


Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE±0.05)





SPECIFICATIONS

Rated Current:1.0AMP  
Contact Resistance:20mΩ Max  
Withstand Voltage:500V AC/DC  
Insulation Resistance:1000MΩ Min  
Operation Temperature:-40°c to +105°c

Contact Material:Brass  
Contact Plating:Au or Sn Over Ni  
Insulator Material:Polyester(UL94V-0)  
Standard: PA6T  
Max.Processing Temp: 230°C for 30-60 seconds  
(260°C for 10 seconds)

Dimension antitheses list			
ITEM	PA	PC	L
Standard	3.80	2.30	7.10
Alternate			



**Ordering Information**

PZ 127 - \* - N - Z - \* - \*\*

No.of Rows  
1=Single Row  
2=Dual Row

No.of Pins  
2-40Pin

Type  
Z=直针  
#=斜针  
S=空船  
WS=弯插

Length  
(塑高)

Contact Plating  
G0:Gold Flash  
G1:1u" Gold  
G2:3u" Gold  
G3:5u" Gold  
G4:10u" Gold  
G5:15u" Gold  
G6:30u" Gold  
S0:Gold Flash/Tin  
S1:Tin

			GENREL TOLERANCE		制 图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核 CHECK		产品名称 TITLE	1.27双排 排针 直针(塑高1.0)	版本 REV.	A
			X.X	±0.30	批 准 APPROVAL		产品料号 PART NO.	PZ127-2-N-Z-1.0-XX(L7.1)	单 位 UNITS	mm
1	初版发行		X.XX	±0.20	比 例 SCALE		材 料 MATERIAL		页 次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X.XXX	±0.10	投 影 Projection					
			Angle	±3.0°						