



2:1

RoHS compliant
by exemption

| | | |
|-----------------|-----------------|--------------------------------------|
| 1727040155 | FMP006S103 | 103 |
| 1731120309 | FMP006S105 | 105 |
| 1731120840 | FMP006S106 | 106 |
| 1731120386 | FMP006S110 | 110 |
| 1731140625 | FMP006S133 | 133 |
| 1731120041 | FMP006S203 | 203 |
| 1731120152 | FMP006S204 | 204 |
| Material Number | FCT Part Number | Material + Finish See extra sheet |

| | | | | | | | | | | | | |
|---|---------------------------------------|-------|--|--|------------------------|---------|--------|-----------------|----------------|----------|----------|----------|
| UNLESS OTHERWISE SPECIFIED DIMENSIONS FOR REFERENCE ONLY | | | | REPLACEMENT FOR DOCUMENT NUMBER: FMP006S | | | | | | | | |
| THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION | | | | | | | | | | | | |
| FUNCTIONAL SYMBOLS | DIMENSION UNITS | SCALE | CURRENT REV DESC: | | | | | | | | | |
| $\frac{F}{A} = 0$ | mm | 5:1 | EC NO: 686935 DRWN: FVETTER 2021/11/29 CHK'D: MTEUBEL 2021/11/30 APPR: MTEUBEL 2021/11/30 | | | | | | | | | |
| $\frac{F}{E} = 0$ | GENERAL TOLERANCES (UNLESS SPECIFIED) | | | | | | | | | | | |
| $\frac{F}{P} = 0$ | ANGULAR TOL ± ° | | | | | | | | | | | |
| DIVISIONAL SYMBOLS | 4 PLACES | ± | | | | | | | | | | |
| | 3 PLACES | ± | INITIAL REVISION: | | | | | | | | | |
| | 2 PLACES | ± | DRWN: VLOKESHA 2021/03/31 | | | | | | | | | |
| | 1 PLACE | ± | APPR: MTEUBEL 2021/11/25 | | | | | | | | | |
| | 0 PLACES | ± | DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS | | FIRST ANGLE PROJECTION | DRAWING | SERIES | MATERIAL NUMBER | CUSTOMER | DOC TYPE | DOC PART | REVISION |
| | | | | | | A4-SIZE | 172704 | SEE TABLE | GENERAL MARKET | PSD | 000 | A1 |



FCT 20A HIGH POWER CONTACT FOR D-SUB

PRODUCT CUSTOMER DRAWING

| | | | | |
|-----------------|----|--------------|------------|----------|
| DOCUMENT STATUS | P1 | RELEASE DATE | 2021/11/30 | 09:44:57 |
|-----------------|----|--------------|------------|----------|