





注: 未经允许禁止传输、复制、编辑该文档, 以及利用其内容进行交流



REV	E.C.N NO.	CONTENT	CHK	DATE

NOTES1:

UL Standard

1. Use group	B	C	D
Rated Current	8A	/	8A
Rated Voltage	300V	/	300V

- 2. Torque value: M2.0, 1.77Lbin
- 3. Wire range: 28~16AWG

IEC Standard

1. Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	2.5KV	2.5KV	2.5KV
Rate Voltage(V)	160V	160V	250V
Rate Current(A)	7A	7A	7A

- 2. Torque value: M2, 0.2Nm
- 3. wire range: 0.2~1.5mm<sup>2</sup>

NOTES2:

- 1. Housing: PA66 (UL94V-0)
- 2. Cover: PA66 (UL94V-0)
- 3. Cage: Brass (Ni Plated)
- 4. Clamp: Copper alloy (Ni Plated)
- 5. Screw: Steel (M2.0, Zn Plated)

NOTES3:

- 1. Pitch: 3.5mm Poles: 02-24P
- 2. Stripping length: 6-7mm
- 3. Operating temperature: -40℃~+105℃
- 4. RoHS Compliance

How to order

MX15EDGK - 3.5 - XXP - XXXX - XX - X - X

产品型号      间距      极数      颜色      01:常规颜色      A-Z其他定制

灰色:GY    橙色:OE    02-99:      0:Y一字螺丝

蓝色:BU    红色:RD    定制颜色      1:S十字螺丝

黑色:BK    透明色:TT      Cu:铜方块      2:PS平头十字螺丝

绿色:GN    黄色:YW      Fe:铁方块

透明色:TT    白色:WE

Pitch Range In mm			Nominal Dimension Range In mm					—	∩	∇
TO	Over 6 TO	Over 10 TO	TO	Over 30 TO	Over 60 TO	Over 100 TO	Over 150	0.1/10		
6	10	24	30	60	100	150		<		
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°		

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG.	CKK	DATE	22.09.14	UNITS	MM
CHK.		DATE		SCALE	1:1
APP.		DATE			
CIXI MAIXU ELECTRONICS CO.,LTD.				NAME	
慈溪市迈旭电子有限公司				MX15EDGK-3.5-XXP	
DWGNO.					