

XL1513

Features

- Wide 3.6V to 18V Input Voltage Range
- Output Adjustable from 0.8V to 16V
- Maximum Duty Cycle 100%
- Minimum Drop Out 0.6V
- Fixed 380KHz Switching Frequency
- 2A Constant Output Current Capability
- Internal Optimize Power MOSFET
- High efficiency
- Excellent line and load regulation
- TTL shutdown capability
- EN pin with hysteresis function
- Built in thermal shutdown function
- Built in current limit function
- Built in output short protection function
- Available in SOP8L package

Applications

- LCD Monitor and LCD TV
- Digital Photo Frame
- Set-up Box
- ADSL Modem
- Telecom / Networking Equipment

General Description

The XL1513 is a 380KHz fixed frequency PWM buck (step-down) DC/DC converter, capable of driving a 2A load with high efficiency, low ripple and excellent line and load regulation. Requiring a minimum number of external components, the regulator is simple to use and include internal frequency compensation and a fixed-frequency oscillator.

The PWM control circuit is able to adjust the duty ratio linearly from 0 to 100%. An enable function, an over current protection function is built inside. When short protection function happens, the operation frequency will be reduced from 380KHz to 80KHz. An internal compensation block is built in to minimize external component count.



Figure 1. Package Type of XL1513



2A 380KHz	18V Buck	CDC to D	C Converter
ZA JOUNIL	IOV DUCE	ים טו טיט	

XL1513

Pin Configurations




Figure 2. Pin Configuration of XL1513 (Top View)

Table 1 Pin Description

Pin Number	Pin Name	Description				
3	NC	No Connected.				
4	VIN	upply Voltage Input Pin. XL1513 operates from a 3.6V to 18V OC voltage. Bypass Vin to GND with a suitably large capacitor of eliminate noise on the input.				
5,6	SW	Power Switch Output Pin (SW). Output is the switch node that supplies power to the output.				
7,8	GND	Ground Pin. Care must be taken in layout. This pin should be placed outside of the Schottky Diode to output capacitor ground path to prevent switching current spikes from inducing voltage noise into XL1513.				
1	FB	Feedback Pin (FB). Through an external resistor divider network, Feedback senses the output voltage and regulates it. The feedback threshold voltage is 0.8V.				
2	EN	Enable Pin. Drive EN pin low to turn off the device, drive it high to turn it on. Floating is default high.				



XL1513

Function Block




Figure 3. Function Block Diagram of XL1513

Typical Application Circuit

Efficiency




Figure 4. XL1513 Typical Application Circuit



2A 380KHz 18V Buck DC to DC Converter	XL1513

Ordering Information

Order Information	Marking ID	Package Type	Packing Type Supplied As
XL1513E1	XL1513E1	SOP8L	2500 Units on Tape & Reel

XLSEMI Pb-free products, as designated with "E1" suffix in the par number, are RoHS compliant.

Absolute Maximum Ratings (Note1)

Parameter	Symbol	Value	Unit
Input Voltage	Vin	-0.3 to 20	V
Feedback Pin Voltage	V_{FB}	-0.3 to Vin	V
EN Pin Voltage	V_{EN}	-0.3 to Vin	V
Output Switch Pin Voltage	V_{Output}	-0.3 to Vin	V
Power Dissipation	P_{D}	Internally limited	mW
Thermal Resistance (SOP8) (Junction to Ambient, No Heatsink, Free Air)	R_{JA}	100	°C/W
Operating Junction Temperature	T_{J}	-40 to 125	°C
Storage Temperature	T_{STG}	-65 to 150	°C
Lead Temperature (Soldering, 10 sec)	T_{LEAD}	260	°C
ESD (HBM)		2000	V

Note1: Stresses greater than those listed under Maximum Ratings may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operation is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.



XL1513

XL1513 Electrical Characteristics

 $T_a = 25$;unless otherwise specified.

Symbol	Parameter	Test Condition	Min.	Тур.	Max.	Unit
System parameters test circuit figure4						
VFB	Feedback	Vin = 7V to 18V, Vout=5V	0.776	0.8	0.824	V
VID	Voltage	Iload=0.2A to 2A				
Efficiency	n	Vin=12V ,Vout=5V		- 89	-	%
Efficiency	ŋ	Iout=2A	_			/0

Electrical Characteristics (DC Parameters)

Vin = 12V, GND=0V, Vin & GND parallel connect a 220uf/50V capacitor; Iout=500mA, T_a = 25 ; the others floating unless otherwise specified.

Parameters	Symbol	Test Condition	Min.	Тур.	Max.	Unit
Input operation voltage	Vin		3.6		18	V
Shutdown Supply Current	I_{STBY}	$V_{EN}=0V$		60	200	uA
Quiescent Supply Current	I_q	$V_{EN} = 2V,$ $V_{FB} = V_{in}$		3	5	mA
Oscillator Frequency	Fosc		323	380	437	Khz
Switch Current Limit	I_L	$V_{FB} = 0$		4		A
EN Pin Threshold	V_{EN}	High (Regulator ON) Low (Regulator OFF)		1.4 0.8		V
EN Pin Input Leakage	I_{H}	$V_{EN} = 2V (ON)$		1	15	uA
Current	I_{L}	$V_{EN} = 0V (OFF)$		1	15	uA
Max. Duty Cycle	D_{MAX}	V _{FB} =0V		100		%



XL1513

Test Circuit and Layout guidelines




Figure 5. Standard Test Circuits and Layout Guides

Select R1 to be approximately 2K, use a 1% resistor for best stability.

C1 and CFF are optional; in order to increase stability and reduce the input power line noise, CIN and C1 must be placed near to VIN and GND;

For output voltages greater than approximately 10V, an additional capacitor CFF is required. The compensation capacitor is typically between 100 pf and 33 nf, and is wired in parallel with the output voltage setting resistor, R2. It provides additional stability for high output voltage, low input-output voltages, and/or very low ESR output capacitors, such as solid tantalum capacitors.

CFF=1/(31*1000*R2); This capacitor type can be ceramic, plastic, silver mica, etc. (Because of the unstable characteristics of ceramic capacitors made with Z5U material, they are not recommended.)



XL1513

Schottky Diode Selection Table

Current	Surface	Through	VR (The same as system maximum input voltage)				
	Mount	Hole					
			20V	30V	40V	50V	60V
1A			1N5817	1N5818	1N5819		
				•			•
			1N5820	1N5821	1N5822		
			MBR320	MBR330	MBR340	MBR350	MBR360
3A			SK32	SK33	SK34	SK35	SK36
JA				30WQ03	30WQ04	30WQ05	
				31DQ03	31DQ04	31DQ05	
			SR302	SR303	SR304	SR305	SR306



XL1513

Typical System Application for $12V \sim 5V/2A$ Version




Figure 6. XL1513 System Parameters Test Circuit (12V ~ 5V/2A)

Typical System Application for 12V ~ 3.3V/2A




Figure 7. XL1513 System Parameters Test Circuit (12V ~ 3.3V/2A)



XL1513

Package Information

SOP8 Package Mechanical Dimensions

