

Electrical Specification @25°C

RoHS Compliant (PB Free)

Isolation: 2250VDC 0.5mA 60sec (UTP Side to Chip Side)

OCL: 350uH Minimum @100KHz 100mV with 8mADC Insertion Loss: −1.0dB Maximum @300KHz ~ 100MHz

Return Loss: -20dB Minimum @1MHz ~ 10MHz / -16dB Minimum @10MHz ~ 30MHz

-12dB Minimum @30MHz \sim 60MHz / -10dB Minimum @60MHz \sim 80MHz


Common Mode Rejection: −30dB Minimum @1MHz ~ 50MHz

−20dB Minimum @50MHz ~ 150MHz

Crosstalk: -40dB Minimum @1MHz ~ 30 MHz / -35dB Minimum @30MHz ~ 60 MHz

-30dB Minimum @60MHz ~ 100MHz

Schematics



Notes: Connect CHS GND to PCB Ground

REV.: 00 1 of 4

Address: No.16, Industrial Road Central, Industrial Zone, Xiaolan Town, Zhongshan City, Guangdong Province, China Tel: (0760)22126805 22132332 Fax: (0760)22132339 Post code: 528416

E-Mail: sales@hanrun.com http://www.hanrun.com


Specifications subject to change without notice. Refer to the approval sheet for lastly edition.




- RoHS Compliant (PB Free)
- Meets or Exceeds IEEE802.3 standards including 350uH Min OCL with 8mADC
- High performance for EMI suppression, Crosstalk, Return Loss and Consistent Electrical
- Minimum 2250VDC isolation per IEEE802.3 requirement
- Minimize PCB space and Simplify PCB Layout
- Less magnetic components to be placed on PCB, higher reliability and yields
- UL Recognized Component: File # E330599

Mechanical Dimensions:






(Side View)



(Bottom View)



Dimensions in mm

Unless otherwise specified, Tolerance: .xx ± 0.25

REV.: 00


Address: No.16, Industrial Road Central, Industrial Zone, Xiaolan Town, Zhongshan City, Guangdong Province, China Tel: (0760)22126805 22132332 Fax: (0760)22132339 Post code: 528416

E-Mail: sales@hanrun.com http://www.hanrun.com

Specifications subject to change without notice. Refer to the approval sheet for lastly edition.




PCB Layout:



Recommended PCB layout (Component Side View) All dimension tolerance are ± 0.08 unless otherwise specified

Suggested Panel Cutout:



SUGGESTED PANEL OPENING

Dimensions in mm

Unless otherwise specified, Tolerance: .xx ± 0.25

REV.: 00 3 of 4

> Address: No.16, Industrial Road Central, Industrial Zone, Xiaolan Town, Zhongshan City, Guangdong Province, China Tel: (0760)22126805 22132332 Fax: (0760)22132339 Post code: 528416

E-Mail: sales@hanrun.com http://www.hanrun.com

Specifications subject to change without notice. Refer to the approval sheet for lastly edition.



Material Specification:

Housing: PA66 GF Black UL94V-0

Shield: 30u" Nickel over 0.20mm Thickness Brass

Insert: PBT GF Black UL94V-0

Phosphor Bronze 0.35mm Thickness
Plating Area, 30u" gold over, 50u" nickel
Solder Area, 100u" tin over, 50u" nickel

Mechanical Performance:

Mating force: 5 lbs Maximum Unmating force: 5 lbs Maximum

Plug to Jack Retention force: 20 lbs Minimum

Operating life: 750 Cycles Minimum

Operating and Storage Temperature:

Operating Temperature Range: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$ Storage Temperature Range: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$