


客户图

NO.	ECN NO.	DESCRIPTION	DATE



Note:

- Material (材料):
 - Barrel: Brass C6801 (针管: 无铅铜 C6801)
 - Plunger: Brass C6801 (针头: 无铅铜 C6801)
 - Spring: SUS304 (弹簧: SUS304)
- Plating (电镀):
 - Barrel: 3u' Au over 50~80u' Ni (针管: 镀金3u', 镍底50~80u'.)
 - Plunger: 3u' Au over 50~80u' Ni (针头: 镀金3u', 镍底50~80u'.)
 - Spring: No plated (弹簧: 不电镀)
- Electrical (电气特性):
 - Rated Current & Voltage: DC 12V; 2A (额定电压&电流: 直流12V, 2A)
 - Contact Resistance: 50 mohm Max. at working height. (接触电阻: 最大50毫欧 (在工作高度状态下))
- Mechanical (机械性能):
 - Force: 40g \pm 20% at working height. (40g \pm 20% 在工作高度)。
 - Durability: 10,000 cycles (min) (寿命: 10000次)
- Work Temperature (工作环境):
 - Withstanding Higt Temperature: 280°C
 - Operational Temperature: -20°C ~ +70°C

深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL: 0755-28773277 FAX: 0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2022.9.24	VER.	A.1

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH		ANGLE	
X.XX	$\pm 0.05\text{mm}$	X.XX	$\pm 0.5^\circ$
X.X	$\pm 0.10\text{mm}$	X.X	$\pm 1.0^\circ$
X.	$\pm 0.20\text{mm}$	X.	$\pm 2.0^\circ$

DESIGNED BY:		DWG. NO.	YZ08415060P-02
CHECKED BY:		TITLE:	Pogo pin连接器
APPROVED BY:			