


	TABLE	OF CO	NTEN	TS
SHEET NO.		SHEET D	ESCRIPT	ION
1		NOTES	AND BO	M
2		CONFIG	SURATIO	NS
3		KEY CON	FIGURAT	IONS
4	RECE	PTACLE CO	NNECTO	R ASSEMBLY



160080 SERIES



160078 SERIES



160076 SERIES

RELEASE DATE | 2021/04/08

DOCUMENT STATUS P1

## NOTES: VALID UNLESS OTHERWISE SPECIFIED

13

#### 1. GENERAL:

14

a. APPLICATION SPECIFICATION SEE: 1601110001-AS

-CONTAINS: PRODUCT INTRODUCTION, PRODUCT SUMMARY,
CONNECTOR ASSEMBLY, PACKAGING INFORMATION, CONNECTOR
MATING, SERVICE INSTRUCTIONS, ELECTRICAL CONTINUITY
CHECKING, CRIMPING, AND TROUBLESHOOTING.
-DESIGNED TO MATE WITH DEVICE OR CONNECTOR AS SPECIFIED
IN THE MATING INTERFACE/CONNECTOR DRAWINGS CHART.
\*DENOTES DRAWINGS THAT CAN BE ACCESED AT http://ewcap.uscarteams.org/.
-ASSEMBLY SHIPPED WITH PLR IN PRE-LOCK POSITION
(SEE PLR PRE-LOCK VIEW SHEET 4).

#### b. PRODUCT SPECIFICATION SEE: 1600760001-PS


CONTAINS: SCOPE, PRODUCT DESCRIPTION, INTEGRAL COMPONENTS AND ACCESSORIES, APPLICABLE DOCUMENTS AND SPECIFICATIONS, RATINGS, PERFORMANCE, PACKAGING, GAUGES AND FIXTURES, AND OTHER INFORMATION

11

- c. PACKAGING SPECIFICATION PER MOLEX DRAWING: SEE PACKAGING CHART d. PARTS MUST BE IN COMPLIANCE TO MOLEX CHEMICAL SUBSTANCES FOR
- PRODUCTS AND PACKAGING SPECIFICATION: QEHS-699000-300
- e. DATA MUST BE SUBMITTED UNDER THE MOLEX PART NUMBER TO IMDS (COMPANY ID#13255)
- 2. DESIGN MATERIALS:
- a. SEE BOM TABLE IN SD-160076-0002
- 3. DESIGN GEOMETRY:
- a. THE 3-D CAD DATA IS BASIC (WITHOUT TOLERANCE) AND MASTER FOR THIS PART WITH THE EXCEPTION OF UNDERLINED DIMENSIONS, DIMENTIONAL INFORMATION NOT SHOWN ON THIS DRAWING IS DEFINED BY THE DATA FILE AT ITS LATEST REVISION.
- b. GEOMETRIC DIMENSIONS AND TOLERANCES PER ASME Y14.5M-2009
- c. EDGES AND UNDIMENSIONED DETAILS PER ISO13715
- d. CORNERS SHOWN AS SHARP TO BE R 0.2 MAX.
- e. LETTERING SHALL BE 0.15 MAX RAISED IN 0.25 MAX RECESS PAD.
- THIS INCLUDES RECYCLING CODE, CAVITY ID, VENDOR IDENTIFICATION.
- f. VISUAL DEFECTS SHALL MEET COSMETIC STANDARD PS-45499-002 (Class B).
- g. LASER MARKING: 1. PART NUMBER
- 2. DAY OF THE YEAR
- 3. MACHINE NO.
- 4. YEAR
- 4. 1 EAR
- FOR ADDITIONAL INFORMATION REFERENCE SECTION 5 UNDER PROCEDURES IN ES-34735-008.


PACKAGIN	IG
DESCRIPTION	DRAWING NO.
10 WAY HYBRID (1.5/2.8)	PK-31300-903
8 WAY HYBRID (1.5/6.3)	PK-31300-903
9 WAY HYBRID (1.5/2.8/6.3)	PK-31300-903


MATING INTERF	ACE/CONNECTOR	DRAWINGS
DESCRIPTION	INTERFACE DEFINITION	MOLEX INLINE
10 WAY HYBRID (1.5/2.8)	999-S-010-2-Z01	SD-160077-0001
8 WAY HYBRID (1.5/6.3)	999-S-008-2-Z01	SD-160077-0001
9 WAY HYBRID (1.5/2.8/6.3)	999-S-009-2-Z01	SD-160077-0001



	A8	UPDATED VIEWS IN SHEET 5	<u>ן</u> כ
	A7	ADDED INTERFACE DRAWINGS IN SHEETS 5,6,7	
	A6	UPDATED VIEWS & GENERAL NOTES	
	A5	UPDATED DRAWING ALONG WITH NEW MODELS	
	A4	MIGRATED DOCUMENT FROM HISTORY	
	A3	UPDATE KEYING STRATEGY	
	A2	UPDATE DIMENSION 3	
INSPECTION NUMBER LOG	A1	UPDATE PACKAGING DRAWINGS	
LAST NUMBER: 5 ADDED:	Α	RELEASE OK TO TOOL	
REMOVED:	REV	REV DESCRIPTION	
			4


					F	REMOVE	D:		REV	REV	DESCRIP	ΓΙΟΝ	
SYMBOLS			ORMATION TH	HAT IS PROPRII	ETARY TO MOLEX	ELECTRON	IIC TEC	CHNOLOGIES, LLC A	ND SHO	OULD NOT BE USED	WITHOUT WE	RITTEN PER	RMISSION
	DIMENSION UNITS	SCALE	CURREN <sup>®</sup>	T REV DES	C:								
= 0	mm	2:1							n	nol	ex		
= 0	GENERAL TOL (UNLESS SF												,
= 0	ANGULAR TOL	± 3.0 °	EC NO:	660404						CPT DUAL R			
<b>S</b> = 0	4 PLACES	±		ATEEGU		2021/0			ROW S	SEALED ASS	EMBLY MA	AT SEA	L
<b>////</b> = 0	3 PLACES	+	CHK'D:	KBORUS	SZEWSKI	2021/0	4/08						
0		-	APPR:	KBORUS	SZEWSKI	2021/0	4/08	PR	RODU	CT CUSTOM	ER DRAW	ING	
<u></u>	2 PLACES	± 0.1	INITIAL	REVISIO	N:			DOCUMENT NUMBER	₹		DOC TYPE	DOC PART	REVISION
= 0	1 PLACE	± 0.2	DRWN:	APROFF	ITT	2015/0	)1/29	CD 46	2005	76 0004	DOD	004	۸٥
	0 PLACES	±	APPR:	VKOSHY	•	2015/0	)5/21	2D-10		76-0001	PSD	001	A8
= 0	DRAFT WHERE A	APPLICABLE	THIRD ANGLE	PROJECTION	DRAWING	SERIE	S	MATERIAL NUMBER		CUSTOMER		SHEET I	NUMBER
<u>~</u> = 0	MUST RE WITHIN DIME				A1-SIZE	1600	76	SEE NOTE	2a.	GENERAL I	MARKET	1 C	)F 7
7		6		E	1			2		2		4	








CHARTED DIMENSIONS								
DESCRIPTION	DIMENS	SIONS						
DESCRIPTION	L	М						
10 WAY HYBRID (1.5/2.8)	15.82	13.82						
8 WAY HYBRID (1.5/6.3)	15.82	13.82						
9 WAY HYBRID (1.5/2.8/6.3)	15.82	13.82						

0)/MD/	OL 0	THIS DRAWING O	CONTAINS INF	ORMATION TH	HAT IS PROPRI	ETARY TO MOLEX	ELECTRONIC TEC	CHNOLOGIES, LLC AND SH	OULD NOT BE USED WI	THOUT WR	ITTEN PER	RMISSION	
SYMBO	JLS —	DIMENSION UNITS			T REV DES								В
=	0	mm	2.5:1						nole	X			
<b>E</b> =	0	GENERAL TOI (UNLESS SI						_					
=	0	ANGULAR TOL		EC NO:	660404				RCPT DUAL ROW	_			
<u></u> \$/=	0	4 PLACES	±		ATEEGU		2021/04/08		SEALED ASSEM	BLY MA	AT SEA	L	
<b>///// =</b>	0	3 PLACES	±		KBORUS	_	2021/04/08		-				
	U		0.4	APPR:	KBORUS	SZEWSKI	2021/04/08	PRODU	JCT CUSTOMER	DRAW	ING		
	0	2 PLACES	± 0.1	INITIAL	REVISIO	N:		DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION	
<b>=</b>	0	1 PLACE	± 0.2	DRWN:	<b>APROFF</b>	ITT	2015/01/29	CD 4600	76 0004	DOD	004		Α
	_	0 PLACES	±	APPR:	VKOSHY	•	2015/05/21	SD-1600	76-0001	PSD	001	A8	
=	0	DRAFT WHERE	APPLICABLE	THIRD ANGLI	E PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	'	SHEET I	NUMBER	
<u></u>	0	MUST RE WITHIN DIME				A1-SIZE	160076	SEE NOTE 2a.	GENERAL MA	RKET	3 C	)F 7	










# MX150 1.5/6.3 HYBRID 8 WAY RECEPTACLE SEALED ASSEMBLY MAT SEAL BOM AND PIN OUT SHEET




ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A1-BLK	HOUSING KEYING OPTION A	BLACK	PA6 GF40
B1-LG	HOUSING KEYING OPTION B	LIGHT GRAY	PA6 GF40
C1-DG	HOUSING KEYING OPTION C	DARK GRAY	PA6 GF40
D1-SG	HOUSING KEYING OPTION D	STONE GRAY	PA6 GF40
A1-BLK-CLIP	HOUSING KEYING OPTION A WITH CLIPSLOT	BLACK	PA6 GF40
B1-LG-CLIP	HOUSING KEYING OPTION B WITH CLIPSLOT	LIGHT GRAY	PA6 GF40
C1-DG-CLIP	HOUSING KEYING OPTION C WITH CLIPSLOT	DARK GRAY	PA6 GF40
D1-SG-CLIP	HOUSING KEYING OPTION D WITH CLIPSLOT	STONE GRAY	PA6 GF40
GCP	GROMMET CAP (PLUGGED)	BLACK	PA6 GF40
GCO	GROMMET CAP (OPEN)	BLACK	PA6 GF40
PLR	PLR	NATURAL	PA6 GF40
CPA	CPA	RED	PBT GF20
M	MAT SEAL	LIGHT BLUE	INHERENTLY LUBRICATED SILICONE
R	RING SEAL	GREEN	INHERENTLY LUBRICATED SILICONE

FOR ADDITIONAL INFORMATION SEE SD-160076-0001

PRIMARY LOCK REINFORCEMENT (PLR)

			(	COMPONEN	IT						BLOCKED	TERMINALS							
ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	THE PRESENCE	OF AN ABBREV	IATION IND		PRESENCE	OF THAT						D TERMINAL N TERMINAL			STATUS	COMMENTS	OPTIONAL ATTATCH	MENTS SOLD SEPERATELY
		HOUSING KEY/COLOR	GROMMET CAP	PLR	СРА	MAT SEAL	. RING SEAL	1	2	3	4	5	6	7	8				BACKSHELL WITHOUT RIBS
KEY A, BLACK, W/O CPA	160078-3001	A1-BLK	GCO	PLR		М	R									SALEABLE		TBD	TBD
KEY B, LIGHT GRAY, W/O CPA	160078-3002	B1-LG	GCO	PLR		М	R									SALEABLE		TBD	TBD
KEY C, DARK GRAY, W/O CPA	160078-3003	C1-DG	GCO	PLR		М	R									SALEABLE		TBD	TBD
KEY D, STONE GRAY, W/O CPA	160078-3004	D1-SG	GCO	PLR		М	R									SALEABLE		TBD	TBD
VOID KEY	160078-3005	$>\!\!<$	$\sim$	$>\!<$	> <	> <	> <	> <	> <	$\overline{}$	> <	$\overline{}$	$\overline{}$	$\overline{}$					$\sim$
KEY A, BLACK, W/ CPA	160078-3006	A1-BLK	GCO	PLR	CPA	М	R									SALEABLE		TBD	TBD
KEY B, LIGHT GRAY, W/ CPA	160078-3007	B1-LG	GCO	PLR	CPA	М	R									SALEABLE		TBD	TBD
KEY C, DARK GRAY, W/ CPA	160078-3008	C1-DG	GCO	PLR	CPA	М	R									SALEABLE		TBD	TBD
KEY D, STONE GRAY, W/ CPA	160078-3009	D1-SG	GCO	PLR	CPA	М	R									SALEABLE		TBD	TBD
VOID KEY	160078-3010	$>\!\!<$	$\sim$	> <	> <	> <	> <	> <	> <	> <	> <	$\overline{}$	$\overline{}$	> <				$\sim$	
KEY A, BLACK, W/ CLIPSLOT, W/O CPA	160078-3011	A1-BLK-CLIP	GCO	PLR		M	R									SALEABLE		TBD	TBD
KEY B, LIGHT GRAY, W/ CLIPSLOT, W/O CPA	160078-3012	B1-LG-CLIP	GCO	PLR		М	R									SALEABLE		TBD	TBD
KEY C, DARK GRAY, W/ CLIPSLOT, W/O CPA	160078-3013	C1-DG-CLIP	GCO	PLR		M	R									SALEABLE		TBD	TBD
KEY D, STONE GRAY, W/ CLIPSLOT, W/O CPA	160078-3014	D1-SG-CLIP	GCO	PLR		M	R									SALEABLE		TBD	TBD
VOID KEY	160078-3015	$>\!\!<$	$>\!\!<$	${}$	$\boxtimes$	$\supset \subset$	$\supset <$	$>\!\!<$	$\supset \subset$	$\supset <$	$>\!\!<$	$>\!\!<$	$\searrow$	$>\!\!<$	$\searrow$		$\sim$	>><	$\sim$
KEY A, BLACK, W/ CLIPSLOT, W/ CPA	160078-3016	A1-BLK-CLIP	GCO	PLR	CPA	М	R									SALEABLE		TBD	TBD
KEY B, LIGHT GRAY, W/ CLIPSLOT, W/ CPA	160078-3017	B1-LG-CLIP	GCO	PLR	CPA	М	R									SALEABLE		TBD	TBD
KEY C, DARK GRAY, W/ CLIPSLOT, W/ CPA	160078-3018	C1-DG-CLIP	GCO	PLR	CPA	М	R									SALEABLE		TBD	TBD
KEY D, STONE GRAY, W/ CLIPSLOT, W/ CPA	160078-3019	D1-SG-CLIP	GCO	PLR	CPA	М	R									SALEABLE		TBD	TBD
VOID KEY	160078-3020	$>\!\!<$	$>\!\!<$	$\geq$	$\times$	$\times$	$>\!\!<$	$\sim$	$\searrow$	$>\!\!<$	$>\!\!<$	$>\!\!<$	$>\!\!<$	$\times$	$\searrow$		$\bigvee$	>>	>>
KEY A, BLACK, W/ CPA	160078-3021	A1-BLK	GCO	PLR	CPA	М	R							7		SALEABLE		TBD	TBD
KEY A, BLACK, W/ CPA	160078-3022	A1-BLK	GCP	PLR	CPA	М	R			3	4	5	6			SALEABLE		TBD	TBD
KEY A, BLACK, W/ CPA	160078-3023	A1-BLK	GCP	PLR	CPA	М	R	1	2	3	4	5	6			SALEABLE		TBD	TBD
KEY B, LIGHT GRAY, W/ CPA	160078-3024	B1-LG	GCP	PLR	CPA	М	R			3	4	5	6			SALEABLE		TBD	TBD
KEY A, BLACK, W/ CLIPSLOT, W/ CPA	160078-3025	A1-BLK-CLIP	GCP	PLR	CPA	М	R	1	2	3						SALEABLE		TBD	TBD
KEY C, DARK GRAY, W/O CPA	160078-3026	C1-DG	GCP	PLR		М	R				4	5	6			SALEABLE		TBD	TBD
KEY A, BLACK, W/ CPA	160078-3027	A1-BLK	GCP	PLR	CPA	М	R	1				5	6			SALEABLE		TBD	TBD
KEY A, BLACK, W/ CPA	160078-3028	A1-BLK	GCP	PLR	CPA	М	R				4	5	6			SALEABLE		TBD	TBD
KEY A, BLACK, W/ CPA	160078-3029	A1-BLK	GCP	PLR	CPA	М	R	1	2	3						SALEABLE		TBD	TBD


### MX150 1.5/2.8/6.3 HYBRID 9 WAY RECEPTACLE SEALED ASSEMBLY MAT SEAL BOM AND PIN OUT SHEET



			(	COMPONEN	T						BLO	CKED TERMII	NALS							
ASSEMBLY DESCRIPTION	ASSEMBLY PART	THE PRESENCE	OF AN ABBREV	IATION IND		PRESENCE	OF THAT			AVITY WITH A							STATUS	COMMENTS	OPTIONAL ATTATCHI	MENTS SOLD SEPERATELY
	1.0.11.2.11	HOUSING KEY/COLOR	GROMMET CAP	PLR	СРА	MAT SEAL	RING	1	2	3	4	5	6	7	8	9			BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
KEY A, BLACK, W/O CPA	160080-3001	A1-BLK	GCO	PLR		М	R										SALEABLE		TBD	TBD
KEY B, LIGHT GRAY, W/O CPA	160080-3002	B1-LG	GCO	PLR		M	R										OK TO TOOL		TBD	TBD
KEY C, DARK GRAY, W/O CPA	160080-3003	C1-DG	GCO	PLR		M	R										OK TO TOOL		TBD	TBD
KEY D, STONE GRAY, W/O CPA	160080-3004	D1-SG	GCO	PLR		M	R										OK TO TOOL		TBD	TBD
VOID KEY	160080-3005	$>\!\!<$	$>\!\!<$	$\times$	$\times$	$\supset$	$\times$	$\times$	$\times$	$\searrow$	$\times$	$>\!\!<$	$\times$	$\times$	$>\!\!<$	X		$\bigvee$	$\sim$	>>
KEY A, BLACK, W/ CPA	160080-3006	A1-BLK	GCO	PLR	CPA	M	R										SALEABLE		TBD	TBD
KEY B, LIGHT GRAY, W/ CPA	160080-3007	B1-LG	GCO	PLR	CPA	М	R										OK TO TOOL		TBD	TBD
KEY C, DARK GRAY, W/ CPA	160080-3008	C1-DG	GCO	PLR	CPA	М	R										OK TO TOOL		TBD	TBD
KEY D, STONE GRAY, W/ CPA	160080-3009	D1-SG	GCO	PLR	CPA	M	R										OK TO TOOL		TBD	TBD
VOID KEY	160080-3010	$>\!\!<$	$>\!\!<$	$>\!\!<$	$\geq \leq$	$>\!\!<$	$\geq \leq$	$\geq \leq$	$>\!\!\!<$	$\supset\!$	$>\!\!<$	$\geq \leq$	$>\!\!<$	$>\!\!<$	$>\!\!<$	$\times$		$\sim$	$>\!\!<$	$>\!\!<$
KEY A, BLACK, W/ CLIPSLOT, W/O CPA	160080-3011	A1-BLK-CLIP	GCO	PLR		M	R										SALEABLE		TBD	TBD
KEY B, LIGHT GRAY, W/ CLIPSLOT, W/O CPA	160080-3012	B1-LG-CLIP	GCO	PLR		M	R										OK TO TOOL		TBD	TBD
KEY C, DARK GRAY, W/ CLIPSLOT, W/O CPA	160080-3013	C1-DG-CLIP	GCO	PLR		M	R										OK TO TOOL		TBD	TBD
KEY D, STONE GRAY, W/ CLIPSLOT, W/O CPA	160080-3014	D1-SG-CLIP	GCO	PLR		M	R										OK TO TOOL		TBD	TBD
VOID KEY	160080-3015	$>\!\!<$	$>\!\!<$	$\geq \leq$	$\geq \leq$	$>\!\!<$	$\geq \leq$	$\geq \leq$	$>\!\!\!<$	$\supset\!$	$>\!\!<$	$\geq \leq$	$>\!\!<$	$\geq \leq$	$>\!\!<$	$\times$		$\sim$	$>\!\!<$	$>\!\!<$
KEY A, BLACK, W/ CLIPSLOT, W/ CPA	160080-3016	A1-BLK-CLIP	GCO	PLR	CPA	M	R										SALEABLE		TBD	TBD
KEY B, LIGHT GRAY, W/ CLIPSLOT, W/ CPA	160080-3017	B1-LG-CLIP	GCO	PLR	CPA	M	R										OK TO TOOL		TBD	TBD
KEY C, DARK GRAY, W/ CLIPSLOT, W/ CPA	160080-3018	C1-DG-CLIP	GCO	PLR	CPA	M	R										OK TO TOOL		TBD	TBD
KEY D, STONE GRAY, W/ CLIPSLOT, W/ CPA	160080-3019	D1-SG-CLIP	GCO	PLR	CPA	M	R										OK TO TOOL		TBD	TBD
VOID KEY	160080-3020	$>\!\!<$	$>\!\!<$	$\searrow$	$>\!\!<$	$\supset\!$	$>\!\!<$	$\geq \leq$	$\supset\!$	$\supset\!$	$\searrow$	$\geq \leq$	$>\!\!<$	$\geq \leq$	$\geq \leq$	$>\!\!<$		$\sim$	$>\!\!<$	>
KEY A, BLACK, W/ CPA	160080-3021	A1-BLK	GCO	PLR	CPA	M	R									9	OK TO TOOL		TBD	TBD
KEY A, BLACK, W/ CPA	160080-3022	A1-BLK	GCP	PLR	CPA	М	R		2		4	5	6				OK TO TOOL		TBD	TBD

EC: 677478 DOCUMENT NO.: E-160076-0002 REVISION:B11 10/11/2021 PAGE: 1 OF 1

#### MX150 1.5/6.3 HYBRID 10 WAY RECEPTACLE SEALED ASSEMBLY MAT SEAL **BOM AND PIN OUT SHEET**



ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A1-BLK	HOUSING KEYING OPTION A	BLACK	PA6 GF40
B1-LG	HOUSING KEYING OPTION B	LIGHT GRAY	PA6 GF40
C1-DG	HOUSING KEYING OPTION C	DARK GRAY	PA6 GF40
D1-SG	HOUSING KEYING OPTION D	STONE GRAY	PA6 GF40
A1-BLK-CLIP	HOUSING KEYING OPTION A WITH CLIPSLOT	BLACK	PA6 GF40
B1-LG-CLIP	HOUSING KEYING OPTION B WITH CLIPSLOT	LIGHT GRAY	PA6 GF40
C1-DG-CLIP	HOUSING KEYING OPTION C WITH CLIPSLOT	DARK GRAY	PA6 GF40
D1-SG-CLIP	HOUSING KEYING OPTION D WITH CLIPSLOT	STONE GRAY	PA6 GF40
GCP	GROMMET CAP (PLUGGED)	BLACK	PA6 GF40
GCO	GROMMET CAP (OPEN)	BLACK	PA6 GF40
PLR	PLR	NATURAL	PA6 GF40
CPA	CPA	RED	PBT GF20
M	MAT SEAL	LIGHT BLUE	INHERENTLY LUBRICATED SILICONE
R	RING SEAL	GREEN	INHERENTLY LUBRICATED SILICONE

EOR ADDITIONAL	INICORMATION SEE	SD-160076-000

ASSEMBLY DESCRIPTION		COMPONENT  THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.						BLOCKED TERMINALS  CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION										STATUS	COMMENTS		
	ASSEMBLY PART NUMBER																			OPTIONAL ATTATCHMENTS SOLD SEPERATELY	
		HOUSING KEY/COLOR	GROMMET CAP	PLR	СРА	MAT SEAL	RING SEAL	1	2	3	4	5	6	7	8	9	10			BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
KEY A, BLACK, W/O CPA	160076-5001	A1-BLK	GCO	PLR		M	R											SALEABLE		TBD	TBD
KEY B, LIGHT GRAY, W/O CPA	160076-5002	B1-LG	GCO	PLR		M	R											SALEABLE		TBD	TBD
KEY C, DARK GRAY, W/O CPA	160076-5003	C1-DG	GCO	PLR		M	R											SALEABLE		TBD	TBD
KEY D, STONE GRAY, W/O CPA	160076-5004	D1-SG	GCO	PLR		M	R											SALEABLE		TBD	TBD
VOID KEY	160076-5005	$>\!\!<$	$\searrow$	${}$	$\supset$	$\supset \!$	$\supset \!$	$\supset \!$	$\supset$	$\supset \!$	$\supset \subset$	$\supset \subset$	$\searrow$	$\supset \!$	$\supset \subset$	$\geq$	$\supset \!$		$\backslash\!\!\!/$	$\sim$	$\sim$
KEY A, BLACK, W/ CPA	160076-5006	A1-BLK	GCO	PLR	CPA	M	R											SALEABLE		TBD	TBD
KEY B, LIGHT GRAY, W/ CPA	160076-5007	B1-LG	GCO	PLR	CPA	M	R											SALEABLE		TBD	TBD
KEY C, DARK GRAY, W/ CPA	160076-5008	C1-DG	GCO	PLR	CPA	M	R											SALEABLE		TBD	TBD
KEY D, STONE GRAY, W/ CPA	160076-5009	D1-SG	GCO	PLR	CPA	M	R											SALEABLE		TBD	TBD
VOID KEY	160076-5010	$>\!\!<$	$\sim$	${}$	$\supset$	$\supset \subset$	$\supset \subset$	$\supset <$	$\supset \subset$	$\supset \subset$	$\longrightarrow$	$\sim$	$\geq$	$\supset \!$	$\searrow$	$\geq$	$\overline{}$		$\sim$	$\sim$	$\sim$
KEY A, BLACK, W/ CLIPSLOT, W/O CPA	160076-5011	A1-BLK-CLIP	GCO	PLR		M	R											SALEABLE		TBD	TBD
KEY B, LIGHT GRAY, W/ CLIPSLOT, W/O CPA	160076-5012	B1-LG-CLIP	GCO	PLR		M	R											SALEABLE		TBD	TBD
KEY C, DARK GRAY, W/ CLIPSLOT, W/O CPA	160076-5013	C1-DG-CLIP	GCO	PLR		M	R											SALEABLE		TBD	TBD
KEY D, STONE GRAY, W/ CLIPSLOT, W/O CPA	160076-5014	D1-SG-CLIP	GCO	PLR		M	R											SALEABLE		TBD	TBD
VOID KEY	160076-5015	$>\!\!<$	$>\!\!<$	${}$	$\times$	$\supset \!$	$\supset$	$\supset \!$	$\supset$	$\supset$	$\supset \!$	$\supset \subset$	$\boxtimes$	$\supset \!$	$\supset \subset$	$\times$	$\supset \!$		$\backslash\!\!\!/$	$\sim$	$\sim$
KEY A, BLACK, W/ CLIPSLOT, W/ CPA	160076-5016	A1-BLK-CLIP	GCO	PLR	CPA	M	R											SALEABLE		TBD	TBD
KEY B, LIGHT GRAY, W/ CLIPSLOT, W/ CPA	160076-5017	B1-LG-CLIP	GCO	PLR	CPA	M	R											SALEABLE		TBD	TBD
KEY C, DARK GRAY, W/ CLIPSLOT, W/ CPA	160076-5018	C1-DG-CLIP	GCO	PLR	CPA	M	R											SALEABLE		TBD	TBD
KEY D, STONE GRAY, W/ CLIPSLOT, W/ CPA	160076-5019	D1-SG-CLIP	GCO	PLR	CPA	M	R											SALEABLE		TBD	TBD
VOID KEY	160076-5020	$>\!\!<$	$\sim$	$\overline{}$	$\geq$	$\supset \subset$	$\supset \subset$	$\supset \subset$	$\supset$	$\supset$	$\searrow$	>>	$\supset$	$\supset \!$	$>\!\!<$	$\sim$	$\supset \!$		$\backslash\!\!\!/$	$\sim$	$\sim$
KEY A, BLACK, W/ CPA	160076-5021	A1-BLK	GCO	PLR	CPA	M	R							7				SALEABLE		TBD	TBD
KEY A, BLACK, W/ CPA	160076-5022	A1-BLK	GCO	PLR	CPA	M	R									9	10	SALEABLE		TBD	TBD
KEY A, BLACK, W/ CPA	160076-5023	A1-BLK	GCO	PLR	CPA	M	R							7	8	9		SALEABLE		TBD	TBD
KEY A, BLACK, W/ CPA	160076-5024	A1-BLK	GCO	PLR	CPA	М	R							7	8		10	SALEABLE		TBD	TBD
KEY A, BLACK, W/ CPA	160076-5025	A1-BLK	GCP	PLR	CPA	М	R	1		3		5		1				OK TO TOOL		TBD	TBD
KEY A, BLACK, W/ CPA	160076-5026	A1-BLK	GCP	PLR	CPA	М	R		2		4		6					OK TO TOOL		TBD	TBD
KEY B, LIGHT GRAY, W/ CPA	160076-5027	B1-LG	GCP	PLR	CPA	М	R	1	2	3		5						OK TO TOOL		TBD	TBD

EC: 677478 DOCUMENT NO.: E-160076-0002