

SILICON BRIDGE RECTIFIERS

Features

- ◆ The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- ◆ Ideal for printed circuit boards
- ◆ Low reverse leakage
- ◆ High forward surge current capability
- ◆ High temperature soldering guaranteed:
260°C/10 seconds, 0.375"(9.5mm) lead length, 5 lbs. (2.3kg) tension

Mechanical Data


Case : JEDEC KBL Molded plastic body

Terminals : Solder plated, solderable per MIL-STD-750, Method 2026

Polarity : Polarity symbol marking on body

Mounting Position : Any

Weight : 0.20ounce , 5.6 grams



Dimensions in inches and (millimeters)

Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter	SYMBOLS	MDD KBL6005	MDD KBL601	MDD KBL602	MDD KBL604	MDD KBL606	MDD KBL608	MDD KBL610	MDD KBL612	UNITS
Marking Code										
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	800	1000	1200	V
Maximum RMS voltage	V_{RMS}	35	70	140	280	420	560	700	840	V
Maximum DC blocking voltage	V_{DC}	50	100	200	400	600	800	1000	1200	V
Maximum average forward output rectified current at $T_A=50^\circ C$	$I_{(AV)}$	6.0								A
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	200								A
Rating for fusing ($t < 8.3ms$)	I^2t	166								A^2sec
Maximum instantaneous forward voltage drop per bridge element at 6.0A	V_F	1.1								V
Maximum DC reverse current $T_A=25^\circ C$ at rated DC blocking voltage $T_A=125^\circ C$	I_R	10								μA
		1.0								mA
Typical Junction Capacitance	C_J	105								pF
Typical Thermal Resistance (Note 1)	$R_{\theta JA}$	10								$^\circ C/W$
Operating junction temperature range	T_J	-55 to +150								$^\circ C$
storage temperature range	T_{STG}	-55 to +150								$^\circ C$

NOTES:

1. Thermal resistance from Junction to Ambient on P.C. board mounting.

Ratings And Characteristic Curves

Fig. 1 Derating Curve for Output Rectified Current




Fig. 2 Maximum Non-repetitive Peak Forward Surge Current




Fig. 3 Typical Instantaneous Forward Characteristics




Fig. 4 Typical Reverse Characteristics at $T_J = 25^\circ\text{C}$





Fig. 5 Typical Junction Capacitance



The curve above is for reference only.